

Specification Of Thermal Transfer Printable Labels

Application(s):	Circuit Board ID, Component ID, Through Hole - Top
Agency Approval (s)/Compliance:	JIG Compliant, UL Recognized
Size:	0.750" W x 0.250" H (19.050 mm W x 6.350 mm H)
Printable Area:	0.750" W X 0.250" H (19.050 mm W X 6.350 mm H)
Web Width:	3.350" (85.09 mm)
Label Type/Style:	Label
Vertical Repeat:	0.350" (8.89 mm)
Color:	Light Green
Finish:	Gloss
Qty Per Row:	4
Material Type:	Light Green Polyimide
Material Description:	Polyimide
Brady Material #:	B-476
Recommended Ribbon Series:	6000
Suggested Ribbon Part#:	R6002
Acceptable Ribbon Series:	6000. 6500
After Process:	Yes, this material will work with this application
Printer Compatibility:	BBP81, Brady 200MVP Plus, Brady 300MVP Plus, Brady 300X-Plus II, Brady 360X-Plus II, Brady 600X Plus II, IP300, IP600, Thermal Transfer Printers
Surface:	Smooth
Surface Mount Technology:	Yes, this material will work with this application
Through Hole Technology:	Yes, this material will work with this application
RoHS Compatibility:	Pass 2002/95/EC
QTY/UOM:	10,000/ Roll