



DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC []

This drawing is the property of Tusonix, Inc., and may not be used, reproduced, published or disclosed to others without expressed authorization by Tusonix Inc.

**Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.**



TUSONIX STYLE	6003
RESONATOR TYPE	QUARTER WAVE
RESONANCE FREQUENCY	2900 MHz $\pm$ 1%
K	10 (NOM)
TEMP. COEFFICIENT	$\pm$ 10 PPM/ $^{\circ}$ C
QUALITY FACTOR Q	> 280

NOTES:

1. TERMINATION: TIN PLATED OVER FIRED ON SILVER, WITH A NICKEL BARRIER.
2. THIS END LAPPED.

REVISION RECORD Original Release C.O. WAS SK 8288-000. S.M. 02-15-07 20070208-3-02 ADDED NOTE 2 & REVISED NOTE 1. S.M. 10-08-07 20071017-1-02	0	--TOLERANCES-- Unless Otherwise Specified DECIMAL ± .010 [0.25] ANGLES ± TUSONIX TUCSON, ARIZONA	Title 2900 MHz COAXIAL RESONATOR	
	1		Drawn S.M. 01-29-07	Scale 6 X
	Approved M.M. 01-29-07			
	A		6003-014-2900-D0C1	