




W-series sets standards!

When it comes to functional perfection even in details, Weidmüller's W-series defines the market standards for many years now!

The W-series comprises products for conductor cross-sections between 1.5 and 300 mm² which can be used for all important electrical applications (connecting, protecting, disconnecting, measuring....). Especially in the following fields the W-series plays a major role:

- Industrial automation
- Building control
- Transport technology
- Process control

Steady progress!

In the range of screw-connection terminals, no other product assortment available on the market has made such consequent improvements and has taken up new developments as the W-series! This success is reflected by our current new developments:

- **WPE 1.5/ R3.5** (prot. conductor terminals) extension of the slimmest product family (3.5 mm) for TS 15 available on the market
- **WDU 4N** (feed-through terminals)
WPE 4N (prot. conductor terminals) Extension of the range of "compact design" terminals, which are especially conceived for confined spaces
- **WDU 10ZR** (feed-through terminals)
WPE 10ZR (prot. conductor terminals) 10 mm² terminal with in total 4 mm² connection for measuring and control applications
- **WDU 240** (feed-through terminals) Acc. to clamping yoke principle for all nominal cross-sections.
WDU 50 / WDU 95 under preparation
- **WF 6-12** (stud terminals) New assortment of single-stud terminals in Wemid (V0) and up to 2300 V
- **ST 4000** (stud terminals) New range of double-stud terminals with a rated voltage of V0 and 4000 V, in particular suitable for railway applications. Weidmüller is the only supplier of stud terminals in the range 0...4000 V.

What is more, all products currently available are continuously improved to fulfill the demands of our customers. Examples:

- **WPE 2.5 / WPE 4**
- **WDK 2.5 F** product range
- **WNT 2.5**

W-series offers advantages


The W-series provides the highest number of advantages compared to all other screw-connection terminals currently available!

1) Easy project planning


- matching contour dimensions between 1.5 – 16 mm² in standard design
- uniform accessories for different cross-section ranges (WDU 2.5 to WDU 16)
- convenient terminal marking options thanks to two marking systems, WS / DEK
- special design of clamping units for connection of 2 conductors (see chapter "Accessories"/page 311)
- Optional selection between standard design with all features and the space-saving compact design for feed-through terminals

2) Maximum safety level

- Wemid insulating material




- best tracking index - non-tracking CTI 600
- temperature-resistant up to 120 °C - no derating up to 75 °C
- self-extinguishing – V0 according to UL
- no harmful substances
- safe from finger-touch (according to VGB 4)
- Best contact reliability thanks to patented clamping yoke system



- 2 conductors of the same cross-section can be connected in EEx e
- no ferrules necessary
- large gas-tight contact – low voltage drop
- highly flexible conductors connectable
- high contact force
- 100 % vibration-proof – no retightening of clamping screws required

3) Time-saving potential distribution with pluggable cross-connection system (ZQV)

40 % of all terminals are cross-connected! Weidmüller offers the screw cross-connection system WQV and the pluggable cross-connection system ZQV. The cross-connection system ZQV can be used for 75 % of all applications (feed-through and double-deck terminals 2.5 and 4 mm², disconnect-test and fuse terminals).



- parallel routing of 2 or 3 potentials (WDU 2.5 and WDU 4)
- easy extension
- coloured marking
- safe from finger-touch (VGB 4)
- faster mounting than screw-type cross-connections

4) Easy mounting

- ergonomic design through recessed grips
- snap-on and removal possible on both sides
- funnel-shaped wire insertion aperture
- no ferrules required
- self-centering on TS 35


5) Convenient testing options

- use of contact-proof test socket screw, partially also for mounted cross-connections WQV
- safe locking on terminal support with test adapter WTA


Feed-through terminals

Standard design


WDU 2.5



WDU 4



WDU 6



Max. technical data

Dimensions / approvals

Width/length/height (mm) with TS 35 x 7.5

Insulation stripping length/clamping screw/screwdriver blade

VDE rated data 0611 Part 1/8.92/IEC 60 947-7-1

Rated voltage/current/cross-section

Rated impulse voltage/pollution severity

Further technical data

Tightening torque range Nm

Torque setting with DMS 2 electric screwdriver

Clampable conductors

Solid H07V-U mm²

Stranded H07V-R mm²

Flexible H07V-K mm²

Flexible H07V-K and ferrule acc. to DIN 46 228/1 mm²

Flexible H07V-K and ferrules with plastic insul. collar mm²

Max. clamping range in mm² / gauge pin iaw. 60 947-1 Size

Cont. current of cross-connect. WQV/ZQV 2-5-pole A

Cont. current of cross-connect. WQV/ZQV 6-10-pole A

UL/CSA rated data

Voltage/current/conductor size UL

Voltage/current/conductor size CSA

Ordering data

Version

Dark beige Wemid

Blue Wemid

Orange PA

Block of 10 terminals, print. mark. DEK 5 1-9 Wemid

Block of 10 terminals, unprint. mark. DEK 5 neutral 1-9 Wemid

End plate/partition

Dark beige Wemid

Blue Wemid

Dark beige Wemid

Blue Wemid

WAP (thickn. 1.5 mm)

WTW

Cross-connection

2-pole WQV ZQV

3-pole WQV ZQV

4-pole WQV ZQV

5...9-pole WQV see p. 262 / ZQV see p. 263

10-pole WQV ZQV

50 and/or 41-pole WQV ZQV

Cross-connection comb WQV ZQV

Screening bar LS 2.8

Notching tool WAW 1

Test adapter

WTA

TA 1

Strain relief

Test plug/socket (safe from finger-contact ⁴⁾)

PS 2.3 Test plug (ø2.3 mm)

Test plug (ø4.0 mm)

Test socket screw 8.5 (ø2.3 mm)

StB 8.5 Test socket screw 14 (ø4.0 mm)

Covers

With symbol

White

WAD for self-labelling/white

Group marking

WGB

T5

Tag carrier for S 10 markers

Marking tags

Print

DEK Standard

WS white neutral

WS indiv. printed

Mounting rails, end brackets, further marking materials see "Accessories"

¹⁾ Ferrules with optimum diam. for terminals with 5 mm pitch:

Cat. No. 1333100000

32 A/4 mm²

5/60/47

10 mm/M 2.5/3.5 x 0.6

800 V/24 A/2.5 mm²

8 kV/3

0.4...0.8

1

0.5...4

1.5...4

0.5...4

0.5...2.5

0.5...2.5¹⁾

0.13...4

32/24

32/24

600 V/25 A/22...12 AWG

600 V/20 A/26...12 AWG

Type Cat. No. Qty.

WDU 2.5 1020000000 100

WDU 2.5 1020080000 100

WDU 2.5 1020060000 100

WDU 2.5/10 1020700000 10

WDU 2.5/10 1020800000 10

Type Cat. No. Qty.

WAP 2.5-10 1050000000 50

WAP 2.5-10 1050080000 50

WTW 2.5-10 1050100000 20

WTW 2.5-10 1050180000 20

41 A/6 mm²

6/60/47

10 mm/M 3/3.5 x 0.6

800 V/32 A/4 mm²

8 kV/3

0.5...1.0

2

0.5...6

1.5...6

0.5...6

0.5...4

0.5...4

0.13...6

41/32

41/32

600 V/35 A/22...10 AWG

600 V/35 A/26...10 AWG

Type Cat. No. Qty.

WDU 4 1020100000 100

WDU 4 1020180000 100

WDU 4/10 1020900000 10

WDU 4/10 1021000000 10

Type Cat. No. Qty.

WAP 2.5-10 1050000000 50

WAP 2.5-10 1050080000 50

WTW 2.5-10 1050100000 20

WTW 2.5-10 1050180000 20

57 A/10 mm²

8/60/47

12 mm/M 3.5/4.0 x 0.8

800 V/41 A/6 mm²

8 kV/3

0.8...1.4

3

0.5...10

1.5...10

0.5...10

0.5...10

0.5...6

0.5...10

0.5...10

57/57

57/57

600 V/45 A/20...8 AWG

600 V/45 A/20...8 AWG

Type Cat. No. Qty.

WDU 6 1020200000 100

WDU 6 1020280000 100

WDU 6 1021400000 10

WDU 6/10 1021300000 10

Type Cat. No. Qty.

WAP 2.5-10 1050000000 50

WAP 2.5-10 1050080000 50

WTW 2.5-10 1050100000 20

WTW 2.5-10 1050180000 20

Standard design

Max. technical data

Dimensions / approvals

Width/length/height (mm) with TS 35 x 7.5

Insulation stripping length/clamping screw/screwdriver blade

VDE rated data 0611 Part 1/8.92/IEC 60 947-7-1

Rated voltage/current/cross-section

Rated impulse voltage/pollution severity

Further technical data

Tightening torque range Nm

Torque setting with DMS 2 electric screwdriver

Clampable conductors

Solid H07V-U mm²

Stranded H07V-R mm²

Flexible H07V-K mm²

Flexible H07V-K and ferrule acc. to DIN 46 228/1 mm²

Flexible H07V-K and ferrules with plastic insul. collar mm²

Max. clamping range in mm² / gauge pin iaw. 60 947-1 Size

Cont. current of cross-connect. WQV/ZQV 2-5-pole A

Cont. current of cross-connect. WQV/ZQV 6-10-pole A

UL/CSA rated data

Voltage/current/conductor size UL

Voltage/current/conductor size CSA

Ordering data

Dark beige Wemid

Blue Wemid

Dark beige Wemid

Blue Wemid

End plate/partition

Dark beige Wemid

Blue Wemid

Dark beige Wemid

Blue Wemid

WAP (thickn. 1.5 mm)

WTW

Cross-connection

2-pole WQV

3-pole WQV

4-pole WQV

5...9-pole WQV see p. 262

10-pole WQV

2-pole Blue

Cross-connection comb

LS 2.8 Screening bar

Notching tool

Test adapter

WTA

TA 1

Strain relief

Test plug/socket (safe from finger-contact ¹⁾)

PS 2.3 Test plug (ø2.3 mm)

Test plug (ø4.0 mm)

Test socket screw 8.5 (ø2.3 mm)

StB 8.5 Test socket screw 14 (ø4.0 mm)

Covers

With symbol

white

WAD for self-labelling/white

Group marking

WGB

T5

Tag carrier for S 10 markers

Marking tags

DEK Standard

WS white neutral


WS indiv. printed

Mounting rails, end brackets, further marking materials see "Accessories"

¹⁾ Finger-safe test socket screw 1071000000 can be used for WDU 10

²⁾ When using the screening bar, rated voltage is reduced to 400 V!

WDU 10



76 A/16 mm²

10/60/47

12 mm/M 4/5.5 x 1.0

1000 V/57 A/10 mm²

8 kV/3

1.2...2.4

4

1.5...16

1.5...16 (16 mm² with 2.4 Nm)

1.5...16

1.5...16

1.5...16

1.31...16

B 6

76/-

63/-

600 V/60 A/16...6 AWG


600 V/65 A/16...6 AWG

Type Cat. No. Qty.

WDU 10 1020300000 50

WDU 10 1020380000 50

WDU 16 • WDU 16/ZA³⁾



101 A/25 mm²

12/60/63

16 mm/M 5/5.5 x 1.0

1000 V/76 A/16 mm²

8 kV/3

2.0...4.0

1.5...16

1.5...25

1.5...25

1.5...16

1.5...16

1.5...25

B 7

101/-

76/-

600 V/70 A/14...6 AWG


600 V/65 A/14...6 AWG

Type Cat. No. Qty.

WDU 16 1028900000 1020400000 50

WDU 16 1028980000 1020480000 50

WDU 35 • WDU 35/ZA³⁾



150 A/50 mm²

16/60/63

18 mm/M 6/6.5 x 1.2

1000 V/125 A/35 mm²

8 kV/3

2.5...5.0 / 3.0...6.0⁴⁾

2.5...16

2.5...50 (with 4 Nm) 6 x 9 x 0.8

2.5...35 9 x 9 x 0.8

2.5...35

2.5...35

2.5...50

B 9

138/-

112/-

600 V/115 A/12...2 AWG

600 V/120 A/12...2 AWG

Type Cat. No. Qty.

WDU 35 1028800000 25 1020500000 40

WDU 35 1028880000 25 1020580000 40

WDU 35 1029000000 25 1020600000 25

Hex. socket Hex. socket

WDU 35 1029080000 25 1020680000 25

Hex. socket Hex. socket

Type Cat. No. Qty.

WAP 16-35 1050100000 20

WAP 16-35 1050180000 20

Type Cat. No. Qty.

WQV 35/2 1053060000 50

WQV 35/3 1055360000 50

WQV 35/4 1055460000 50

WQV see p. 262

WQV 35/10 1053160000 10

WQV 35/2 Blue 1053080000 50

Type Cat. No. Qty.

WAW 1 9004500000 1

Type Cat. No. Qty.

PS 4 (ø 4) 0299600000 20

PS 4 (ø 4) 0299600000 20

StB 16 (ø 4) 0140200000 50

StB 16 (ø 4) 0140200000 50

WAD 12 1055960000 50

WAD12 white 1056260000 50

Type Cat. No. Qty.

T 5 0348500000 100

SF 10 0332400000 1000

SG 10 0332500000 1000

Type Cat. No. Qty.

DEK 5 see "Accessories"

WS 12/6.5 1609920000 540

WS 12/6.5 1609930000 108

Type Cat. No. Qty.

DEK 5 see "Accessories"

WS 12/6.5 1609920000 540

WS 12/6.5 1609930000 108

Type Cat. No. Qty.

DEK 5 see "Accessories"

WS 12/6.5 1609920000 540

WS 12/6.5 1609930000 108

Type Cat. No. Qty.

DEK 5 see "Accessories"

WS 12/6.5 1609920000 540

WS 12/6.5 1609930000 108

Type Cat. No. Qty.

DEK 5 see "Accessories"

WS 12/6.5 1609920000 540

WS 12/6.5 1609930000 108

Type Cat. No. Qty.

DEK 5 see "Accessories"

WS 12/6.5 1609920000 540

WS 12/6.5 1609930000 108

Type Cat. No. Qty.

DEK 5 see "Accessories"

WS 12/6.5 1609920000 540

WS 12/6.5 1609930000 108

Feed-through terminals

Compact-Design "N" for low type

Max. technical data

Dimensions / approvals

Width/length/height (mm) with TS 35 x 7.5

Insulation stripping length/clamping screw/screwdriver blade

VDE rated data 0611 Part 1/8.92/IEC 60 947-7-1

Rated voltage/current/cross-section

Rated impulse voltage/pollution severity

Further technical data

Tightening torque range Nm

Torque setting with DMS 2 electric screwdriver

Clampable conductors

Solid H07V-U mm²

Stranded H07V-R mm²

Flexible H07V-K mm²

Flexible H07V-K and ferrule acc. to DIN 46 228/1 mm²

Flexible H07V-K and ferrules with plastic insul. collar mm²

Max. clamping range in mm² / gauge pin iaw. 60 947-1 Size

Cont. current of cross-connect. WQV/ZQV 2-5-pole A

Cont. current of cross-connect. WQV/ZQV 6-10-pole A

UL/CSA rated data

Voltage/current/conductor size UL

Voltage/current/conductor size CSA

Ordering data

Version

Dark beige Wemid

Blue Wemid

Orange PA

Block of 10 terminals, print. mark. DEK 5 1-9 Wemid

Block of 10 terminals, unprint. mark. DEK 5 neutral 1-9 Wemid

End plate/partition

Dark beige Wemid

Cross-connection



WQV



ZQV

2-pole

3-pole

4-pole

5...9-pole

10-pole

50-pole



WQB 12/24

Cross-connection comb



LS 2.8

Screening bar

Notching tool

Test adapter



WTA

TA 1

Strain relief

Test plug/socket (safe from finger-contact¹⁾)



PS 2.3

Test plug (ø2.3 mm)

Test plug (ø4.0 mm)



StB 8.5

Test socket screw 8.5 (ø2.3 mm)

Test socket screw 14 (ø4.0 mm)


Covers



With symbol

white

WAD for self-labelling/white



WGB

T5

Tag carrier for S 10 markers

Marking tags

Print



DEK



WS

Standard

WS white neutral

WS indiv. printed

WDU 16N



101 A/25 mm²

12/60/47

12 mm/M 4/5.5 x 1.0

690 V/76 A/16 mm²

6 kV/3

1.2...2.4

4

1.5...16

1.5...25 (25 mm with 2.2 Nm)

1.5...16

1.5...16

1.5...16

1.5...25 B 7

76/-

57 (3 + 4-pole)/-

300 V/70 A/14...6 AWG

300 V/45 A/20...8 AWG

Type Cat. No. Qty.

WDU 16N 1036100000 50

WDU 16N BL 1036180000 50

Type Cat. No. Qty.

WTW EX 1058800000 20

WDU 35N



150 A / 50 mm²

16/66/51

18 mm/M 6/5.5 x 1.0

500 V/125 A/35 mm²

6 kV/3

2.5...5.0

Conductor Strips

2.5...16 3 x 9 x 0.8

2.5...50 6 x 9 x 0.8

2.5...35 9 x 9 x 0.8

2.5...35

2.5...35

2.5...50 B 9

115/-

100/-

300 V/10 A/12...2 AWG

300 V/10 A/12...2 AWG


Type Cat. No. Qty.

WDU 35N 1040400000 20

WDU 35N BL 1040480000 20

Type Cat. No. Qty.

WDU 70N



192 A/70 mm²

20.5/75/86

22 mm/M 8/5 6 DIN 6911

1000 V/192 A/70 mm²

8 kV/3

6.0...10

Conductor Strips

10...16 3 x 9 x 0.8

10...95 6 x 9 x 0.8

10...70 9 x 9 x 0.8

10...70

10...70

10...95 B 11

192/-

192 (3-pole)/-

600 V/175 A/6...2/0 AWG

600 V/205 A/8...2/0AWG

Type Cat. No. Qty.

WDU 70 N/35 9512190000 10

WDU 70 N/3 BL 9512420000 10

(WDU 70N only with hexagonal socket)

Type Cat. No. Qty.

¹⁾ Finger-safe StB 1071000000 can be used for WDU 16N

Feed-through terminals

Compact-Design “N” for low type

Max. technical data

Dimensions / approvals

Width/length/height (mm) with TS 35 x 7.5

Insulation stripping length/clamping screw/screwdriver blade

VDE rated data 0611 Part 1/8.92/IEC 60 947-7-1

Rated voltage/current/cross-section

Rated impulse voltage/pollution severity

Further technical data

Tightening torque range Nm

Torque setting with DMS 2 electric screwdriver

Clampable conductors

Solid H07V-U mm²

Stranded H07V-R mm²

Flexible H07V-K mm²

Flexible H07V-K and ferrule acc. to DIN 46 228/1 mm²

Flexible H07V-K and ferrules with plastic insul. collar mm²

Max. clamping range in mm² / gauge pin iaw. 60 947-1 Size

Cont. current of cross-connect. WQV/ZQV 2–5-pole A

Cont. current of cross-connect. WQV/ZQV 6–10-pole A

UL/CSA rated data

Voltage/current/conductor size UL

Voltage/current/conductor size CSA

Ordering data

Version

Dark beige Wemid

Blue Wemid

Orange PA

Block of 10 terminals, print. mark. DEK 5 1–9 Wemid

Block of 10 terminals, unprint. mark. DEK 5 neutral 1–9 Wemid

End plate/partition



WAP (thickness 1.5 mm) WTW

Cross-connection



ZQV



WQB 12/24



LS 2.8

Test adapter



TA 1

Marking tags

Print



DEK Standard


WS white neutral

WS indiv. printed

Mounting rails, end brackets, further marking materials see “Accessories”

¹⁾ When using the screen plug, rated voltage is reduced to 400 V!

WDK 2.5N



28 A/4 mm²

5/60/62

8 mm/M 2.5/3.5 x 0.6

800 V/24 A/2.5 mm²

8 kV/3

0.4...0.6

1

0.5...4

1.5...4

0.5...4

0.5...2.5

0.5...2.5

0.13...4

A 3

-/24

-/24

600 V/20 A/16...12 AWG

300 V/20 A/26...12 AWG

Type	Cat. No.	Qty.
WDK 2.5N	1041600000	100
WDK 2.5N	1041680000	100
WDK 2.5N	1041660000	100
WDK 2.5N/10	1041700000	10
WDK 2.5N/10	1041800000	10
Type	Cat. No.	Qty.
WAP	1084000000	20
WAP BL	1084080000	20
WTW	1058800000	20

WDK 2.5N V



28 A/4 mm²

5/60/62

8 mm/M 2.5/3.5 x 0.6

800 V/24 A/2.5 mm²

8 kV/3

0.4...0.6

1

0.5...4

1.5...4

0.5...4

0.5...2.5

0.5...2.5

0.13...4

A 3

-/24


-/24

600 V/20 A/16...12 AWG

300 V/20 A/26...12 AWG

Type	Cat. No.	Qty.
WDK 2.5N V	1041610000	100
Type	Cat. No.	Qty.
WAP	1084000000	20
WAP BL	1084080000	20
WTW	1058800000	20

WDK 2.5N DU-PE



28 A/4 mm²

5/60/62

8 mm/M 2.5/3.5 x 0.6

800 V/24 A/2.5 mm²

8 kV/3

0.4...0.6

1

0.5...4

1.5...4

0.5...4

0.5...2.5

0.5...2.5

0.13...4

A 3

-/24

-/24

600 V/20 A/16...12 AWG

300 V/20 A/26...12 AWG

Type	Cat. No.	Qty.
WDK 2.5N DU-PE	1041650000	100
lower connection level marked in green-yellow		
Type	Cat. No.	Qty.
WAP	1084000000	20
WAP BL	1084080000	20
WTW	1058800000	20

Feed-through terminals


Large-size conductors no longer have to be inserted into the clamping unit with force; they can easily be placed in the terminal.

For each terminal type, terminal-block variants are available - consisting of three-, four- or five-pole terminals - in addition to the individual terminals. All blocks are permanently screwed together for additional torsional rigidity.

Slots provided in the underside of the terminals enable direct fitting. Terminal blocks can be screwed directly to the mounting plates with 25 mm pitch.

Further advantages are:


- Constant force transmission by self-adjusting connection system
- Random wiring direction
- Safe from finger-touch (VBG 4), even with cross-connection fitted
- Extreme distortion resistance



Open terminal cover and remove screw unit



Place conductor in terminal and replace screw unit



Close cover and tighten screw with hexagon wrench

Max. technical data

Dimensions / approvals

Width/length/height (mm) with TS 35 x 7.5

Insul. strip. length/clamp. screw/wrench size acc. to DIN 6911

VDE rated data 0611 Part 1/8.92/IEC 60 947-7-1

Rated voltage/current/cross-section

Rated impulse voltage/pollution severity

Further technical data

Tightening torque range Nm

Torque setting with DMS 2 electric screwdriver

Clampable conductors

Solid H07V-U mm²

Stranded H07V-R mm²

Flexible H07V-K mm²

Flexible H07V-K and ferrule acc. to DIN 46 228/1 mm²

Flexible H07V-K and ferrules with plastic insul. collar mm²

Strips mm

Strips mm

Max. clamping range in mm² Gauge pin iaw. 60 947-1 Size

Cont. current of cross-connect. 2-pole A

Cont. current of cross-connect. Multi-pole A

UL/CSA rated data

Voltage/current/conductor size UL

Voltage/current/conductor size CSA

Ordering data Version

Hexagonal socket 6 mm Dark beige Wemid

Hexagonal socket 6 mm Blue Wemid

Hexagonal socket 6 mm Green Wemid

Hexagonal socket 6 mm Terminal block¹⁾ 3-pole Wemid

Hexagonal socket 6 mm Terminal block¹⁾ 4-pole Wemid

Hexagonal socket 6 mm Terminal block¹⁾ 5-pole Wemid

Mains terminal block 3 x beige, 1x blue, 1x green Wemid

Cross-connection



Auxiliary/control conductor terminal Pressure piece³⁾

WZAD (up to 4 mm², 32 A)

WFL




Cover



Test plug



Fixing screw



Hexagon wrench



Screwdriver for direct fitting 1 x 5.5 x 125



Marking tags



Print

DEK Standard

WS white neutral


WS indiv. printed

Mounting rails, end brackets, further marking materials see "Accessories"

¹⁾ Terminal block for direct fitting only

²⁾ Using 95 and 120 mm² with 10 Nm tightening torque

WDU 70/95



232 A/95 mm²

27/132/108

30 mm/M 8/S 6

1000 V/232 A/95 mm²

8 kV/3

6...12

16

16...120²⁾

16...95²⁾

16...95²⁾

16...50

3 x 9 x 0.8

4 x 16 x 0.8

16...120

232

(3) 232

600 V/175 A/6...2/0 AWG

600 V/205 A/6...2/0 AWG

WDU 70/95

WDU 70/95

WDU 70/95

WDU 70/95

WDU 70/95

WDU 70/95

WDU 70/95

WDU 70/95

WDU 70/95

WDU 70/95

WDU 70/95

WDU 70/95

WDU 70/95

WDU 70/95

WDU 70/95

WDU 70/95

WDU 70/95

WDU 70/95

WDU 70/95

WDU 70/95

WDU 70/95

WDU 70/95

WDU 70/95

WDU 70/95

WDU 70/95

WDU 70/95

WDU 70/95

WDU 70/95

WDU 70/95

WDU 70/95

WDU 70/95

WDU 70/95

WDU 70/95

WDU 70/95

WDU 70/95

WDU 70/95

WDU 70/95

WDU 70/95

WDU 70/95

WDU 70/95

WDU 70/95

WDU 70/95

WDU 70/95

WDU 70/95

WDU 70/95

WDU 70/95

WDU 70/95

WDU 70/95

WDU 70/95

WDU 70/95

WDU 70/95

WDU 70/95

WDU 70/95

WDU 70/95


WDU 70/95

WDU 70/95

WDU 70/95

Feed-through terminals

WDU 70/95/...



Drill template for direct fitting
232 A/95 mm²

81/132/108 (block of 3)*

30 mm/M 8/S 6

1000 V/232 A/95 mm²

8 kV/3

6...12

16

16...120²⁾

16...95²⁾

16...95²⁾

16...50

3 x 9 x 0.8

6 x 9 x 0.8

4 x 16 x 0.8

6 x 16 x 0.8

16...120

B 12

232

(3) 232

600 V/175 A/6...2/0 AWG

600 V/205 A/6...2/0 AWG

Type	Cat. No.	Qty.
WDU 70/95/...	1026700000 ¹⁾	4
WDU 70/95/...	1026800000 ¹⁾	3
WDU 70/95/...	1026900000 ¹⁾	2
WDU 70/95/...	1032300000 ¹⁾	2
Type	Cat. No.	Qty.
WQV 70/2	1063500000	5
WQV 70/3	1063600000	5

WZAD 70

1066000000

10

WFL 70/95

1616330000

10

WAD 27

With danger sign

1062860000

10

WAD 27

Without danger sign

1062960000

10

PS 4

0299600000

20

Pluggable in screw head of connection system

M 6x16

1063700000

20

SK wrench

0407900000

1

6 mm acc. to DIN 6911

SDI

9008410000

1

DEK 5

see "Accessories"

WS 12/6.5

1609920000


540

WS 12/6.5

1609930000

108

WDU 120/150



309 A/150 mm²

32/132/118

35 mm/M 10/S 6

1000 V/269 A/120 mm²

8 kV/3

10...20

35...150

35...150

35...95

35...50

3 x 9 x 0.8

6 x 9 x 0.8

4 x 16 x 0.8

6 x 16 x 0.8

35...150

B 13

292

(3) 292

600 V/225 A/2...250 kcmil AWG

600 V/285 A/2...250 kcmil AWG

Type	Cat. No.	Qty.
WDU 120/150	1024500000	10
WDU 120/150	1024580000	10
WDU 120/150	1024550000	10

Type

Cat. No.

Qty.

WQV 120/2

1063300000

5

WQV 120/3

1063400000

5

WZAD 120

1066100000

10

WFL 120/150

1616340000

10

WAD 27

With danger sign

1062860000

10

WAD 27

Without danger sign

1062960000

10

PS 4

0299600000

20

Pluggable in screw head of connection system

M 6x16

1063700000

20

SK wrench

0407900000

1

6 mm acc. to DIN 6911

SDI

9008410000

1

DEK 5

see "Accessories"

WS 12/6.5

1609920000


540

WS 12/6.5

1609930000

108

WDU 120/150/...



Drill template for direct fitting
309 A/150 mm²

96/132/118 (block of 3)*

35 mm/M 10/S 6

1000 V/269 A/120 mm²

8 kV/3

10...20

35...150

35...150

35...95

35...50

3 x 9 x 0.8

6 x 9 x 0.8

4 x 16 x 0.8

6 x 16 x 0.8

35...150

B 13

292

(3) 292

600 V/225 A/2...250 kcmil AWG

600 V/285 A/2...250 kcmil AWG

Type	Cat. No.	Qty.
WDU 120/150/...	1026400000 ¹⁾	3
WDU 120/150/...	1026500000 ¹⁾	2
WDU 120/150/...	1026600000 ¹⁾	2
WDU 120/150/...	1032400000 ¹⁾	2
Type	Cat. No.	Qty.
WQV 120/2	1063300000	5
WQV 120/3	1063400000	5

WZAD 120

1066100000

10

WFL 120/150

1616340000

10

WAD 27

With danger sign

1062860000

10

WAD 27

Without danger sign

1062960000

10

PS 4

0299600000

20

Pluggable in screw head of connection system

M 6x16

1063700000

20

SK wrench

0407900000

1

6 mm acc. to DIN 6911

SDI

9008410000

1

DEK 5

see "Accessories"

WS 12/6.5

1609920000

540

WS 12/6.5

1609930000


108

¹⁾ Terminal block for direct fitting only


²⁾ Using 95 and 120 mm² with 10 Nm tightening torque

Stud terminals


WF 6




WF 8



WF 10



WF 12



Max. technical data

Dimensions / approvals

Width/length/height with 	mm
Pitch with partition	mm
Stud size	

125 A/35 mm ²
 
19.6 / 67 / 56
18
M6

150 A/50 mm ²
 
24.6 / 67 / 65
23
M8

265 A/120mm ²
 
35.6 / 67 / 74
34
M10

265 A/120mm ²
 
35.6 / 67 / 72
34
M12

Rated data

Rated voltage/current/cross-section
Rated voltage/current/cross-section
Rated impulse voltage/pollution severity ¹⁾
Rated impulse voltage/pollution severity ²⁾

1000 V ¹⁾ / - / -
2.300 V ²⁾ / - / -
8 kV / 3
12 kV / PD 3

1000 V ¹⁾ / - / -
2.300 V ²⁾ / - / -
8 kV / 3
12 kV / PD 3

1000 V ¹⁾ / - / -
2.300 V ²⁾ / - / -
8 kV / 3
12 kV / PD 3

1000 V ¹⁾ / - / -
2.300 V ²⁾ / - / -
8 kV / 3
12 kV / PD 3

Further technical data

Tightening torque range	Nm
-------------------------	----

3 ... 6

6 ... 12

10 ... 20

14 ... 31

Clampable conductors

DIN 46234 / number per side ¹⁾
DIN 46235 / number per side ¹⁾
DIN 46234 / number per side ²⁾
DIN 46235 / number per side ²⁾

...35 / 2
...25 / 2
...35 / 1
...25 / 1

...50 / 2
...35 / 2
...50 / 1
...35 / 1

...120 / 2
... 95 / 2
...120 / 1
... 95 / 1

...120 / 2
... 95 / 2
...120 / 1
... 95 / 1

UL/CSA rated data

Voltage/current/conductor size	UL
Voltage/current/conductor size	CSA

1000 V/115 A/14...2 AWG
1000 V/150 A/14...2 AWG

1000 V/115 A/14...1/0 AWG
1000 V/200 A/14...1/0 AWG

1000 V/255 A/10...250 kcmil AWG
1000 V/320 A/10...250 kcmil AWG

1000 V/255 A/10...250 kcmil AWG
1000 V/320 A/10...250 kcmil AWG

Ordering data

Version

Dark beige Wemid

Type	Cat. No.	Qty.
WF 6	1780850000	25

Type	Cat. No.	Qty.
WF 8	1780860000	25

Type	Cat. No.	Qty.
WF 10	1780870000	20

Type	Cat. No.	Qty.
WF 12	1780880000	20

Partition / version



Dark beige Wemid ¹⁾
Epoxy resin ²⁾

Dimensions (width/length/ height)

Dark beige Wemid; length: 50 mm (for insul. cable lugs)

WTW WF 6	1781220000	20
WTW WF 6 2300	1781230000	20
2/101.8/58.5		
WTW WF 50	1781240000	20

WTW WF 8	1780900000	20
WTW WF 8 2300	1780910000	20
2/109.8/67		
WTW WF 50	1781240000	20

WTW WF10/12	1780890000	20
WTW WF10/12 2300	1780920000	20
2/156/76.5		
WTW WF 50	1781240000	20

WTW WF 10/1	1780890000	20
WTW WF 10/12 2300	1780920000	20
2/156/76.5		
WTW WF 50	1781240000	20

Cross-connection

2-pole
3-pole
Special 2-pole
Special 3-pole

WQL 2 WF 6	1780970000	5
WQL 3 WF 6	1780980000	5
WQL 2 WF 6-8	1809880000	5

WQL 2 WF 8	1780990000	5
WQL 3 WF 8	1781000000	5
WQL 2 WF 6-8	1809880000	5

WQL 2 WF 10	1781010000	5
WQL 3 WF 10	1781020000	5
WQL 2 WF 6-10	1806620000	5
WQL 3 WF 6-10/2	1806640000	5

WQL 2 WF 12	1781030000	5
WQL 3 WF 12	1781040000	5

Prof. material for cover

1000 mm

ADP WF 6/WF 8
1780930000 10

ADP WF 6/WF 8	
1780930000	10

ADP WF 10/WF12
1806640000 10

ADP WF 10/WF 12
1780940000 10

Support for Cover

Dark beige Wemid

HA WF	1781050000	50
-------	-------------------	----

HA WF	1781050000	50
-------	-------------------	----

HA WF	1781050000	50
-------	-------------------	----

HA WF	1781050000	50
-------	-------------------	----

to avoid lateral displacement
of cover

Marking tags



DEK



WS

DEK 5 Standard	DEK 5	see "Accessories"
WS 10/5 neutral	WS 10/5	1635000000 720
WS 12/5 neutral	WS 12/5	1609860000 720
WS 15/5 neutral	WS 15/5	1609880000 480
WS 10/6 neutral	WS 10/6	1060960000 200
DEK 6	DEK 6	see "Accessories"

DEK 5	see "Accessories"
WS 10/5	1635000000 720
WS 12/5	1609860000 720
WS 15/5	1609880000 480
WS 10/6	1060960000 200
DEK 6	see "Accessories"

DEK 5	see "Accessories"
WS 10/5	1635000000 720
WS 12/5	1609860000 720
WS 15/5	1609880000 480
WS 10/6	1060960000 200
DEK 6	see "Accessories"

DEK 5	see "Accessories"
WS 10/5	1635000000 720
WS 12/5	1609860000 720
WS 15/5	1609880000 480
WS 10/6	1060960000 200
DEK 6	see "Accessories"

Mounting rails, end brackets, further marking materials see "Accessories"

¹⁾ With WTW made from WEMID, nominal voltage 1000 V

²⁾ With WTW made from epoxy resin, nominal voltage 2.300 V acc. to prEN 50124-1

Stud terminals

WF 6/2 BZ



WF 8/2 BZ



WF 10/2 BZ



Dimensions			WF 6/2 BZ	WF 8/2 BZ	WF 10/2 BZ
Width/length/height with 	mm		19.6 / 67 / 56	24.6 / 67 / 65	35.6 / 67 / 74
Pitch with partition	mm		18	23	34
Stud size			M6	M8	M10
Rated data					
Rated voltage/current/cross-section ¹⁾			1000 V ¹⁾ / 125A / 35 mm ²	1000 V ¹⁾ / 150A / 50 mm ²	1000 V ¹⁾ / 269A / 120 mm ²
Rated impulse voltage/pollution severity ¹⁾			8 kV / 3	8 kV / 3	8 kV / 3
Further technical data					
Tightening torque range	Nm		3 ... 6	6 ... 12	10 ... 20
Clampable conductors					
DIN 46234 / number per side ¹⁾			...35 / 2	...50 / 2	... 95 / 2
DIN 46235 / number per side ¹⁾			...25 / 2	...35 / 2	...120 / 2 ⁵⁾
UL/CSA rated data					
Voltage/current/conductor size	UL		under preparation	under preparation	under preparation
Voltage/current/conductor size	CSA		under preparation	under preparation	under preparation
Ordering data		Version	Type	Cat. No.	Qty.
		Dark beige Wemid	WF 6/2 BZ	1789770000	25
Partition / Version			Type	Cat. No.	Qty.
		Dark beige Wemid ¹⁾	WTW WF10/12	1780890000	20
		Epoxy resin ²⁾			
		Dimensions (width/length/height)	2/156/76.5	2/156/76.5	2/156/76.5
		Dark beige Wemid; length: 50 mm (for insul. cable lugs)			
Cross-connection					
		Standard 2-pole	WQL 2 WF 6	1780970000	5
		Standard 3-pole	WQL 3 WF 6	1780980000	5
		Special 2-pole ³⁾			
		Special 2-pole ⁴⁾			
Prof. material for cover					
		1000 mm	ADP WF10/WF12	1780930000	10
Support for cover					
		Dark beige Wemid	HA WF	1781050000	50
		to avoid lateral displacement of cover			
Marking tags					
		DEK 5 FW/FS...	DEK 5	see "Accessories"	
		WS 10/5 neutral	WS 10/5	1635000000	720
		WS 12/5 neutral	WS 12/5	1609860000	720
		WS 15/5 neutral	WS 15/5	1609880000	480
Mounting rails, end brackets, further marking materials see "Accessories"					

¹⁾ With WTW made from WEMID, nominal voltage 1000 V


²⁾ With WTW made from epoxy resin, nominal voltage 2.300 V acc. to prEN 50124-1

³⁾ Only for cross-connection WF10/2BZ with WF6/2BZ

⁴⁾ Only for cross-connection WF10/2BZ with WF6/2BZ, if WF10/2BZ or WF6/2BZ are already cross-connected

⁵⁾ Only for cable lugs with a width of ≤ 31 mm


Stud terminals



WFF 35



Drill template for direct fitting
150 A/50 mm²



Max. technical data

Dimensions / approvals

Width/length/height (mm)	without WAH
Width/length/height (mm)	with WAH
Stud size	M

VDE rated data 0611 Part 1/8.92/IEC 60 947-7-1

Rated voltage/current/cross-section	
Rated impulse voltage/pollution severity	

Further technical data

Tightening torque range	Nm
-------------------------	----

Clampable conductors

Cable lug acc. to DIN 46 235	mm ²
Cable lug acc. to DIN 46 234	mm ²
2 x cable lug acc. to DIN 46 235	mm ²
2 x cable lug acc. to DIN 46 234	mm ²

Strips	mm
Strips	mm
Strips	mm

Max. connect. area in mm², gauge for flat conn. to EN 50043 Size

Cont. current of cross-connect. 2-pole A

Cont. current of cross-connect. 3-pole A

UL/CSA rated data

Voltage/current/conductor size UL

Voltage/current/conductor size CSA

Ordering data

Version

Dark beige Wemid
Blue Wemid

with covers

Dark beige Wemid
Dark beige Wemid

Partition (thickness 2 mm)



Cross-connection

WQL



Auxiliary/control conductor terminal

WZAF 35 (up to 4 mm², 32 A)



Cover



Beige PA 66
Blue PA 66
Light green PA 66

Danger sign



Yellow, self-adhesive,
with lightning flash,
can be stuck to WAH only

Fixing screw/Screwdriver



For direct fitting
Screwdriver

Cupal washers



For aluminium conductors

Marking tags



Print	
DEK Standard	DEK 5
WS white neutral	WS 12/6.5
WS indiv. printed	WS 12/6.5

Mounting rails, end brackets, further marking materials see "Accessories"

- ¹⁾ The WAP can be used only in conjunction with the WAH.
In the event that no conductor is connected, it guarantees shock protection in the connection.
²⁾ Screw locking e.g. with Loctite 243 for e.g. railway applications acc. to DIN EN 50 155/5.96

WFF 70



Drill template for direct fitting
232 A/95 mm²



Dimensions / approvals

Width/length/height (mm)	without WAH
Width/length/height (mm)	with WAH
Stud size	M

VDE rated data 0611 Part 1/8.92/IEC 60 947-7-1

Rated voltage/current/cross-section	
Rated impulse voltage/pollution severity	

Further technical data

Tightening torque range	Nm
-------------------------	----

Clampable conductors

Cable lug acc. to DIN 46 235	mm ²
Cable lug acc. to DIN 46 234	mm ²
2 x cable lug acc. to DIN 46 235	mm ²
2 x cable lug acc. to DIN 46 234	mm ²

Strips	mm
Strips	mm
Strips	mm

Max. connect. area in mm², gauge for flat conn. to EN 50043 Size

Cont. current of cross-connect. 2-pole A

Cont. current of cross-connect. 3-pole A

UL/CSA rated data

Voltage/current/conductor size UL

Voltage/current/conductor size CSA

Ordering data


Version

Dark beige Wemid
Blue Wemid

with covers


Dark beige Wemid

Partition (thickness 2 mm)




Cross-connection

WQL




Auxiliary/control conductor terminal

WZAF 70 (up to 4 mm², 32 A)




Cover




Beige PA 66
Blue PA 66
Light green PA 66

Danger sign



Yellow, self-adhesive,
with lightning flash,
can be stuck to WAH only

Fixing screw/Screwdriver



For direct fitting
Screwdriver

Cupal washers



For aluminium conductors

Marking tags



Print	
DEK Standard	DEK 5
WS white neutral	WS 12/6.5
WS indiv. printed	WS 12/6.5

Mounting rails, end brackets, further marking materials see "Accessories"


Note: If tension rods are used, individual terminals can be combined for protection. (available on request)

Stud terminals

WFF 120



Drill template for direct fitting
309 A/150 mm²



42/132/72	
42/230/81	
10	
1000 V/269 A/120 mm ²	
8 kV/3	
10...20	
16...150	
6...150	
16...120	
6...120	
2 x 20 x 1	
6 x 20 x 1	
5 x 24 x 1	
5.26...150	C 8
292	
292	

1000 V/310 A/10...250 kcmil AWG	
600 V/310 A/10...250 kcmil AWG	

	Cat. No.	Qty.
WFF 120	1028500000	5
WFF 120	1028580000	5

WFF 120	1029500000	5
---------	-------------------	---

Type	Cat. No.	Qty.
WTW WFF 120	1067300000	10

WQL 2/120	1065100000	5
WQL 3/120	1065600000	5

WZAF 120	1066300000	10
----------	-------------------	----

WAH 120	1064660000	20
WAH 120 BL	1064680000	20
WAH 120 HG	1064650000	20
WAP ¹⁾	1073000000	20

WD 1	1563900000	5
Qty. = 5 cards with 6 labels each		

M 6x16 ²⁾	1063700000	20
SDI	9008410000	1


CPSB M 10	0156400000	50
-----------	-------------------	----

DEK 5	see "Accessories"	
WS 12/6.5	1609920000	540
WS 12/6.5	1609930000	108

WFF 185 / WFF 185 M 12 + M 16



Drill template for direct fitting
415 A/240 mm²



55/163/78	
55/287/91	
12	
1000 V/353 A/185 mm ²	
8 kV/3	
14...31	
25...240	
10...240	
25...185	
10...185	
2 x 24 x 1	10 x 24 x 1
2 x 32 x 1	6 x 32 x 1
3 x 35 x 1	
8.37...240	C 11
382	
382	

1000 V/380 A/8...500 kcmil AWG	
600 V/360 A/8...500 kcmil AWG	

	Cat. No.	Qty.
WFF 185	1028600000	4
WFF 185	1028680000	4

WFF 185	1029600000	4
---------	-------------------	---

Type	Cat. No.	Qty.
WTW WFF 185	1067400000	10

WQL 2/185	1065200000	5
WQL 3/185	1065700000	5

WZAF 185	1066400000	10
----------	-------------------	----

WAH 185/300	1064760000	10
WAH 185/300 BL	1064780000	10
WAH 185/300 HG	1064750000	10


WD 1	1563900000	5
Qty. = 5 cards with 6 labels each		

M 6x16 ²⁾	1063700000	20
SDI	9008410000	1


CPSB M 12	0156500000	20
-----------	-------------------	----

DEK 5	see "Accessories"	
WS 12/6.5	1609920000	540
WS 12/6.5	1609930000	108

WFF 300



Drill template for direct fitting
520 A/300 mm²



55/163/86	
55/287/90	
16	
1000 V/520 A/300 mm ²	
8 kV/3	
25...60	
50...300	
25...240	
50...240	
25...240	
2 x 40 x 1	3 x 35 x 1
6 x 40 x 1	8 x 32 x 1
8 x 40 x 1	
13.3...300	-
520	
520	

1000 V/500 A/6...600 kcmil AWG	
600 V/510 A/6...600 kcmil AWG	

	Cat. No.	Qty.
WFF 300	1028700000	4
WFF 300	1028780000	4

WFF 300	1029700000	4
---------	-------------------	---

Type	Cat. No.	Qty.
WTW WFF 300	1067400000	10

WQL 2/300	1065300000	5
WQL 3/300	1065800000	5

WZAF 300	1066500000	10
----------	-------------------	----

WAH 185/300	1064760000	10
WAH 185/300 BL	1064780000	10
WAH 185/300 HG	1064750000	10

WD 1	1563900000	5
Qty. = 5 cards with 6 labels each		

M 6x16 ²⁾	1063700000	20
SDI	9008410000	1

CPSB M 16	0156500000	20
-----------	-------------------	----

DEK 5	see "Accessories"	
WS 12/6.5	1609920000	540
WS 12/6.5	1609930000	108

¹⁾ The WAP can be used only in conjunction with the WAH.
In the event that no conductor is connected, it guarantees shock protection in the connection.
²⁾ Screw locking e.g. with Loctite 243 for e.g. railway applications acc. to DIN EN 50 155/5.96

Note: If tension rods are used, individual terminals can be combined for protection. (available on request)

Standard design

WPE 2.5



Dimensions / approvals			
Width/length/height (mm)		with TS 35 x 7.5 	
Insulation stripping length/clamping screw/screwdriver blade			
Rated data acc. to VDE 0611 Part 3/IEC 60 947-7-2			
Rated voltage/current for PEN/cross-section			
Rated voltage/impulse voltage/pollution severity to adjacent terminal			
Further technical data			
Tightening torque range		Nm	
Torque setting with DMS 2 electric screwdriver			
Clampable conductors			
Solid H07V-U		mm ²	
Stranded H07V-R		mm ²	
Flexible H07V-K		mm ²	
Flexible H07V-K and ferrule acc. to DIN 46 228/1		mm ²	
Flexible H07V-K and ferrules with plastic insul. collar		mm ²	
AWG conductor		Nr.	
Max. clamping range in mm ² /Gauge pin acc. to 60 947-7-1		Size	
Ordering data		Green/yellow Wemid	
Support block⁽¹⁾			
Marking tags		Print	
		DEK	Standard
		WS White	neutral
		WS	individ. printed

WPE 2.5

                 		
5/60/47		
10 mm/M 2.5/3.5 x 0.6		
– V/– A/2.5 mm ²		
800 V/8 kV/3		
0.4...0.7		
1/1		
0.5...4		
1.5...4		
0.5...4		
0.5...2.5		
0.5...2.5 ³⁾		
26...12		
0.13...4		
Type	Cat. No.	A 3 Qty.
WPE 2.5	1010000000	100
SH 2	0494920000	10
DEK 5	see "Accessories"	
WS 12/5	1609860000	720
WS 12/5	1773380000	300

WPE 4



    		
6/60/47		
10 mm/M 3/3.5 x 0.6		
– V/– A/4 mm ²		
800 V/8 kV/3		
0.5...1.0/0.5...0.8 (for centre screw)		
2/2 (for centre screw)		
0.5...6		
1.5...6		
0.5...6		
0.5...4		
0.5...4		
26...10		
0.13...6		
Type	Cat. No.	Qty.
WPE 4	1010100000	100
SH 2	0494920000	10
DEK 6	see "Accessories"	
WS 8/5	1640740000	720
WS 8/5	1773360000	300

WPE 6



 		
8/60/47		
12 mm/M 3.5/4.0 x 0.8		
– V/– A/6 mm ²		
800 V/8 kV/3		
0.8...1.6/0.5...1.0 (for centre screw)		
3/2 (for centre screw)		
0.5...10		
1.5...6		
0.5...10		
0.5...6		
0.5...6		
26...8		
0.13...10		A 5
Type	Cat. No.	Qty.
WPE 6	1010200000	50
SH 2	0494920000	10
DEK 8	see "Accessories"	
WS 12/6.5	1609920000	540
WS 12/6.5	1609930000	108

Standard design

WPE 10



Dimensions / approvals			
Width/length/height (mm)	with TS 35 x 7.5 		
Insulation stripping length/clamping screw/screwdriver blade			
Rated data acc. to VDE 0611 Part 3/IEC 60 947-2			
Rated voltage/current for PEN/cross-section			
Rated voltage/impulse voltage/pollution severity to adjacent terminal			
Further technical data			
Tightening torque range	Nm		
Torque setting with DMS 2 electric screwdriver			
Clampable conductors			
Solid H07V-U	mm ²		
Stranded H07V-R	mm ²		
Flexible H07V-K	mm ²		
Flexible H07V-K and ferrule acc. to DIN 46 228/1	mm ²		
Flexible H07V-K and ferrules with plastic insul. collar	mm ²		
AWG conductor	Nr.		
Max. clamping range in mm ² /Gauge pin acc. to 60 947-7-1 Size			
Ordering data		Green/yellow Wemid	
		Green/yellow Wemid	
Support block¹⁾			
Bridge²⁾			
Marking tags		Print	
	DEK		WS
		DEK	WS
		WS White	neutral
		WS	individ. printed
Support rails, end brackets, further marking materials			


WPE 10

                 		
10/60/47		
12 mm/M 4/5.5 x 1.0		
– V/– A/10 mm ²		
800 V/8 kV/3		
1.2...2.4 / 0.5...1.0 (for centre screw)		
3/2 (for centre screw)		
1.5...16		
1.5...16 (16 mm with 2.4 Nm)		
1.5...16		
1.5...16		
1.5...16		
16...8		
1.31...16		B 6
Type	Cat. No.	Qty.
WPE 10	1010300000	50
Type	Cat. No.	Qty.
SH 2	0494920000	10
on the external side		
WQB-PEN10	1060300000	10
DEK 8	see "Accessories"	
WS 12/6.5	1609920000	540
WS 12/6.5	1609930000	108
"Accessories"		

WPE 16



    		
12/60/63		
16 mm/M 5/5.5 x 1.0		
– V/– A/16 mm ²		
800 V/8 kV/3		
2.0...4.0 / 1.2...2.4 (for centre screw)		
–/4 (for centre screw)		
1.5...16		
1.5...16		
1.5...16		
1.5...16		
14...6		
1.5...25		
Type	Cat. No.	Qty.
WPE 16	1010400000	50
Type	Cat. No.	Qty.
SH 2	0494920000	10
on the external side		
WQB-PEN16	1060200000	10
DEK 8	see "Accessories"	
WS 12/6.5	1609920000	540
WS 12/6.5	1609930000	108

WPE 35






16/60/70.5 (with  TS 35 x 15)

18 mm/M 6/6.5 x 1.2

– V/A/35 mm²

800 V/8 kV/3

2.5...5.0 / 1.2...2.4 (for centre screw)

–/4 (for centre screw)

2.5...16

2.5...50 (with 4 Nm)

2.5...50

2.5...50

2.5...50

12...2

2.5...35

B 9

Type

Cat. No.

Qty.

WPE 35

1010500000

25

for hexagonal socket

1012600000

25

Type

Cat. No.

Qty.

SH 2

0494920000

10

on the external side

WQB-PEN35

1060100000

10

DEK 8

see "Accessories"

WS 12/6.5

1609920000

540

WS 12/6.5

1609930000

108

- 1) For insul. arrangement of mount. rails in totally insul. installations
- 2) Insertable bridge in a TN C distribution network between N terminal (WDU blue) and PE terminal (WPE)
- 3) Ferrules with optimum diam. for terminals with 5 mm pitch: Cat. No. **1333100000**

Protective conductor terminals

Standard design

Dimensions / approvals	
Width/length/height (mm)	with TS 35 x 7.5
Insulation stripping length/clamping screw/screwdriver blade	
Rated data acc. to VDE 0611 Part 3/IEC 60 947-7-2	
Rated voltage/current for PEN/cross-section	
Rated voltage/impulse voltage/pollution severity to adjacent terminal	
Further technical data	
Tightening torque range	Nm
Torque setting with DMS 2 electric screwdriver	
Clampable conductors	
Solid H07V-U	mm ²
Stranded H07V-R	mm ²
Flexible H07V-K	mm ²
Flexible H07V-K and ferrule acc. to DIN 46 228/1	mm ²
Flexible H07V-K and ferrules with plastic insul. collar	mm ²
AWG conductor	Nr.
Max. clamping range in mm ² /Gauge pin acc. to 60 947-7-1 Size	
Ordering data	
Green/yellow Wemid	
Support block ¹⁾	
Marking tags	
	DEK
	WS
Print	
Standard	Standard
neutral	neutral
indiv. printed	indiv. printed

WPE 1.5/ZZ




   	5/60/47
7 mm/M 2.5/3.5 x 0.6	
– V/– A/1.5 mm ²	
690 V/8 kV/3	
0.4...0.6	
1/1	
0.5...2.5	
1.5...2.5	
0.5...1.5	
0.5...1.5	
0.5...1.5	
26...14	
0.08...2.5	
A 1	
Twin connection	
Type	Cat. No.
WPE 1.5 ZZ	1016500000
SH 2	0494920000
DEK 5	see "Accessories"
WS 12/5	1609860000
WS 12/5	1773380000

WPE 2.5/1.5/ZR



   	5/60/47
10/7 mm/M 2.5/3.5 x 0.6	
– V/– A/2.5 mm ²	
690 V/8 kV/3	
0.4...0.6	
1/1	
0.5...4	
1.5...4	
0.5...1.5	
0.5...2.5	
0.5...2.5 ³⁾	
26...12	
0.13...4	
A3	
Twin connection	
Type	Cat. No.
WPE 2.5/1.5 ZR	1016400000
SH 2	0494920000
DEK 5	see "Accessories"
WS 12/5	1609860000
WS 12/5	1773380000

WDK 2.5 PE WDK 2.5 DU-PE



 	5/69/63
10 mm/M 2.5/3.5 x 0.6	
– V/– A/2.5 mm ²	
400 V/6 kV/3	
0.4...0.6	
1/1	
0.5...4	
1.5...4	
0.5...4	
0.5...2.5	
0.5...2.5 ³⁾	
22...12	
0.13...4	
A 3	
Twin connection	
Type	Cat. No.
WDK 2.5 PE	1036300000
WDK 2.5 DU-PE	1036400000
SH 2	0494920000
DEK 5	see "Accessories"
WS 8/5	1640740000
WS 8/5	1773360000

Standard design

WPE 10 ZR



Dimensions / approvals	
Width/length/height (mm)	with TS 35 x 7.5
Insulation stripping length/clamping screw/screwdriver blade	
Rated data acc. to VDE 0611 Part 3/IEC 60 947-7-2	
Rated voltage/current for PEN/cross-section	
Rated voltage/impulse voltage/pollution severity to adjacent terminal	
Further technical data	
Tightening torque range	Nm
Torque setting with DMS 2 electric screwdriver	
Clampable conductors	
Solid H07V-U	mm ²
Stranded H07V-R	mm ²
Flexible H07V-K	mm ²
Flexible H07V-K and ferrule acc. to DIN 46 228/1	mm ²
Flexible H07V-K and ferrules with plastic insul. collar	mm ²
AWG conductor	Nr.
Max. clamping range in mm ² /Gauge pin acc. to 60 947-7-1 Size	
Ordering data	
Green/yellow Wemid	
Support block ¹⁾	
Bridge ²⁾	
Marking tags	
	DEK
	WS
Print	
Standard	Standard
neutral	neutral
indiv. printed	indiv. printed

WPE 70/95



  	27/132/115.5 (with TS 35 x 15)
30 mm/M 8/S 6 DIN 6911	
– V/– A/95 mm ²	
1000 V/8 kV/3	
6.0...12/3.0...6.0 (for centre screw)	
16	
16...120	
16...95	
35...95	
35...50	
6...2/0	
16...120	
B 12	
Twin connection	
Type	Cat. No.
WPE 70/95	1037300000
SH 2	0494920000
DEK 5	see "Accessories"
WS 12/6.5	1609920000
WS 12/6.5	1609930000

WPE 120



 	32/132/125.5 (with TS 35 x 15)
35 mm/M 10/S 6 DIN 6911	
– V/– A/120 mm ²	
1000 V/8 kV/3	
10...20/3.0...6.0 (for centre screw)	
–	
35...150	
35...150	
–	
–	
2...MCM 250	
35...150	
B 13	
Twin connection	
Type	Cat. No.
WPE 120	1019700000
SH 2	0494920000
DEK 5	see "Accessories"
WS 12/6.5	1609920000
WS 12/6.5	1609930000


¹⁾ For insul. arrangement of mount. rails in totally insul. installations
²⁾ Insertable bridge in a TN C distribution network between N terminal (WDU blue) and PE terminal (WPE)
³⁾ Ferrules with optimum diam. for terminals with 5 mm pitch: Cat. No. 1333100000

⁴⁾ TS 35x15 Cu,
Cat. No. 0270100000

Protective conductor terminals

Compact design “N” for low type

WPE 2.5N



WPE 4N



Dimensions / approvals			
Width/length/height (mm)		with TS 35 x 7.5	
Insulation stripping length/clamping screw/screwdriver blade			
Rated data acc. to VDE 0611 Part 3/IEC 60 947-7-2			
Rated voltage/current for PEN/cross-section			
Rated voltage/impulse voltage/pollution severity to adjacent terminal			
Further technical data			
Tightening torque range		Nm	
Torque setting with DMS 2 electric screwdriver			
Clampable conductors			
Solid H07V-U		mm ²	
Stranded H07V-R		mm ²	
Flexible H07V-K		mm ²	
Flexible H07V-K and ferrule acc. to DIN 46 228/1		mm ²	
Flexible H07V-K and ferrules with plastic insul. collar		mm ²	
AWG conductor		Nr.	
Max. clamping range in mm ² /Gauge pin acc. to 60 947-7-1		Size	
Ordering data			
		Green/yellow Wemid	
Support block ¹⁾			
Marking tags		Print	
	DEK		WS
		DEK	Standard
		WS White	neutral
		WS	indiv. printed

        			
5/54/37.5			
10 mm/M 2.5/3.5 x 0.6			
– V/– A/2.5 mm ²			
500 V/6 kV/3			
0.4...0.6			
1/1			
0.5...4			
1.5...4			
0.5...4			
0.5...2.5			
0.5...2.5 ³⁾			
26...12			
0.13...4			
		A 3	
Type	Cat. No.	Qty.	
WPE 2.5N	1016200000	100	
SH 2	0494920000	10	
DEK 5	see "Accessories"		
WS 12/5	1609860000	720	
WS 12/5	1773380000	300	

Type	Cat. No.	Qty.	
WPE 4N	1042700000	100	
SH 2	0494920000	10	
DEK 6	see "Accessories"		
WS 12/6	1609900000	720	
WS 12/6	1609910000	30	

Compact design “N” for low type

WPE 16N



WPE 35N



WPE 70N



Dimensions / approvals			
Width/length/height (mm)		with TS 35 x 7.5	
Insulation stripping length/clamping screw/screwdriver blade			
Rated data acc. to VDE 0611 Part 3/IEC 60 947-7-2			
Rated voltage/current for PEN/cross-section			
Rated voltage/impulse voltage/pollution severity to adjacent terminal			
Further technical data			
Tightening torque range		Nm	
Torque setting with DMS 2 electric screwdriver			
Clampable conductors			
Solid H07V-U		mm ²	
Stranded H07V-R		mm ²	
Flexible H07V-K		mm ²	
Flexible H07V-K and ferrule acc. to DIN 46 228/1		mm ²	
Flexible H07V-K and ferrules with plastic insul. collar		mm ²	
AWG conductor		Nr.	
Max. clamping range in mm ² /Gauge pin acc. to 60 947-7-1		Size	
Ordering data			
		Green/yellow Wemid	
Support block ¹⁾			
Bridge ²⁾			
Marking tags		Print	
	DEK	DEK	Standard
	WS	WS White	neutral
		WS	indiv. printed
Mounting rails, end brackets, further marking materials			



12/60/47		
12 mm/M 4/5.5 x 1.0		
– V/– A/16 mm ²		
400 V/6 kV/3		
1.2...2.0/0.5...1.0 (for centre screw)		
–/2 (for centre screw)		
4...16		
4...25 (25 mm ² for 2.2 Nm)		
4...16		
4...16		
4...16		
14...6		
1.5...2		
Type	Cat. No.	Qty.
WPE 16N	1019100000 ³⁾	50
SH 2	0494920000	10
Bridge on internal side		
WQV 16N-PEN	1071360000 ⁴⁾	10
DEK 8	see "Accessories"	
WS 12/6.5	1609920000	540
WS 12/6.5	1609930000	108

"Accessories"

Type	Cat. No.	Qty.	
WPE 35N	1717740000 ⁵⁾	20	
SH 2	0494920000	10	
Bridge on the external side			
WQB-PEN35N	1079500000	10	
DEK 8	see "Accessories"		
WS 12/6.5	1609920000	540	
WS 12/6.5	1609930000	108	

 		
20.5/75/93.5 (with  TS 35 x 15) ³⁾		
22 mm/M 8/S 6 DIN 6911		
– V/– A/70 mm ²		
1000 V/8 kV/3		
6.0...10/2.0...4.0 (for centre screw)		
10...16		
10...95		
10...70		
10...70		
10...70		
8...2/0		
10...95		
		B 11
Type	Cat. No.	Qty.
WPE 70N	9512200000 ⁵⁾	10
SH 2	0494920000	10
Bridge on internal side		
WQV 70N-PEN	9525840000	5
DEK 8	see "Accessories"	
WS 12/6.5	1609920000	540
WS 12/6.5	1609930000	108

¹⁾ For insul. arrangement of mount. rails in totally insul. installations

²⁾ Insertable bridge in a TN C distribution network between N terminal (WDU blue) and PE terminal (WPE)

³⁾ WPE 35 and WPE 70N for TS 35 x 15 Cu Cat. No. 0270100000

⁴⁾ For preparing PEN bridges and using WQV 16 N, route the N conductor-in-feed between PE and phase.

⁵⁾ Ferrules with optimum diam. for terminals with 5 mm pitch: Cat. No. 1333100000

Protective conductor terminals

Compact design “N” for low type

Dimensions / approvals

Width/length/height (mm) with TS 35 x 7.5

Insulation stripping length/clamping screw/screwdriver blade

Rated data acc. to VDE 0611 Part 3/IEC 60 947-7-2

Rated voltage/current for PEN/cross-section

Rated voltage/impulse voltage/pollution severity to adjacent terminal

Further technical data

Tightening torque range Nm

Torque setting with DMS 2 electric screwdriver

Clampable conductors

Solid H07V-U mm²

Stranded H07V-R mm²

Flexible H07V-K mm²

Flexible H07V-K and ferrule acc. to DIN 46 228/1 mm²

Flexible H07V-K and ferrules with plastic insul. collar mm²

AWG conductor Nr.

Max. clamping range in mm²/Gauge pin acc. to 60 947-7-1 Size

Ordering data

Green/yellow Wemid

Support block¹⁾

Marking tags



DEK



WS


Print

DEK Standard

WS White neutral

WS indiv. printed

WDK 2.5N PE



UL CUL LR DNV

5/60/62

8 mm/M 2.5/3.5 x 0.6

– V/– A/2.5 mm²

800 V/8 kV/3

0.4...0.6

1

0.5...4

1.5...4

0.5...4

0.5...2.5

0.5...2.5²⁾

22...12

0.13...4

A 3

Type	Cat. No.	Qty.
WDK 2.5N PE	1041620000	100

SH 2	0494920000	10
------	------------	----

DEK 5	see "Accessories"
-------	-------------------

WS 8/5	1640740000	720
--------	------------	-----

WS 8/5	1773360000	300
--------	------------	-----

WDK 2.5N DU-PE



UL CUL LR DNV

5/60/62

8 mm/M 2.5/3.5 x 0.6

– V/– A/2.5 mm²

800 V/8 kV/3

0.4...0.6

1

0.5...4

1.5...4

0.5...4

0.5...2.5

0.5...2.5²⁾

22...12

0.13...4

A 3

Type	Cat. No.	Qty.
WDK 2.5N DU-PE	1041650000	100

SH 2	0494920000	10
------	------------	----

DEK 5	see "Accessories"
-------	-------------------

WS 8/5	1640740000	720
--------	------------	-----

WS 8/5	1773360000	300
--------	------------	-----

Compact design “N” for low type

Dimensions / approvals

Width/length/height (mm) with TS 35 x 7.5

Insulation stripping length/clamping screw/screwdriver blade

Rated data acc. to VDE 0611 Part 3/IEC 60 947-7-2

Rated voltage/current for PEN/cross-section

Rated voltage/impulse voltage/pollution severity to adjacent terminal

Further technical data

Tightening torque range Nm

Torque setting with DMS 2 electric screwdriver

Clampable conductors

Solid H07V-U mm²

Stranded H07V-R mm²

Flexible H07V-K mm²

Flexible H07V-K and ferrule acc. to DIN 46 228/1 mm²

Flexible H07V-K and ferrules with plastic insul. collar mm²

AWG conductor Nr.

Max. clamping range in mm²/Gauge pin acc. to 60 947-7-1 Size

Ordering data

Green/yellow Wemid

Support block¹⁾

Marking tags



DEK



WS


Print

DEK Standard

WS White neutral

WS indiv. printed

WDK 4N PE



UL CUL LR DNV

5/60/64

8 mm/M 3/3.5 x 0.6

– V/– A/4 mm²

800 V/8 kV/3

0.5...1.0

2

0.5...6

1.5...6

0.5...4

1.5...4

1.5...4

26...10

0.13...6

A3

Type	Cat. No.	Qty.
WDK 4N PE	1041920000	100


SH 2	0494920000	10
------	------------	----

DEK 5	see "Accessories"
-------	-------------------

WS 8/5	1640740000	720
--------	------------	-----

WS 8/5	1773360000	300
--------	------------	-----

WDK 4N DU-PE



UL CUL LR DNV

5/60/64

8 mm/M 3/3.5 x 0.6

– V/– A/4 mm²

800 V/8 kV/3

0.5...1.0

2

0.5...6

1.5...6

0.5...4

0.5...4

0.5...4

26...10

0.13...6

A 3

Type	Cat. No.	Qty.
WDK 4N DU-PE	1041950000	100

SH 2	0494920000	10
------	------------	----

DEK 5	see "Accessories"
-------	-------------------

WS 8/5	1640740000	720
--------	------------	-----

WS 8/5	1773360000	300
--------	------------	-----


Mounting rails, end brackets, further marking materials see "Accessories"

¹⁾ For insul. arrangement of mount. rails in totally insul. installations

²⁾ Ferrules with optimum diam. for terminals with 5 mm pitch: Cat. No. 1333100000


Neutral disconnect terminals

WNT 16N




- / -

WNT 35N



- / -

WNT 70N



207 A/95 mm²

Max. technical data

Dimensions / approvals

Width/length/height (mm) with TS 35 x 7.5

Insulation stripping length/clamping screw/screwdriver blade

VDE rated data 0611 Part 5

Rated voltage/current/cross-section

Rated voltage/impulse voltage/pollution severity

Further technical data

Tightening torque range clamping screw / N disconnect Nm

Torque setting with DMS 2 electric screwdriver

Clampable conductors

Solid H07V-U mm²

Stranded H07V-R mm²

Flexible H07V-K mm²

Flexible H07V-K and ferrule acc. to DIN 46 228/1 mm²

Flexible H07V-K and ferrules with plastic insul. collar mm²

Max. clamping range in mm²/Gauge pin acc. to 60 947-7-1 Size

UL/CSA rated data

Voltage/current/conductor size UL

Voltage/current/conductor size CSA

Ordering data

For busbar 10 x 3

Blue Wemid

Support plate



for SSch 10 x 3 Blue Wemid

Dark beige Wemid

Thickness 1.5 mm

Distance WHP-WHP max. 200mm


Busbar 10 x 3



Cu 140 A

Distance f. upper edge busbar to upper edge of TS 35 = 25.5 mm

Clamping yoke



Supply for SSch 10 x 3
16...50 mm² stranded

ZB 35 K

ZB 35

Test plug



End bracket

Bridge on the external side

Cross-section of connection is reduced by one level

Marking tags



DEK



WS

DEK Standard

WS White neutral

WS indiv. printed

12/60/47

12 mm/M 4/5.5 x 1.0

400 V/76 A/16 mm²

400 V/6 kV/3

1.2...2.2 / 0.8...1.6

4

1.5...16

1.5...25 (25 mm² with 2.4 Nm)

1.5...16

1.5...16

1.5...16

1.5...25

16/66/51

18mm/M 6/5.5 x 1.0

400 V/125 A/35 mm²

400 V/6 kV/3

2.5...5 / 1.2...2.4

-

2.5...16

2.5...50

2.5...35

2.5...35

2.5...35

2.5...35

20.5/75/86

22 mm/M 8/S 6 DIN 6911

400 V/192 A/70 mm²

400 V/6 kV/3

6.0...10 / 2.5...5

-

10...16

10...95

10...70

10...70

10...70

10...95

Type	Cat. No.	Qty.
WNT 16N	1019000000	50

WHP 2.5-10	1050280000	20
WHP 2.5-10	1050200000	20

SSch 10 x 3 Cu 0348900000 1 m

ZB 35 K	0502680000	20
ZB 35	0266500000	20

PS 2.3 0180400000 20

WEW 35 / 2 1061200000 50

WQB-PEN 16N 1079600000 10

DEK 5	see "Accessories"
WS 12/6.5	1609920000 540
WS 12/6.5	1609930000 108

Type	Cat. No.	Qty.
WNT 35N	1718550000	20

WHP 2.5-10	1050280000	20
WHP 2.5-10	1050200000	20

SSch 10 x 3 Cu 0348900000 1 m

ZB 35 K	0502680000	20
ZB 35	0266500000	20

PS 2.3 0180400000 20

WEW 35 / 2 1061200000 50

WQB-PEN 35N 1079500000 10

DEK 5	see "Accessories"
WS 12/6.5	1609920000 540
WS 12/6.5	1609930000 108

Type	Cat. No.	Qty.
WNT 70N	9512210000	10

WHP 2.5-10	1050280000	20
WHP 2.5-10	1050200000	20

SSch 10 x 3 Cu 0348900000 1 m

ZB 35 K	0502680000	20
ZB 35	0266500000	20

PS 4 0299600000 20


WEW 35 / 2 1061200000 50

WQB-PEN 70N 1079700000 10

DEK 5	see "Accessories"
WS 12/6.5	1609920000 540
WS 12/6.5	1609930000 108

Mounting rails, end brackets, further marking materials see "Accessories"


TN-S-Circuit




Disconnect test terminals



WTR 2.5 D with diode plug



WTR 2.5 D with StB with diode plug and test socket screw 2.3



WTR 4



Max. technical data

Dimensions / approvals
Width/length/height (mm) with TS 35 x 7.5

Insulation stripping length/clamping screw/screwdriver blade

Rated data

Rated voltage/current/cross-section

Rated impulse voltage acc. to VDE 0110/pollution severity

Further technical data

Tightening torque range Nm

Torque setting with DMS 2 electric screwdriver

Clampable conductors

Solid H07V-U mm²

Stranded H07V-R mm²

Flexible H07V-K mm²

Flexible H07V-K and ferrule acc. to DIN 46 228/1 mm²

Flexible H07V-K and ferrules with plastic insul. collar mm²

Max. clamping range in mm²/Gauge pin acc. to 60 947-7-1 Size

Cont. current of cross-connect. multi-pole A

UL/CSA rated data

Voltage/current/conductor size UL

Voltage/current/conductor size CSA

Ordering data

Version	
Dark beige Wemid	
Dark beige Wemid	
Blue Wemid	
Blue Wemid	
Dark beige Wemid	
Orange PA	

End plate/partition

WAP	WAP (thickness 1.5 mm)
	Dark beige Wemid
	Blue Wemid
	WTW Dark beige Wemid

Cross-connection / test plug

QL 2-10	
PS	
Cross-connection plug (2-pole, ø 2.3) QVB	
Screening bar LS 2.8	

Notching tool for cross-connections

To notch the punch-out in the terminal support

Screwdriver

SDIZ	
------	--

Fuse holder

SIHA 1/G 20	for 5x20 SIHA	
WTR 2.5 D	400 V AD/DC	
	10-36 V AD/DC	
	35-70 V AD/DC	
SIHA 2/G 20	60-150 V AD/DC	
WTR 4	140-250 V AD/DC	

Diode plug ³⁾

	(up to 250 V)
	+ -
	- +
	With wire link
	Without special components

Marking tags

DEK	Standard
WS White	neutral
WS	indiv. printed

Mounting rails, end brackets, further marking materials see "Accessories"

14 A/2.5 mm²

5/60/49 + 18 for WSD
10 mm/M 2.5/3.5 x 0.6

500 V³⁾/14 A⁴⁾/2.5 mm²
6 kV/3

0.4...0.6

1

0.5...4

1.5...4

0.5...4

0.5...2.5

0.5...2.5¹⁾

0.13...4 A 3

26

300 V/10 A/22...12 AWG

300 V/10 A/26...12 AWG

Type	Cat. No.	Qty.
+	1013500000	25
+	1013600000	25
With wire link	1013700000	25

Type	Cat. No.	Qty.
WAP 2.5-10	1050000000	50
WAP 2.5-10 BL	1050080000	50
WTW 2.5-10	1050100000	20

QL 2	0215800000	100
QL 3	0215900000	100
QL 4	0216000000	50
QL 10	0338000000	20
BS-M 2.5x4.5	1062700000	100
PS 2.3(ø 2.3)	0180400000	20
PS 2.0(ø 2.0)	0293800000	20

LS 2.8 1056400000 50

WQB B/24 1579060000 20

WAW 2 9004510000 1

SDIZ 9008450000 1

without LED	with LED	Qty.
9537550000		25
	9537560000	25
	9537570000	25
	9537580000	25
	9537590000	25

WSD 2.5	1058460000	25
WSD 2.5	1058560000	25
WSD 2.5	1058660000	25
WSD 2.5	1058760000	25

DEK 5	see "Accessories"
WS 12/5	1609860000 720
WS 12/5	1773380000 300

14 A/2.5 mm²

5/60/49 + 18 for WSD
10 mm/M 3/3.5 x 0.6

800 V³⁾/14 A⁴⁾/2.5 mm²
6 kV/3

0.4...0.6 / 0.5...0.6 (for test socket)

2

0.5...4

1.5...4

0.5...4

0.5...2.5

0.5...2.5¹⁾

0.13...4 A 3

26

300 V/10 A/22...12 AWG

300 V/10 A/26...12 AWG

Type	Cat. No.	Qty.
+	1013200000	25
+	1013300000	25
With wire link	1013400000	25

Type	Cat. No.	Qty.
WAP 2.5-10	1050000000	50
WAP 2.5-10 BL	1050080000	50
WTW 2.5-10	1050100000	20

QL 2	0215800000	100
QL 3	0215900000	100
QL 4	0216000000	50
QL 10	0338000000	20
BS-M 2.5x4.5	1062700000	100
PS 2.3(ø 2.3)	0180400000	20
PS 2.0(ø 2.0)	0293800000	20

LS 2.8 1056400000 50

WQB B/24 1579060000 20

WAW 2 9004510000 1

SDIZ 9008450000 1

without LED	with LED	Qty.
9537550000		25
	9537560000	25
	9537570000	25
	9537580000	25
	9537590000	25

WSD 2.5	1058460000	25
WSD 2.5	1058560000	25
WSD 2.5	1058660000	25
WSD 2.5	1058760000	25

DEK 5	see "Accessories"
WS 12/5	1609860000 720
WS 12/5	1773380000 300

32 A/4 mm²

6/60/47
13 mm/M 3/3.5 x 0.6

400 V/32 A⁴⁾/4 mm²
6 kV/3

0.5...1.0 / 0.5...0.6 (for test socket)

2

0.5...6

1.5...6

0.5...4

0.5...4

0.5...4

1...6 A 4

32

300 V¹⁾/10 A¹⁾/22...12 AWG

300 V¹⁾/10 A¹⁾/22...10 AWG

Type	Cat. No.	Qty.
with StB	7910210000	50
without StB	7910180000	50
with StB	7910220000	50
without StB	7910190000	50

Type	Cat. No.	Qty.
WAP 2.5-10	1050000000	50
WAP 2.5-10 BL	1050080000	50
WTW 2.5-10	1050100000	20

ZQV 4N/2	1758250000	60
ZQV 4N/3	1762630000	60
ZQV 4N/4	1762620000	60
ZQV 4N/10	1758260000	20
ZQV 4N/41	1758270000	10
QB75/6.2/15	0535200000	10
ISPFQB75 SW	0526700000	10
ISPF QB75 BL	0526780000	10
ISPFQB75 RT	0526760000	10
PS 2.3(ø 2.3)	0180400000	20

SDIZ	9008450000	1
------	------------	---

without LED	with LED	Qty.
9537600000		25
	9537610000	25
	9537620000	25
	9537630000	25
	9537640000	25

DEK 6	see "Accessories"
WS 12/6	1609900000 600
WS 12/6	1609910000 120

¹⁾ Ferrules with optimum diam. for terminals with 5 mm pitch: Cat. No. 1333100000

²⁾ As disconnect test terminal 500 V

³⁾ Apply only 250 V to the diode

⁴⁾ Rated current is limited to 1 A, if a diode plug with soldered diode is used

Disconnect test terminals

WDT 1.5/1
with space-saving TOP
connection



WDT 1.5/2
with space-saving TOP
connection



WDT 1.5/3
with space-saving TOP
connection



Dimensions / approvals

Width/length/height (mm) with TS 35 x 7.5

Insulation stripping length/clamping screw/screwdriver blade

Rated data

Rated voltage/current/cross-section

Rated impulse voltage acc. to VDE 0110/1.89 /pollution severity

Further technical data

Tightening torque range

Nm

Torque setting with DMS 2 electric screwdriver

Clampable conductors

Solid H07V-U

mm²

Stranded H07V-R

mm²

Flexible H07V-K

mm²

Flexible H07V-K and ferrule acc. to DIN 46 228/1

mm²

Flexible H07V-K and ferrules with plastic insul. collar

mm²

Max. clamping range in mm²/Gauge pin acc. to 60 947-1

Size

Cont. current of cross-connect. 2-pole

A

Cont. current of cross-connect. multi-pole

A

UL/CSA rated data

Voltage/current/conductor size

UL

Voltage/current/conductor size

CSA

Ordering data

Version

Dark beige/yellow Wemid

Beige/yellow PA

Blue/light blue PA

Test plug



PS



6.5/112/67

10 mm/M 2.5/3.5 x 0.6

250 V/10 A/1.5 mm²

4 kV/3

0.4...0.6

1

0.5...2.5

1.5...2.5

0.5...1.5

0.5...1.5

0.5...1.5

0.13...2.5 A 2

150 V/10 A/26...14 AWG

150 V/10 A/26...14 AWG

Cat. No. Qty.

1015800000 25

1015860000 25

Type Cat. No. Qty.

PS 2.3 0180400000 20



6.5/112/67

10 mm/M 2.5/3.5 x 0.6

250 V/10 A/1.5 mm²

4 kV/3

0.4...0.6

1

0.5...2.5

1.5...2.5

0.5...1.5

0.5...1.5

0.5...1.5

0.13...2.5 A 2

150 V/10 A/26...14 AWG

150 V/10 A/26...14 AWG

Cat. No. Qty.

1015900000 25

1015560000 25

Type Cat. No. Qty.

PS 2.3 0180400000 20



6.5/112/67

10 mm/M 2.5/3.5 x 0.6

250 V/10 A/1.5 mm²

4 kV/3

0.4...0.6

1

0.5...2.5

1.5...2.5

0.5...1.5

0.5...1.5

0.5...1.5

0.13...2.5 A 2

150 V/10 A/26...14 AWG

150 V/10 A/26...14 AWG

Cat. No. Qty.

1016000000 25

1015760000 25

1016160000 25

Type Cat. No. Qty.

PS 2.3 0180400000 20

Switching examples

WDT 1.5/...



Disconnect test terminals

W-series



The WDT 1.5 enables the disconnection of one- and two-pole signal lines. By simply operating the selection switch, insulation and current measurements can be performed.

- Quick and reliable conductor connection thanks to TOP connection with open clamping unit
- Test point via test socket screw
- Clear colour coding of conductor connection, test point and switch position
- Non-symmetrical shape enhances mounting rail orientation
- High distortion stiffness thanks to dual-shell enclosed terminal carrier



WDT 1.5/1
with space-saving TOP
connection



WDT 1.5/2
with space-saving TOP
connection



WDT 1.5/3
with space-saving TOP
connection



Marking tags



DEK



WS

Print

DEK Standard

WS White neutral

WS indiv. printed

DEK 6.5 see

"Accessories"

WS 8/5 1640740000 720

WS 8/5 1773360000 300

DEK 6.5 see

"Accessories"

WS 8/5 1640740000 720

WS 8/5 1773360000 300

DEK 6.5 see

"Accessories"

WS 8/5 1640740000 720

WS 8/5 1773360000 300

Mounting rails, end brackets, further marking materials see "Accessories"

Fuse terminals

Note:

With blown fuse the follow-on circuit is still under current. Disconnect lever to open circuit.

Max. technical data

Dimensions/approvals

Width/length/height (mm) with TS 35 x 7.5

Insulation stripping length/clamping screw/screwdriver blade

Rated data of terminal base

Rated voltage/current/cross-section

Rated impulse voltage acc. to VDE 0110/1.89 /pollution severity

Further technical data

Tightening torque range Nm

Torque setting with DMS 2 electric screwdriver

Clampable conductors

Solid H07V-U mm²

Stranded H07V-R mm²

Flexible H07V-K mm²

Flexible H07V-K and ferrule acc. to DIN 46 228/1 mm²

Flexible H07V-K and ferrules with plastic insul. collar mm²

Max. clamping range in mm²/Gauge pin acc. to 947-1 Size

Cont. current of cross-connect. 2-pole A

Cont. current of cross-connect. multi-pole A

UL/CSA rated data

Voltage/current/conductor size UL

Voltage/current/conductor size CSA

Ordering data

Version	
Dark beige Wemid	
Dark beige Wemid/LED	
Dark beige Wemid/LED	
Dark beige Wemid/LED	
Dark beige Wemid/LED	

Partition/End plate

WAP	WTW
Thickness 1.5 mm	Thickness 1.5 mm

Cross-connection



Notching tool for QL WAW 2

G fuse inserts 5 x 20 mm

Acc. to IEC 60127-2 (VDE 0820 T.2 BI²) Rat. current (A):0.10 fast

Rated voltage 250 V 0.20 fast

Rated switch-off capacity 1500 A 0.25 fast

(at 250 V, 50 Hz, cos φ = 0.7) 0.50 fast

1.0 fast

1.6 fast

2.0 fast

2.5 fast

3.15 fast

4.0 fast

5.0 fast

6.3 fast

Marking tags

Print	
DEK Standard	DEK 5
WS White neutral	WS 12/6.5
WS indiv. printed	WS 12/6.5

Mounting rails, end brackets, further marking materials see "Accessories"

¹⁾ Pay attention to the power loss of the fuse insert up to 1.6 W

²⁾ Maximum power loss 1.6 W

WTR 2.5/SI with fuse holder for G fuse inserts 5x20



6.3 A¹⁾/-

5/60/83

10 mm/M 2.5/3.5 x 0.6

400 V/6.3 A²⁾/2.5 mm²

6 kV/3

0.4...0.8

1/2

0.5...4

1.5...4

0.5...4

0.5...2.5

0.5...2.5³⁾

0.13...4 A 3

26

400 V/10 A/22...10 AWG⁵⁾

400 V

10-36 V UL: 36 V/10 A/22...10 AWG

35-70 V UL: 70 V/10 A/22...10 AWG

60-150 V UL: 150 V/10 A/22...10 AWG

140-250 V UL: 250 V/10 A/22...10 AWG

Type Cat. No. Qty.

WAP 2.5-10 1050000000 50

WAP2.5-10BL 1050080000 50

WTW 2.5-10 1050100000 20

QL 2 0215800000 100

QL 3 0215900000 100

QL 4 0216000000 50

QL 10 0338000000 20

BS-M 2.5x4.5 1052100000 100

WQB B 24 1579060000 20

WAW 2 9004510000 1

0430300000 10

0430400000 10

0430500000 10

0430600000 10

0430700000 10

0430800000 10

0430900000 10

0431000000 10

0431100000 10

0431200000 10

0431300000 10

0431400000 10

WTR 4/SI



6.3 A¹⁾/-

6/60/82

13 mm/M 3/3.5 x 0.6

400 V/6.3 A²⁾/4 mm²

6 kV/3

0.5...1.0

2

0.5...6

1.5...6

0.5...4

0.5...4

0.13...6 A 4

32

300 V/6.3 A/22...10 AWG⁴⁾

300 V/6.3 A/22...10 AWG⁴⁾

WTR 4 SI 7910240000 25

10-36 V CSA: 36 V/6.3 A/22...10 AWG 7914370000 25

35-70 V CSA: 70 V/6.3 A/22...10 AWG 7914380000 25

60-150 V CSA: 150 V/6.3 A/22...10 AWG 7914390000 25

140-250 V CSA: 250 V/6.3 A/22...10 AWG 7914400000 25

Type Cat. No. Qty.

WAP 2.5-10 1050000000 50

WAP2.5-10BL 1050080000 50

WTW 2.5-10 1050100000 20

ZQV 4N/2 1758250000 60

ZQV 4N/3 1762630000 60

ZQV 4N/4 1762620000 60

ZQV 4N/10 1758260000 60

ZQV 4N/41 1758270000 60

QB75/6.2/15 0535200000 20

ISPF QB75 SW 0526700000 20

ISPF QB75 BL 0526780000 20

ISPF QB75 RT 0526760000 20

0430300000 10

0430400000 10

0430500000 10

0430600000 10

0430700000 10

0430800000 10

0430900000 10

0431000000 10

0431100000 10

0431200000 10

0431300000 10

0431400000 10

0430300000 10

0430400000 10

0430500000 10

0430600000 10

0430700000 10

0430800000 10

0430900000 10

0431000000 10

0431100000 10

0431200000 10

0431300000 10

0431400000 10

DEK 6 see "Accessories"

WS 12/6 1609900000 600

WS 12/6 1609910000 120

⁴⁾ WTR 4 SI

⁵⁾ WTR 2.5 SI

Fuse terminals

Note:
With blown fuse the follow-on circuit is still under current. Disconnect lever to open circuit..

Max. technical data

Dimensions/approvals

Width/length/height (mm) with TS 35 x 7.5

Insulation stripping length/clamping screw/screwdriver blade

Rated data of terminal base

Rated voltage/current/cross-section

Rated impulse voltage acc. to VDE 0110/1.89 /pollution severity

Further technical data

Tightening torque range Nm

Torque setting with DMS 2 electric screwdriver

Clampable conductors

Solid H07V-U mm²

Stranded H07V-R mm²

Flexible H07V-K mm²

Flexible H07V-K and ferrule acc. to DIN 46 228/1 mm²

Flexible H07V-K and ferrules with plastic insul. collar mm²

Max. clamping range in mm²/Gauge pin acc. to 947-1 Size

Cont. current of cross-connect. 2-pole A

Cont. current of cross-connect. multi-pole A

UL/CSA rated data

Voltage/current/conductor size UL

Voltage/current/conductor size CSA

Ordering data

Version

Dark beige Wemid

Dark beige Wemid/LED

Dark beige Wemid/LED

Dark beige Wemid/LED

Partition/End plate

WTW

Thickness 1.5 mm

Cross-connection

QL 2-10



SAKS 2/35

for D fuses **E 16**



28/80/75

12 mm/M 4/5.5 x 1

500 V/10 (25) A[§]/10 mm²

6 kV/3

1.2...2.4

4

0.5...16

0.5...10

0.5...10

0.5...10

0.33...16

B 6

(QL 2...5) 47

(QL 6...10) 36

600 V/25 A/22...8 AWG

Dark beige Wemid KrG

1368700000 20

Diazed E 16

Type Cat. No. Qty.

WTW **1058800000** 20

QL 2 **0207800000** 20

QL 3 **0207900000** 20

QL 4 **0208000000** 20

QL 10 **0338900000** 20

BS M 4x9 **0103300000** 100

SS M 4 **0136400000** 100

D fuse inserts

Rated voltage 500 V

E 10 A **0208500000** 25

E 16 A **0208600000** 25

E 20 A **0208700000** 25

E 25 A **0208800000** 25

Gauge rings

P 16/10 **0208900000** 100

P 16/16 **0209000000** 100

P 16/20 **0209100000** 100

Screw cap (spare)

SK **0284110000** 20

Marking tags



DEK Standard

WS White neutral

WS indiv. printed

Print

DEK 5 see "Accessories"

WS 12/6.5 **1609920000** 540

WS 12/6.5 **1609930000** 108

SAKS 4/35

for D 01 fuses **E 14**



24/75/66

14 mm/M 4/5.5 x 1

400 V[§]/16 A/10 mm²

6 kV/3

1.2...2.4

4

0.5...16

1.5...10

0.5...10

0.5...10

0.33...16

B 6

(QL 2...5) 47

(QL 6...10) 36

600 V/30 A/22...8 AWG

Dark beige Wemid KrG

0501800000 20

Neozed D 01

Type Cat. No. Qty.

WTW **1058800000** 20

QL 2 **0328000000** 20

QL 3 **0328100000** 20

QL 4 **0328200000** 20

QL 10 **0339000000** 20

BS M 4x9 **0103300000** 100

SS M 4 **0136400000** 100

D 01 fuse inserts

Rated voltage 400 V

E 14/2 **0137400000** 10

E 14/4 **0137500000** 10

E 14/6 **0328300000** 10

E 14/10 **0328400000** 10

E 14/16 **0328500000** 10

Gauge rings

P 14/10 **0328700000** 50

Screw cap (spare)

SK **0339410000** 20

SAKS 5/35

for D 02 fuses **E 18**



28/80/66

13 mm/M 4/5.5 x 1

400 V[§]/63 A/16 mm²

6 kV/3

1.2...2.4

4

1.5...16

1.5...16

1.5...16

1.5...16

1.5...16

B 7

(QL 2...5) 47

(QL 6...10) 36

600 V/63 A/14...6 AWG

Dark beige Wemid KrG

0502100000 20

Neozed D 02

Type Cat. No. Qty.

WTW **1058800000** 20

QL 2 **0207800000** 20

QL 3 **0207900000** 20

QL 4 **0208000000** 20

QL 10 **0338900000** 20

BS M 4x9 **0103300000** 100

SS M 4 **0136400000** 100

D 02 fuse inserts

Rated voltage 400 V

E 18/20 **0361300000** 10

E 18/25 **0361400000** 10

E 18/35 **0361500000** 10

E 18/50 **0361600000** 10

E 18/63 **0361700000** 10

Gauge rings

P 18/20 **0361800000** 50

P 18/25 **0361900000** 50

P 18/35 **0362000000** 50

P 18/50 **0362100000** 50

Screw cap (spare)

SK **0359310000** 20

Mounting rails, end brackets, further marking materials see "Accessories"


[§]) Also for 400 V - with Neozed marine fuse

[§]) Current for overload up to 10 A, for short-circuits up to 25 A

Distribution terminals for N rail 10 x 3

Terminals/accessories

WDL 2.5/S/ NT/L/PE



32 A/4 mm²



6/84.5/48.7

8 mm/M 2.5/3.5 x 0.6

VDE 0611 Part 4

250V/400V/24 A/2.5 mm²

250V/400 V/4 kV/3

0.4...0.6

1

Clampable conductors

Solid H07V-U mm² 0.5...4

Stranded H07V-R mm² 1.5...4

Flexible H07V-K mm² 0.5...4

Flexible H07V-K and ferrule acc. to DIN 46 228/1 mm² 0.25...2.5

Flexible H07V-K and ferrules with plastic insul. collar mm² 0.25...2.5

Max. clamping range in mm²/Gauge pin acc. to 60 947-7-1 Size 0.13...4 A 3

Cont. current of cross-connect. Q multi-pole 24

UL/CSA rated data

Voltage/current/conductor size UL 300 V/15 A/22...12 AWG

Voltage/current/conductor size CSA 300 V/10 A/26...12 AWG


Ordering data Version

for TS 35 / Dark beige Wemid

Cat. No. Qty. 1030600000 50

(NT connection coded blue)

WDL 2.5/S/ L/L



32 A/4 mm²



6/84.5/48.7

8 mm/M 2.5/3.5 x 0.6

IEC 60 947-7-1

400 V/24 A/2.5 mm²

400 V/6 kV/3

0.4...0.6

1

Clampable conductors

Solid H07V-U mm² 0.5...4

Stranded H07V-R mm² 1.5...4

Flexible H07V-K mm² 0.5...4

Flexible H07V-K and ferrule acc. to DIN 46 228/1 mm² 0.25...2.5

Flexible H07V-K and ferrules with plastic insul. collar mm² 0.25...2.5

Max. clamping range in mm²/Gauge pin acc. to 60 947-7-1 Size 0.13...4 A 3

Cont. current of cross-connect. Q multi-pole 24

UL/CSA rated data

Voltage/current/conductor size UL 300 V/15 A/22...12 AWG

Voltage/current/conductor size CSA 300 V/10 A/26...12 AWG

Ordering data Version

Cat. No. Qty. 1031200000 50

Installation specifications for heavy-current installations up to 1000 V (according to VDE 0100; IEC 364) require an insulation measurement test of the erected installation. Special regulations stipulate an insulation measurement of all outgoing conductors (L 1, L 2, L 3, N) without making any disconnections. These requirements are met by the three-way terminal WDL. Circuits can be connected on three levels across a width of only 6 mm in a clear and space-saving manner.

WDL 2.5/S...

N cross-connection with the proven busbar system 10 x 3 mm up to 140 A. The supply power of the busbar is fed directly via a separate clamping yoke (ZB 35) or a N disconnect terminal from the WNT-series.

WDL 2.5/S/L/L

Three-phase circuits can be realized by combining three-way terminals (L 1, NT, PE) with WDL 2.5/S/L/L two-way terminals (L 2, L 3).

End plate




Support plate



Small partition for Q



Cross-connection (L/N/NT)



Busbar 10 x 3

Distance f. upper edge busbar to upper edge of TS 35 = 25.5 mm

Cu 140 A


Clamping yoke




N-Disconnect terminal

as input terminals

End bracket



Marking tags



Type Cat. No. Qty.

WAP WDL 2.5/S		
	1067700000	20

Type Cat. No. Qty.

WHP WDL 2.5/S		
	1067980000	20

Type Cat. No. Qty.

TSch 1	0319160000	100
--------	-------------------	-----

Type Cat. No. Qty.

Q 2	1071500000	50
-----	-------------------	----

Type Cat. No. Qty.

Q 3	1071600000	50
-----	-------------------	----

Type Cat. No. Qty.

Q 4	1071700000	50
-----	-------------------	----

Type Cat. No. Qty.

Q 10	1071800000	20
------	-------------------	----

Type Cat. No. Qty.

Q 20	1074200000	20
------	-------------------	----

Type Cat. No. Qty.

SSch 10 x 3 Cu		
	0348900000	1 m

Type Cat. No. Qty.

ZB 35 K	0502680000	50
---------	-------------------	----

Type Cat. No. Qty.

WNT 10	1010980000	50
--------	-------------------	----

Type Cat. No. Qty.

WNT 16 N	1019000000	50
----------	-------------------	----

Type Cat. No. Qty.

WNT 70 N	9512210000	10
----------	-------------------	----

Type Cat. No. Qty.

WEW 35 / 2	1061200000	50
------------	-------------------	----

Type Cat. No. Qty.

WAP WDL 2.5/S		
	1067700000	20

Type Cat. No. Qty.

WHP WDL 2.5/S		
	1067980000	20

Type Cat. No. Qty.

TSch 1	0319160000	100
--------	-------------------	-----

Type Cat. No. Qty.

Q 2	1071500000	50
-----	-------------------	----

Type Cat. No. Qty.

Q 3	1071600000	50
-----	-------------------	----

Type Cat. No. Qty.

Q 4	1071700000	50
-----	-------------------	----

Type Cat. No. Qty.

Q 10	1071800000	20
------	-------------------	----

Type Cat. No. Qty.

Q 20	1074200000	20
------	-------------------	----

Type Cat. No. Qty.

SSch 10 x 3 Cu		
	0348900000	1 m

Type Cat. No. Qty.

ZB 35 K	0502680000	50
---------	-------------------	----

Type Cat. No. Qty.

WNT 10	1010980000	50
--------	-------------------	----

Type Cat. No. Qty.

WNT 16 N	1019000000	50
----------	-------------------	----

Type Cat. No. Qty.

WNT 70 N	9512210000	10
----------	-------------------	----

Type Cat. No. Qty.

WEW 35 / 2	1061200000	50
------------	-------------------	----

Distribution terminals for N rail 10 x 3

WDL 2.5/S blocks
for a three-phase circuit
for three AC circuits32 A/4 mm²

12/18/84.5/48.7
8 mm/M 2.5/3.5 x 0.6
250V/400V/24 A/2.5 mm²
250V/400V/4 kV/3

0.4...0.6
1

0.5...4
1.5...4
0.5...4
0.25...2.5
0.25...2.5
0.13...4 A 3
24

300 V/15 A/22...12 AWG
300 V/10 A/26...12 AWG

Cat. No. Qty.
Block of 3; 1030600000

= **1034200000** 25
Block of 1 à 1 piece 1030600000 a.
1031200000 = **1034100000** 20

Type Cat. No. Qty.

WAP WDL 2.5/S
1067700000 20

WHP WDL 2.5/S
1067980000 20

TSch 1 **0319160000** 100

Q 2 **1071500000** 50
Q 3 **1071600000** 50
Q 4 **1071700000** 50
Q 10 **1071800000** 20
Q 20 **1074200000** 20

SSch 10 x 3 Cu
0348900000 1 m

ZB 35 K **0502680000** 50

WNT 10 **1010980000** 50

WNT 16 N **1019000000** 50

WNT 70 N **9512210000** 10

WEW 35 / 2 **1061200000** 50

DEK 6 see "Accessories"

WS 8/5 **1640740000** 720

WS 8/5 **1773360000** 300

WDL 2.5/S/N

32 A/4 mm²

6/84.5/48.7
8 mm/M 2.5/3.5 x 0.6
IEC 60 947-7-1
400 V/24 A/2.5 mm²
400 V/6 kV/3

0.4...0.6
1

0.5...4
1.5...4
0.5...4
0.25...2.5
0.25...2.5
0.13...4 A 3
24

300 V/15 A/22...12 AWG
300 V/10 A/26...12 AWG

Cat. No. Qty.
Block of 3; 1030600000

= **1030900000** 50
(N connection
coded blue)

Type Cat. No. Qty.

WAP WDL 2.5/S
1067700000 20

TSch 1 **0319160000** 100

Q 2 **1071500000** 50
Q 3 **1071600000** 50
Q 4 **1071700000** 50
Q 10 **1071800000** 20
Q 20 **1074200000** 20


WEW 35 / 2 **1061200000** 50

DEK 6 see "Accessories"

WS 8/5 **1640740000** 720

WS 8/5 **1773360000** 300

WDL 2.5/S/L

32 A/4 mm²

6/84.5/48.7
8 mm/M 2.5/3.5 x 0.6
IEC 60 947-7-1
400 V/24 A/2.5 mm²
400 V/6 kV/3

0.4...0.6
1

0.5...4
1.5...4
0.5...4
0.25...2.5
0.25...2.5
0.13...4 A 3
24

300 V/15 A/22...12 AWG
300 V/10 A/26...12 AWG

Cat. No. Qty.
Block of 3; 1030600000

= **1031300000** 50
(N connection
coded blue)

Type Cat. No. Qty.

WAP WDL 2.5/S
1067700000 20

TSch 1 **0319160000** 100


Q 2 **1071500000** 50
Q 3 **1071600000** 50
Q 4 **1071700000** 50
Q 10 **1071800000** 20
Q 20 **1074200000** 20

WEW 35 / 2 **1061200000** 50

DEK 6 see "Accessories"

WS 8/5 **1640740000** 720

WS 8/5 **1773360000** 300

WDL 2.5/S/
N/L32 A/4 mm²

6/84.5/48.7
8 mm/M 2.5/3.5 x 0.6
IEC 60 947-7-1
400 V/24 A/2.5 mm²
400 V/6 kV/3

0.4...0.6
1

0.5...4
1.5...4
0.5...4
0.25...2.5
0.25...2.5
0.13...4 A 3
24

300 V/15 A/22...12 AWG
300 V/10 A/26...12 AWG

Cat. No. Qty.
Block of 3; 1030600000

= **1030800000** 50
(N connection
coded blue)

Type Cat. No. Qty.

WAP WDL 2.5/S
1067700000 20

TSch 1 **0319160000** 100


Q 2 **1071500000** 50
Q 3 **1071600000** 50
Q 4 **1071700000** 50
Q 10 **1071800000** 20
Q 20 **1074200000** 20

WEW 35 / 2 **1061200000** 50

DEK 6 see "Accessories"

WS 8/5 **1640740000** 720

WS 8/5 **1773360000** 300

WDL 2.5/S/
N/L/PE32 A/4 mm²

6/84.5/48.7
8 mm/M 2.5/3.5 x 0.6
250V/400V/24 A/2.5 mm²
250V/400 V/4 kV/3

0.4...0.6
1

0.5...4
1.5...4
0.5...4
0.25...2.5
0.25...2.5
0.13...4 A 3
24

300 V/15 A/22...12 AWG
300 V/10 A/26...12 AWG

Cat. No. Qty.
Block of 3; 1030600000

= **1030700000** 50
(N connection
coded blue)

Type Cat. No. Qty.

WAP WDL 2.5/S
1067700000 20

TSch 1 **0319160000** 100


Q 2 **1071500000** 50
Q 3 **1071600000** 50
Q 4 **1071700000** 50
Q 10 **1071800000** 20
Q 20 **1074200000** 20

WEW 35 / 2 **1061200000** 50

DEK 6 see "Accessories"

WS 8/5 **1640740000** 720

WS 8/5 **1773360000** 300

WDL 2.5/S/
L/L/PE32 A/4 mm²

6/84.5/48.7
8 mm/M 2.5/3.5 x 0.6
250V/400V/24 A/2.5 mm²
250V/400 V/4 kV/3

0.4...0.6
1

0.5...4
1.5...4
0.5...4
0.25...2.5
0.25...2.5
0.13...4 A 3
24

300 V/15 A/22...12 AWG
300 V/10 A/26...12 AWG

Cat. No. Qty.
Block of 3; 1030600000

= **1031100000** 50
(N connection
coded blue)

Type Cat. No. Qty.

WAP WDL 2.5/S
1067700000 20

TSch 1 **0319160000** 100

Q 2 **1071500000** 50
Q 3 **1071600000** 50
Q 4 **1071700000** 50
Q 10 **1071800000** 20
Q 20 **1074200000** 20

WEW 35 / 2 **1061200000** 50

DEK 6 see "Accessories"

WS 8/5 **1640740000** 720

WS 8/5 **1773360000** 300

Distribution terminals with N cross-connection WQV

Terminals/accessories

WDL 2.5/NT/L/PE

WDL 2.5/L/L



32 A/4 mm²

6/90/48.7

8 mm/M 2.5/3²/3.5 x 0.6

VDE 0611 Part 4

250V/400V/24 A/2.5/4² mm²

250V/400 V/4 kV/3

32 A/4 mm²

6/90/48.7

8 mm/M 2.5/3²/3.5 x 0.6

IEC 60 947-7-1

400 V/24 A/2.5/4² mm²

400 V/6 kV/3

Installation specifications for heavy-current installations up to 1000 V (according to VDE 0100; IEC 364) require an insulation measurement test of the erected installation. Special regulations stipulate an insulation measurement of all outgoing conductors (L 1, L 2, L 3, N) without making any disconnections. These requirements are met by the three-way terminal WDL. Circuits can be connected on three levels across a width of only 6 mm in a clear and space-saving manner.

WDL 2.5...

N cross-connection with the cross-connection system WQV 4 from the W-series. The supply power of the busbar is fed directly via a clamping yoke (4/6 mm² = A 4) into the terminal up to 32 A.

WDL 2.5/L/L

Three-phase circuits can be realized by combining three-way terminals (L 1, NT, PE) with WDL 2.5/S/L/L two-way terminals (L 2, L 3).

Max. technical data

Dimensions / approvals

Width/length/height (mm) with TS 35 x 7.5

Insulation stripping length/clamping screw/screwdriver blade

Rated data

Rated voltage/current/cross-section

Rated voltage/impulse voltage/pollution severity

Further technical data

Tightening torque range Nm

Torque setting with DMS 2 electric screwdriver

Clampable conductors

Solid H07V-U mm²

Stranded H07V-R mm²

Flexible H07V-K mm²

Flexible H07V-K and ferrule acc. to DIN 46 228/1 mm²

Flexible H07V-K and ferrules with plastic insul. collar mm²

Max. clamping range in mm²/Gauge pin acc. to 60 947-7-1 Size

Cont. current of cross-connect. Q multi-pole A

Cont. current of cross-connect. WQV 4 multi-pole A

UL/CSA rated data

Voltage/current/conductor size UL

Voltage/current/conductor size CSA

Ordering data

Version

for TS 35 / Dark beige Wemid

End plate



Small partition



Cross-connection (L, NT, N)



Cross-connection¹⁾ input (L, NT, N)



Notching tool for WQV

Type Cat. No. Qty.

WAP WDL 2.5

1067800000 20

TSch 1 0319160000 100

Q 2 1071500000 50

Q 3 1071600000 50

Q 4 1071700000 50

Q 10 1071800000 20

Q 20 1074200000 20

WQV 4/2 1051960000 50

WQV 4/3 1054560000 50

WQV 4/4 1054660000 50

WQV 4/10 1052060000 20

WAW 1 9004500000 1

WAW 1 9004500000 1

WEW 35 / 2 1061200000 50

WEW 35 / 2 1061200000 50

DEK 6 see "Accessories"

WS 8/5 1640740000 720

WS 8/5 1773360000 300

WS 8/5 1640740000 720

WS 8/5 1773360000 300

WS 8/5 1640740000 720

WS 8/5 1773360000 300

WS 8/5 1640740000 720

WS 8/5 1773360000 300

WS 8/5 1640740000 720

WS 8/5 1773360000 300

WS 8/5 1640740000 720

WS 8/5 1773360000 300

WS 8/5 1640740000 720

WS 8/5 1773360000 300

WS 8/5 1640740000 720

WS 8/5 1773360000 300

WS 8/5 1640740000 720

WS 8/5 1773360000 300

Type Cat. No. Qty.

WAP WDL 2.5

1067800000 20

TSch 1 0319160000 100

Q 2 1071500000 50

Q 3 1071600000 50

Q 4 1071700000 50

Q 10 1071800000 20

Q 20 1074200000 20

WQV 4/2 1051960000 50

WQV 4/3 1054560000 50

WQV 4/4 1054660000 50

WQV 4/10 1052060000 20

WAW 1 9004500000 1

WAW 1 9004500000 1

WEW 35 / 2 1061200000 50

WEW 35 / 2 1061200000 50

DEK 6 see "Accessories"

WS 8/5 1640740000 720

WS 8/5 1773360000 300

WS 8/5 1640740000 720

WS 8/5 1773360000 300

WS 8/5 1640740000 720

WS 8/5 1773360000 300

WS 8/5 1640740000 720

WS 8/5 1773360000 300

WS 8/5 1640740000 720

WS 8/5 1773360000 300

WS 8/5 1640740000 720

WS 8/5 1773360000 300

WS 8/5 1640740000 720

WS 8/5 1773360000 300

WS 8/5 1640740000 720

WS 8/5 1773360000 300

WS 8/5 1640740000 720

WS 8/5 1773360000 300

End bracket

Marking tags



DEK Standard

WS White neutral


WS indiv. printed

Print

Mounting rails, end brackets, further marking materials see "Accessories"

¹⁾ Cross-connection WQV 4

²⁾ Values refer to top left clamping unit (A4)



Terminals for temperature measuring circuits


WDU 2.5/TC



Weidmüller thermocouple terminals are specially designed to transmit very small voltages in temperature measuring circuits. Special busbars ensure that no false signals are transmitted in the terminal when temperature differences between the positive and negative paths exist. This high measuring precision is required, for example, in aircraft engine performance test rigs, complicated chemical processes, controllers, etc.

- Busbar material corresponds to thermal and compensating conductors
- Clear thermocouple marking
- 2-pole blocks per thermocouple
- Stacking width 10 mm

Configuration of a temperature measuring circuit



- 1 Thermocouple (sensor) 4 Reference junction
2 Thermocouple terminals 5 Supply conductors (to and from)
3 Compensating conductor 6 Measuring instrument

The thermocouple terminals shown in this measuring circuit thermoelectrically transmit thermoelectric voltage from the thermocouple to the reference junction and the indicator unit via the compensating conductor. Thermocouple terminals are required for constructing a temperature circuit.

Technical data

Thermocouples acc. to IEC 584 (DIN 43 710)

Busbar	
	Cromel Alumel
	E-Copper Constantan
	Iron Konstantan
	E-Copper/ A-Copper
	S-Copper/ E-Copper
	Cromel- Constantan

Dimensions/approvals

Width/length/height (mm) with TS 35 x 7.5
Insulation stripping length/clamping screw/screwdriver blade

Rated data

Rated voltage/current/cross-section
Rated impulse voltage acc. to VDE 0110/1.89/pollution severity

Further technical data

Tightening torque range Nm
Torque setting with DMS 2 electric screwdriver

Clampable conductors

Solid H07V-U mm²
Stranded H07V-R mm²
Flexible H07V-K mm²
Flexible H07V-K and ferrule acc. to DIN 46 228/1 mm²
Flexible H07V-K and ferrules with plastic insul. collar mm²
Max. clamping range in mm²/Gauge pin acc. to IEC 60 947-7-1 Size
Cont. current of cross-connect. 2-pole A
Cont. current of cross-connect. multi-pole A

UL/CSA rated data

Voltage/current/conductor size UL
Voltage/current/conductor size CSA

Ordering data

For thermocouples Type K NiCr – Ni
acc. to IEC 584 Type T Cu – CuNi
(DIN 43710) Type J Fe – CuNi
Type S u. R PT 10% – Pt Rh/PT 13% – Pt Rh
Type B Pt 30% Rh – Pt 6% Rh
Type E NiCr – CuNi
Type N NiSi – Nicrosil

End plate

WAP (thickness 1.5 mm) Dark beige Wemid

Partition

WTW (thickness 1.5 mm) Dark beige Wemid

10/60/50.5

10 mm/M 2.5/3.5 x 0.6

–/–/2.5 mm²

0.4...0.6

1

0.5...2.5

1.5...2.5

0.5...2.5

0.5...2.5

0.5...2.5

0.13...4

A 2

	Cat. No.	Qty.
	1024100000	50
	1024200000	50
	1024300000	50
	1024400000	50
	1033700000	50
	1033300000	50
	1041500000	50

Type	Cat. No.	Qty.
WAP 2.5-10	1050000000	50

WTW 2.5-10	1050100000	20
------------	-------------------	----

Marking tags

DEK Standard
WS white neutral
WS indiv. printed


Print

DEK 5	see "Accessories"
WS 12/5	1609860000 720
WS 12/5	1773380000 300

Mounting rails, end brackets, further marking materials see "Accessories"

Feed-through terminals with WSA plug adapter

WDU 4 SA



Dimensions/approvals	
Width/length/height (mm)	with TS 35 x 7.5
Insulation stripping length/clamping screw/screwdriver blade	10 mm/M 3/3.5 x 0.6
Rated data	
Rated voltage/current/cross-section	400 V/34 A/4 mm ²
Rated impulse voltage acc. to VDE 0110/1.89/pollution severity	6 kV/3
Further technical data	
Tightening torque range	Nm 0.5...1.0
Torque setting with DMS 2 electric screwdriver	2
Clampable conductors	
Solid H07V-U	mm ² 0.5...6
Stranded H07V-R	mm ² 1.5...6
Flexible H07V-K	mm ² 0.5...4
Flexible H07V-K and ferrule acc. to DIN 46 228/1	mm ² 0.5...4
Flexible H07V-K and ferrules with plastic insul. collar	mm ² 0.5...4
Max. clamping range in mm ² /Gauge pin acc. to IEC 60 947-7-1 Size	0.13...6 A 4
Cont. current of cross-connect. 2-pole	A
Cont. current of cross-connect. multi-pole	A
UL/CSA rated data	
Voltage/current/conductor size	UL 300 V/25 A/22...12 AWG
Voltage/current/conductor size	CSA 300 V/-/22...12 AWG
Ordering data	
	Dark beige Wemid
	Blue Wemid

End plate	
WAP (thickness 1.5 mm)	
Partition	
WTW (thickness 1.5 mm)	
Cross-connection	
Screening bar LS 2.8	

Plug adapter WSA 2	
380 V~/10 A/1.5 mm ²	Version with
Crimp connections	
	Version with
	screw connection
	TOPP system
	Green
Covers	

Crimp contact 0.5–1.5 mm ²	
	einzeln

Marking tags	
DEK	WS
Print	
DEK	Standard
WS white	neutral
WS	indiv. printed

Mounting rails, end brackets, further marking materials see "Accessories"

- 1) With hook 3) With dovetail 5) Crimping tool, type CZ 22E 0560400000
2) without Rasthaken 4) Without dovetail


Feed-through terminals

for retrofitting electronic components

Dimensions/approvals	
Width/length/height (mm)	with TS 35 x 7.5
Insulation stripping length/clamping screw/screwdriver blade	10 mm/M 3/3.5 x 0.6
Rated data IEC 60 947-7-1	
Rated voltage/current/cross-section	250 V/32 A/4 mm ²
Rated impulse voltage acc. to VDE 0110/1.89 /pollution severity	4 kV/3
Further technical data	
Tightening torque range	Nm 0.5...1.0
Torque setting with DMS 2 electric screwdriver	2
Clampable conductors	
Solid H07V-U	mm ² 0.5...4
Stranded H07V-R	mm ² 1.5...4
Flexible H07V-K	mm ² 0.5...4
Flexible H07V-K and ferrule acc. to DIN 46 228/1	mm ² 0.5...4
Flexible H07V-K and ferrules with plastic insul. collar	mm ² 0.5...4
Max. clamping range in mm ² / Gauge pin acc. to 60 947-1 Size	0.13...4 A 3
Wire diameter of electronic components	mm 0.8...1.0 mm
UL/CSA rated data	
Voltage/current/conductor size	UL 300 V/10 A/26...12 AWG
Voltage/current/conductor size	CSA 300 V/10 A/26...12 AWG
Ordering data	
	Dark beige Wemid

Barrier	
Thickness 2.5 mm	

Busbar	
SSch 7.3x1.2	1071200000 1m




WPO 4 with filled varistor
Weidmüller varistor terminals have been designed for retrofitting electronic components, such as varistors, diodes, gas discharge tubes, etc.
These electronic terminals no longer have to be configured prior installation to subsequently be delivered with soldered components which can no longer be distinguished.
The significant advantages of this design are:

- **Cost saving**
Components can be changed quickly on site.
Service is limited to visual inspection
- **Clarity:**
Components are easy to distinguish.
- **Flexibility:**
Components can immediately be adapted to changed conditions.

Note:
Never change electronic components in energized systems

Marking tags	
DEK	WS
Print	
DEK	Standard
WS white	neutral
WS	indiv. printed


WPO 4



Dimensions/approvals	
Width/length/height (mm)	with TS 35 x 7.5
Insulation stripping length/clamping screw/screwdriver blade	9 mm/M 3/3.5 x 0.6
Rated data IEC 60 947-7-1	
Rated voltage/current/cross-section	250 V/32 A/4 mm ²
Rated impulse voltage acc. to VDE 0110/1.89 /pollution severity	4 kV/3
Further technical data	
Tightening torque range	Nm 0.5...1.0
Torque setting with DMS 2 electric screwdriver	2
Clampable conductors	
Solid H07V-U	mm ² 0.5...4
Stranded H07V-R	mm ² 1.5...4
Flexible H07V-K	mm ² 0.5...4
Flexible H07V-K and ferrule acc. to DIN 46 228/1	mm ² 0.5...4
Flexible H07V-K and ferrules with plastic insul. collar	mm ² 0.5...4
Max. clamping range in mm ² / Gauge pin acc. to 60 947-1 Size	0.13...4 A 3
Wire diameter of electronic components	mm 0.8...1.0 mm
UL/CSA rated data	
Voltage/current/conductor size	UL 300 V/10 A/26...12 AWG
Voltage/current/conductor size	CSA 300 V/10 A/26...12 AWG
Ordering data	
	Dark beige Wemid

Barrier	
Thickness 2.5 mm	

Busbar	
SSch 7.3x1.2	1071200000 1m




Overvoltage in a three-phase supply discharged to earth via WPE 4 with the aid of varistors and a gas discharge tube.

When using the screening bar rated data is reduced data!

Feed-through terminals

WDU 2.5 F



WDU 2.5 FF



WDK 2.5 F



WDK 2.5 FV



Max. technical data

Dimensions/approvals

Width/length/height (mm) with TS 35 x 7.5

Insulation stripping length/clamping screw/screwdriver blade

Rated data

Rated voltage/current/cross-section

Rated cross-section of clamping yoke

Rated cross-section of 2.8 mm push-on tab/solder connection

Rated impulse voltage acc. to VDE 0110/1.89/pollution severity

Further technical data

Tightening torque range Nm

Torque setting with DMS 2 electric screwdriver

Clampable conductors

Solid H07V-U mm²

Stranded H07V-R mm²

Flexible H07V-K mm²

Flexible H07V-K and ferrule acc. to DIN 46 228/1 mm²

Flexible H07V-K and ferrules with plastic insul. collar mm²

Max. clamping range in mm²/Gauge pin acc. to IEC 60 947-7-1 Size

Cont. current of cross-connect. 2-pole A

Cont. current of cross-connect. multi-pole A

UL/CSA rated data

Voltage/current/conductor size UL

Voltage/current/conductor size CSA

Ordering data

Version

Dark beige Wemid

Dark beige Wemid

Dark beige Wemid

Dark beige Wemid

Blue Wemid

End plate/partition



WAP (thickness 3 mm)

WAP 2.5 (thickness 1.5 mm)



WTW (thickness 1.5 mm) Wemid

Cross-connection



WQV

LS 2.8

Screening bar

Notching tool for WQV

Test adapter

WTA

TA 1



Strain relief

Test plugs/sockets/insulating sleeves

PS 2.3

StB 8.5

Insulating sleeves



Cover



WAD with symbol

WAD white for self-labelling

Group marking

WT 4

T 5



WGB



Tag carrier for S 10 markers

Marking tags



DEK



WS

Standard

WS white neutral

WS indiv. printed

DEK

WS

WS

12 A/-

UL KEMA LR

5/60/47

10 mm/M 2.5/3.5 x 0.6

500 V m. IH/12 (2x6) A

2.5 mm²

1 / - mm²

6 kV/3

0.4...0.8

1

0.5...4

1.5...4

0.5...4

0.5...2.5

0.5...2.5¹⁾

0.13...4

12

12

300 V/10 A/22...12 AWG

300 V/10 A/26...12 AWG

Type Cat. No. Qty.

1021800000 100

12 A/-

UL KEMA LR

5/60/47

10 mm/-

500 V m. IH/12 (2x6) A

1 / - mm²

6 kV/3

0.4...0.6

1

0.5...4/1

1.5...2.5

0.5...2.5

0.5...2.5

0.5...2.5¹⁾

0.13...4

12

12

300 V/10 A/22...12 AWG

300 V/10 A/26...12 AWG

Type Cat. No. Qty.

1021900000 100

12 A/-

UL KEMA LR

5/69/63

10 mm/M 2.5/3.5 x 0.6

400 V m. IH/12 (2x6) A/2.5

2.5 mm²

1 / - mm²

6 kV/3

0.4...0.6

1

0.5...4/1

1.5...2.5

0.5...2.5

0.5...2.5

0.5...2.5¹⁾

0.13...4

32

32

300 V/10 A/22...12 AWG

300 V/10 A/26...12 AWG

Type Cat. No. Qty.

1021600000 100

12 A/-

UL KEMA LR

5/69/63

10 mm/M 2.5/3.5 x 0.6

400 V m. IH/12 (2x6) A/2.5

2.5 mm²

1 / - mm²

6 kV/3

0.4...0.6

1

0.5...4/1

1.5...2.5

0.5...2.5

0.5...2.5

0.5...2.5¹⁾

0.13...4

32

32

300 V/10 A/22...12 AWG

300 V/10 A/26...12 AWG

Type Cat. No. Qty.

1022400000 100

1) Ferrules with optimum diameter for terminals with 5 mm pitch: Cat. No. 1333100000
When using the screening bar rated data is reduced data!

Feed-through terminals



Dimensions/approvals

Width/length/height (mm) with TS 15 x 7.5

Insulation stripping length/clamping screw/screwdriver blade

VDE rated data 0611 Part 1 / IEC 60 947-7-1

Rated voltage/current/cross-section

Rated impulse voltage/pollution severity

Further technical data

Tightening torque range Nm

Clampable conductors

Solid H07V-U mm²

Stranded H07V-R mm²

Flexible H07V-K mm²

Flexible with ferrule acc. to DIN 46 228/1 mm²

Flexible with ferrule with plastic insul. collar mm²

Gauge pin acc. to IEC 60 947-7-1 Size

UL/CSA rated data

Voltage/current/conductor size UL

Voltage/current/conductor size CSA

Ordering data

Version

Dark beige Wemid


Blue Wemid

Green-yellow Wemid

End plates/partitions

WAP (thickness 1.5 mm) Dark beige Wemid

WDU 1.5/R 3.5



3.5/24.5/25

7 (-1) mm/M 2/0.4 x 2.5

400 V/17.5 A/1.5 mm²

4 kV/3

0.3...0.4

0.5...1.5

1.5

0.5...1.5

0.5...1.5

0.5

A 1


300 V/10 A/26...14 AWG

300 V/10 A/26...14 AWG

TS15	Cat. No.	Qty.
WDU 1.5/R 3.5	1753280000	100
WDU 1.5/R 3.5 BL	1754170000	100

Type	Cat. No.	Qty.
WAP WDU 1.5/R3.5	1754190000	20

WDK 1.5/R 3.5



3.5/46.5/38.5

7 (-1) mm/M 2/0.4 x 2.5

400 V/16 A/1.5 mm²

4 kV/3

0.3...0.4

0.5...1.5

1.5

0.5...1.5

0.5...1.5

0.5

A 1

300 V/10 A/26...14 AWG


300 V/10 A/26...14 AWG

TS15	Cat. No.	Qty.
WDK 1.5/R 3.5	1753290000	100
WDK 1.5/R 3.5 BL	1754180000	100

Type	Cat. No.	Qty.
WAP WDK 1.5/R3.5	1754200000	20

WPE 1.5/R 3.5

new



3.5/24.5/25

7 (-1) mm/M 2/0.4 x 2.5

- /- 1.5 mm²

4 kV/3

0.3...0.4

0.5...1.5

1.5

0.5...1.5

0.5...1.5

0.5

A 1

300 V/10 A/26...14 AWG

300 V/10 A/26...14 AWG

TS15	Cat. No.	Qty.
WPE 1.5/R 3.5	1798400000	100

Type	Cat. No.	Qty.
------	----------	------

Cross-connections



ZQV

2-pole

3-pole

4-pole

5-pole

6-pole

7-pole

8-pole

9-pole

10-pole

30-pole

ZQV 1.5/R3.5/2 GE	1754210000	60
ZQV 1.5/R3.5/3 GE	1754220000	60
ZQV 1.5/R3.5/4 GE	1754230000	60
ZQV 1.5/R3.5/5 GE	1754240000	20
ZQV 1.5/R3.5/6 GE	1754250000	20
ZQV 1.5/R3.5/7 GE	1754260000	20
ZQV 1.5/R3.5/8 GE	1754270000	20
ZQV 1.5/R3.5/9 GE	1754280000	20
ZQV 1.5/R3.5/10 GE	1754290000	20
ZQV 1.5/R3.5/30 GE	1754300000	10

ZQV 1.5/R3.5/2 GE	1754210000	60
ZQV 1.5/R3.5/3 GE	1754220000	60
ZQV 1.5/R3.5/4 GE	1754230000	60
ZQV 1.5/R3.5/5 GE	1754240000	20
ZQV 1.5/R3.5/6 GE	1754250000	20
ZQV 1.5/R3.5/7 GE	1754260000	20
ZQV 1.5/R3.5/8 GE	1754270000	20
ZQV 1.5/R3.5/9 GE	1754280000	20
ZQV 1.5/R3.5/10 GE	1754290000	20
ZQV 1.5/R3.5/30 GE	1754300000	10

Screwdriver



SDI 0.4 x 2.5 **9008370000** 1

SDI 0.4 x 2.5 **9008370000** 1

SDI 0.4 x 2.5 **9008370000** 1

Marking tags

Print

Consecutive vertical

DEK 5/3.5 FS 1-10	1762320001	500
DEK 5/3.5 FS 11-20	1762320011	500
DEK 5/3.5 FS 21-30	1762320021	500
DEK 5/3.5 FS 31-40	1762320031	500
DEK 5/3.5 FS 41-50	1762320041	500
DEK 5/3.5 FS 51-60	1762320051	500
DEK 5/3.5 FS 61-70	1762320061	500
DEK 5/3.5 FS 71-80	1762320071	500
DEK 5/3.5 FS 81-90	1762320081	500
DEK 5/3.5 FS 91-100	1762320091	500
DEK 5/3.5 MC neutral	1755270000	500
DEK 5/3.5 MC GW 1	1755280001	500
DEK 5/3.5 MC GW 2	1755280002	500
DEK 5/3.5 MC GW 3	1755280003	500
DEK 5/3.5 MC GW 4	1755280004	500
DEK 5/3.5 MC GW 5	1755280005	500
DEK 5/3.5 MC GW 6	1755280006	500
DEK 5/3.5 MC GW 7	1755280007	500
DEK 5/3.5 MC GW 8	1755280008	500
DEK 5/3.5 MC GW 9	1755280009	500
DEK 5/3.5 MC GW 0	1755281000	500

DEK 5/3.5 FS 1-10	1762320001	500
DEK 5/3.5 FS 11-20	1762320011	500
DEK 5/3.5 FS 21-30	1762320021	500
DEK 5/3.5 FS 31-40	1762320031	500
DEK 5/3.5 FS 41-50	1762320041	500
DEK 5/3.5 FS 51-60	1762320051	500
DEK 5/3.5 FS 61-70	1762320061	500
DEK 5/3.5 FS 71-80	1762320071	500
DEK 5/3.5 FS 81-90	1762320081	500
DEK 5/3.5 FS 91-100	1762320091	500
DEK 5/3.5 MC neutral	1755270000	500
DEK 5/3.5 MC GW 1	1755280001	500
DEK 5/3.5 MC GW 2	1755280002	500
DEK 5/3.5 MC GW 3	1755280003	500
DEK 5/3.5 MC GW 4	1755280004	500
DEK 5/3.5 MC GW 5	1755280005	500
DEK 5/3.5 MC GW 6	1755280006	500
DEK 5/3.5 MC GW 7	1755280007	500
DEK 5/3.5 MC GW 8	1755280008	500
DEK 5/3.5 MC GW 9	1755280009	500
DEK 5/3.5 MC GW 0	1755281000	500

DEK 5/3.5 FS 1-10	1762320001	500
DEK 5/3.5 FS 11-20	1762320011	500
DEK 5/3.5 FS 21-30	1762320021	500
DEK 5/3.5 FS 31-40	1762320031	500
DEK 5/3.5 FS 41-50	1762320041	500
DEK 5/3.5 FS 51-60	1762320051	500
DEK 5/3.5 FS 61-70	1762320061	500
DEK 5/3.5 FS 71-80	1762320071	500
DEK 5/3.5 FS 81-90	1762320081	500
DEK 5/3.5 FS 91-100	1762320091	500
DEK 5/3.5 MC neutral	1755270000	500
DEK 5/3.5 MC GW 1	1755280001	500
DEK 5/3.5 MC GW 2	1755280002	500
DEK 5/3.5 MC GW 3	1755280003	500
DEK 5/3.5 MC GW 4	1755280004	500
DEK 5/3.5 MC GW 5	1755280005	500
DEK 5/3.5 MC GW 6	1755280006	500
DEK 5/3.5 MC GW 7	1755280007	500
DEK 5/3.5 MC GW 8	1755280008	500
DEK 5/3.5 MC GW 9	1755280009	500
DEK 5/3.5 MC GW 0	1755281000	500

Mounting rails, end brackets, further marking materials see "Accessories"

W-series

- 1) with Insulating sleeves
- 2) Touch-safe with prof. material for cover ADP4


Feed-through terminals for initiators and actuators

DLI 2.5 DB




6/65/49
7 mm/M 2.5/3.5 x 0.6

DLI 2.5 LD DB PNP




6/65/49
7 mm/M 2.5/3.5 x 0.6

DLI 2.5 LD DB NPN



6/65/49
7 mm/M 2.5/3.5 x 0.6

DLD 2.5 DB²⁾



6/82/49
7 mm/M 2.5/3.5 x 0.6

Dimensions/approvals

Width/length/height (mm)	with TS 35 x 7.5
Insulation stripping length/clamping screw/screwdriver blade	

Rated data IEC 60 947-7-1

Rated voltage/current/cross-section	250 V/20 A/2.5 mm ²
Rated impulse voltage/pollution severity	4 kV/3

Further technical data

Tightening torque range	Nm 0.4...0.6
Torque setting with DMS 2 electric screwdriver	1

Clampable conductors

Solid H07V-U	mm ² 0.5...4
Stranded H07V-R	mm ² 1.5...4
Flexible H07V-K	mm ² 0.5...4
Flexible H07V-K and ferrule acc. to DIN 46 228/1	mm ² 0.25...2.5
Gauge pin acc. to IEC 60 947-7-1	Size A 3
Continuous current of terminal for conductor size	20 A/2.5 mm ²
Cont. current of cross-connect. 2...5-pole	A (Q 2...10) 20
Cont. current of cross-connect. 6...10-pole	A

UL/CSA rated data

Voltage/current/conductor size	UL 300 V/10 A/26...12 AWG
Voltage/current/conductor size	CSA 300 V/10 A/26...12 AWG

Ordering data

Standard Wemid	Cat. No.	Qty.
with diode 1N4007 Wemid	1783820000	100
With red LED (5...30 V) Wemid		
With green LED (5...30 V) Wemid		
with LED and diode 1N4007 Wemid		
with LED and diode 1N4007 Wemid		
Block of 10 ¹⁾ Wemid	(w/o dekafix) 1783850000	10
Block of 10 ¹⁾ Wemid	(w. dekafix) 1783830000	10
Fuse inserts Wemid		

End plate/small partition

AP-DLI	AP-DLD	Part-AP	TSch 1
			(thickness 1.5 mm)

Test plug/socket

StB 8.5	PS
---------	----

Cross-connection

Q 3	Q 2	Q 3	Q 4	Q 10	Q 20

VQB



Snap fit, external cross-connection VQB 1.5.

For cross-connections for more than 20 terminals, replace VH with VH 4.2
Cat. No. 1345800000
without internal thread

Group marking

WT 4	WT 4	SF 10	SG 10
------	------	-------	-------

Cover

HP 4	ADP	HP 4
------	-----	------

Marking tags

1	2	3	4	5	6
---	---	---	---	---	---


Mounting rails, end brackets, further marking materials see "Accessories"

¹⁾ DLI 2.5/35/10 = Block of 10 with built-in cross-connections

²⁾ StB 8.5 only in upper busbar

Feed-through terminals for initiators and actuators

DLA 2.5 DB



6/65/49
7 mm/M 2.5/3.5 x 0.6
250 V ¹⁾ /17.5 A/2.5 mm ²
4 kV/3
0.4...0.6
1
0.5...4
1.5...4
0.5...4
0.25...2.5
A 3
20 A/2.5 mm ²
(Q 2...20) 20

300 V/10 A/26...12 AWG
300 V/10 A/26...12 AWG
Cat. No. Qty.
1783560000 100
(no dekafix) 1783570000 10
(w. dekafix) 1783580000 10

Type	Cat. No.	Qty.
AP	1783550000	20
TSch 1	0319160000	100

StB8.5 ²⁾ (ø2.3) 0215700000 50
PS 2.3 0180400000 20


Q 2 1312500000 50
Q 3 1312600000 50
Q 4 1312700000 50
Q 10 1313100000 20
Q 20 1399800000 20

QL 2 0297200000 100
VH 4.2 1345800000 100
VQB1.5/50 BL 1633280000 5
VQB1.5/50 RT 1633290000 5
VQB1.5/50 SW 1635120000 5

WT 4 1341060000 100
SF 10 0332400000 1000
SG 10 0332500000 1000
ADP 0485400000 20
HP 4 0485860000 20

DEK 6	see "Accessories"
-------	-------------------

DLA 2.5/D DB



6/65/49
7 mm/M 2.5/3.5 x 0.6
250 V ¹⁾ /17.5 A/2.5 mm ²
4 kV/3
0.4...0.6
1
0.5...4
1.5...4
0.5...4
0.25...2.5
A 3
20 A/2.5 mm ²
(Q 2...20) 20

300 V/10 A/26...12 AWG
300 V/10 A/26...12 AWG
Cat. No. Qty.
1783590000 100

Type	Cat. No.	Qty.
AP	1783550000	20
TSch 1	0319160000	100


Q 2 1312500000 50
Q 3 1312600000 50
Q 4 1312700000 50
Q 10 1313100000 20
Q 20 1399800000 20

QL 2 0297200000 100
VH 4.2 1345800000 100
VQB1.5/50 BL 1633280000 5
VQB1.5/50 RT 1633290000 5
VQB1.5/50 SW 1635120000 5

WT 4 1341060000 100
SF 10 0332400000 1000
SG 10 0332500000 1000
ADP 0485400000 20
HP 4 0485860000 20

DEK 6	see "Accessories"
-------	-------------------

DLA 2.5/LD DB



6/65/49
7 mm/M 2.5/3.5 x 0.6
5-30 V/17.5 A/2.5 mm ²
0.8 kV/3
0.4...0.6
1
0.5...4
1.5...4
0.5...4
0.25...2.5
A 3
20 A/2.5 mm ²
(Q 2...20) 20

300 V/10 A/26...12 AWG
5-30 V/10 A/26...12 AWG
Cat. No. Qty.
1783600000 100
1783610000 100

Type	Cat. No.	Qty.
AP	1783550000	20
TSch 1	0319160000	100


Q 2 1312500000 50
Q 3 1312600000 50
Q 4 1312700000 50
Q 10 1313100000 20
Q 20 1399800000 20

QL 2 0297200000 100
VH 4.2 1345800000 100
VQB1.5/50 BL 1633280000 5
VQB1.5/50 RT 1633290000 5
VQB1.5/50 SW 1635120000 5

WT 4 1341060000 100
SF 10 0332400000 1000
SG 10 0332500000 1000
ADP 0485400000 20
HP 4 0485860000 20

DEK 6	see "Accessories"
-------	-------------------

DLA 2.5/LD/D DB



6/65/49
7 mm/M 2.5/3.5 x 0.6
5-30 V/17.5 A/2.5 mm ²
0.8 kV/3
0.4...0.6
1
0.5...4
1.5...4
0.5...4
0.25...2.5
A 3
20 A/2.5 mm ²
(Q 2...20) 20

300 V/10 A/26...12 AWG
5-30 V/10 A/26...12 AWG
Cat. No. Qty.
(red LED) 1783620000 100
(green LED) 1783630000 100

Type	Cat. No.	Qty.
AP	1783550000	20
TSch 1	0319160000	100


Q 2 1312500000 50
Q 3 1312600000 50
Q 4 1312700000 50
Q 10 1313100000 20
Q 20 1399800000 20

QL 2 0297200000 100
VH 4.2 1345800000 100
VQB1.5/50 BL 1633280000 5
VQB1.5/50 RT 1633290000 5
VQB1.5/50 SW 1635120000 5

WT 4 1341060000 100
SF 10 0332400000 1000
SG 10 0332500000 1000
ADP 0485400000 20
HP 4 0485860000 20

DEK 6	see "Accessories"
-------	-------------------

DLD 2.5/PE DB



6/74.5/49
7 mm/M 2.5/3.5 x 0.6
250 V ¹⁾ /17.5 A/2.5 mm ²
4 kV/3
0.4...0.6
1
0.5...4
1.5...4
0.5...4
0.25...2.5
A 3
20 A/2.5 mm ²
(Q 2...20) 20

300 V/10 A/26...12 AWG
300 V/10 A/26...12 AWG
Cat. No. Qty.
1783790000 100

Type	Cat. No.	Qty.
AP	1783800000	20
AP (part-AP)	1783810000	
TSch 1	0319160000	100

StB8.5 ²⁾ (ø2.3) 0215700000 50
PS 2.3 0180400000 20


Q 2 1312500000 50
Q 3 1312600000 50
Q 4 1312700000 50
Q 10 1313100000 20
Q 20 1399800000 20

QL 2 0297200000 100
VH 4.2 1345800000 100
VQB1.5/50 BL 1633280000 5
VQB1.5/50 RT 1633290000 5
VQB1.5/50 SW 1635120000 5

WT 4 1341060000 100
SF 10 0332400000 1000
SG 10 0332500000 1000
ADP 0485400000 20
HP 4 0485860000 20

DEK 6	see "Accessories"
-------	-------------------

KDKS1/PE



8/91/65
8 mm/M 3/M 2.5 ³⁾ /3.5 x 0.6
500 V/6.3 A/4 mm ²
6 kV/3
0.5...1/0.4...0.7 ³⁾
2/1 ³⁾
0.5...4
1.5...4
0.5...4
0.25...2.5
A 4 / A 3 ³⁾

-/-/22...12 AWG
Cat. No. Qty.
9532450000 50
cannot be combined with DLI / DLA

Type	Cat. No.	Qty.
AP	9503330000	50
AP Wemid 9532470000		50

StB8.5 ²⁾ (ø2.3) 0215700000 50
PS 2.3 0180400000 20

Q 2 1312500000 50
Q 3 1312600000 50
Q 4 1312700000 50
Q 10 1313100000 20
Q 20 1399800000 20

QL 2 0297200000 100
VH 4.2 1345800000 100
VQB1.5/50 BL 1633280000 5
VQB1.5/50 RT 1633290000 5
VQB1.5/50 SW 1635120000 5

WT 4 1341060000 100
SF 10 0332400000 1000
SG 10 0332500000 1000
ADP 0485400000 20
HP 4 0485860000 20


DEK 8	see "Accessories"
-------	-------------------

¹⁾ If the cross-connection runs via the PE connection of the DLA or if a pole is generally skipped, nominal voltage is reduced to 30 V~
²⁾ StB 8.5 only in upper busbar


³⁾ Upper busbar

Feed-through terminals for initiators and actuators


VLI 1.5



VLI 1.5PE



MAK 2.5



Dimensions/approvals

Width/length/height (mm)	with TS 35 x 7.5
Insulation stripping length/clamping screw/screwdriver blade	



6/79/64
8 mm/M 2.5/3.5 x 0.6



6/69/63
8 mm/M 2.5/3.5 x 0.6



6/88/64
8 mm/M 2.5/3.5 x 0.6

Rated data IEC 60 947-7-1

Rated voltage/current/cross-section

250 V/17.5 A/1.5 mm²

250 V/17.5 A/1.5 mm²

500 V (L-L)/250 V (L-PE)/ 24 A/2.5 mm²

Rated impulse voltage/pollution severity

4 kV/3

4 kV/3

6 kV/3

Further technical data

Tightening torque range	Nm
Torque setting with DMS 2 electric screwdriver	

0.4...0.6^{d)}
1

0.4...0.6
1

0.4...0.6
1

Clampable conductors

Solid H07V-U	mm ²
Stranded H07V-R	mm ²
Flexible H07V-K	mm ²
Flexible H07V-K and ferrule acc. to DIN 46 228/1	mm ²
Flexible H07V-K and ferrules with plastic insul. collar	mm ²
Gauge pin acc. to IEC 60 947-7-1	Size
Continuous current of terminal for conductor size	
Cont. current of cross-connect. , multi-pole	A

0.5...4.0
0.5...2.5
0.5...2.5
0.5...2.5
0.5...2.5
A3
24 A/2.5 mm²
24

0.5...4.0
0.5...2.5
0.5...4
0.5...2.5
0.5...2.5
A3
24 A/2.5 mm²
24

0.5...4.0
0.5...2.5
1.5...4
0.5...2.5
0.5...2.5
A3
31 A/4 mm²
24

UL/CSA rated data

Voltage/current/conductor size	UL
Voltage/current/conductor size	CSA

300 V/10 A/26...12 AWG
300 V/10 A/26...12 AWG

300 V/10 A/26...12 AWG
300 V/10 A/26...12 AWG

300 V/10 A/22...12 AWG
300 V/10 A/22...12 AWG

Ordering data

Version
Wemid

	Cat. No.	Qty.
	1784120000	50

	Cat. No.	Qty.
	1784130000	50

	Cat. No.	Qty.
	7917030000	50

	7917020000	50
--	-------------------	----

End plate/partition

End plate
Partial end plate for VLI1.5 – MAK2.5 combination
Partial end plate for VLI1.5 – VLI1.5PE combination
Partial end plate for VLI1.5PE – MAK2.5 combination

Type	Cat. No.	Qty.
AP VLI1.5	1784150000	20
TEAP2 MAK2.5	1782950000	20
TEAP VLI1.5	1784170000	20

Type	Cat. No.	Qty.
AP VLI1.5/PE	1784160000	20
TEAP VLI1.5	1784170000	20
TEAP1 MAK2.5	1782940000	20

Type	Cat. No.	Qty.
AP MAK2.5	7917000000	20
TEAP2 MAK2.5	1782950000	20
TEAP1 MAK2.5	1782940000	20

Cross-connection

VQB 50-pole, snap-fit, external cross-connection



QB 25-pole external cross-connection

VQB1.5/50BL ¹⁾	1633280000	5
VQB1.5/50RT ¹⁾	1633290000	5
VQB1.5/50SW ¹⁾	1635120000	5

VQB1.5/50BL ¹⁾	1633280000	5
VQB1.5/50RT ¹⁾	1633290000	5
VQB1.5/50SW ¹⁾	1635120000	5


VQB1.5/50BL ¹⁾	1633280000	5
VQB1.5/50RT ¹⁾	1633290000	5
VQB1.5/50SW ¹⁾	1635120000	5
QB 25 SW ¹⁾	0520000000	20
QB 25 RT ¹⁾	0520060000	20
QB 25 BL ¹⁾	0520080000	20

Group marking

Tag carrier
for S 10 markers

Marking tags

Print



FW/FS/...

T 5	0348500000	100
SF 10	0332400000	1000
SG 10	0332500000	1000
DEK 5	see "Accessories"	

T 5	0348500000	100
SF 10	0332400000	1000
SG 10	0332500000	1000
DEK 5	see "Accessories"	

T 5	0348500000	100
SF 10	0332400000	1000
SG 10	0332500000	1000
DEK 5	see "Accessories"	

Mounting rails, end brackets, further marking materials see "Accessories"

¹⁾ When using cross-connection bridges, the connection cross-section is reduced by one level.

Feed-through terminals

WMA 4/4 WMA 4/5



WDK 2.5 D WDK 2.5 D GET.SCH.

Terminals for incorporating electronic components



WDU 240



Max. technical data

Dimensions / approvals

Width/length/height (mm) with TS 35 x 7.5

Insulation stripping length/clamping screw/screwdriver blade

VDE rated data 0611 Part 1/8.92/IEC 60 947-7-1

Rated voltage/current/cross-section

Rated impulse voltage/pollution severity

Further technical data

Tightening torque range Nm

Torque setting with DMS 2 electric screwdriver

Clampable conductors

Solid H07V-U mm²

Stranded H07V-R mm²

Flexible H07V-K mm²

Flexible H07V-K and ferrule acc. to DIN 46 228/1 mm²

Flexible H07V-K and ferrules with plastic insul. collar mm²

Max. clamping range in mm²/Gauge pin acc. to IEC 60 947-7-1 Size

Cont. current of cross-connect. WQV/ZQV 2-5-pole A

Cont. current of cross-connect. WQV/ZQV 6-10-pole A

UL/CSA rated data

Voltage/current/conductor size UL

Voltage/current/conductor size CSA

Ordering data

Version

Motor connection block (L1, L2, L3, PE) Wemid

Motor connection block (L1, L2, L3, N, PE) Wemid

Dark beige Wemid

Blue Wemid

End plate/partition



WAP (thickness 1.5 mm)

WTW

Dark beige Wemid


Blue Wemid

Dark beige Wemid

Blue Wemid

Frame (5 mm)

Cross-connection



WQB 12/24

WQB 240/3

2-pole

LGB 240/3 3-pole

4-pole

5...9-pole

10-pole

41-pole

Cross-connection comb

LS 2.8

Screening bar

Notching tool

Test adapter / strain relief / compensating terminals



WTA

Strain relief

Compensating terminal

Test plug/socket/hexagon wrench

PS 2.3 Test plug (ø2.3 mm)

StB 8.5 Test socket screw 8.5 (ø2.3)

SK wrench

Covers



With symbol

White

WAD for self-labelling/white

Group marking



WGB

T5

Tag carrier for S 10 markers

Marking tags

Print



DEK

WS

DEK Standard

WS white neutral

WS indiv. printed

Mounting rails, end brackets, further marking materials see "Accessories"

¹⁾ Ferrules with optimum diam. for terminals with 5 mm pitch: Cat. No. **1333100000**

²⁾ Screws with hexagonal socket

41 A/6 mm²

24.5(30.6)/60/47

10 mm/M 3/3.5 x 0.6

800 V/32 A/4 mm²

8 kV/3

0.5...1.0

2

0.5...6

1.5...6

0.5...6

0.5...4

0.5...4

0.13...6 A 4

41/32

41/32

WMA 4/4 **1034000000** 20

WMA 4/5 **1033800000** 20

Type Cat. No. Qty.

WAP 2.5-10 **1050000000** 50

WAP 2.5-10 **1050080000** 50

WTW 2.5-10 **1050100000** 20

WTW 2.5-10 **1050180000** 20

ZQV4N Qty. WQV Qty.

1758250000 60 **1051960000** 50

1762630000 60 **1054560000** 50

1762620000 60 **1054660000** 50

ZQV see p. 263 / WQV see p. 262

1758260000 20 **1052060000** 20

1758270000 10 (41-pole)

LS 2.8³⁾ **1056400000** 50

WAW 1 **9004500000** 1

WTA 3 **1632350000** 50

WTA 3/ZA **1632360000** 50

WTA 3/10 **1632370000** 5

Strain relief ZE 1 **1632150000** 50

PS 2.3(ø2.3) **0180400000** 20

StB 8.5(ø2.3) **0280600000** 50

WAD 5 **1053460000** 50

WAD 5 white **1056060000** 50

WGB 5 **1050760000** 50

T 5 **0348500000** 100

SF 10 **0332400000** 1000

SG 10 **0332500000** 1000

DEK 6 see "Accessories"

WS 12/6 **1609900000** 600

WS 12/6 **1609910000** 120

-/2.5 mm²

5/69/63

10 mm/M 2.5/3.5 x 0.6

-/2.5 mm²

0.4...0.6

1

0.5...4

1.5...4

0.5...2.5

0.5...2.5

0.5...2.5¹⁾

0.13...4 A 3

300 V/20 A/22...12 AWG

Type Cat. No. Qty.

1023200000 100

With divided busbar (bottom)

1023100000 100

Type Cat. No. Qty.

WAP **1059100000** 20

WAP **1059180000** 20

WTW **1058800000** 20

WDK 2.5 **1074000000** 20

Type Cat. No. Qty.

WQV 2.5/2 **1053660000** 50

WQV 2.5/3 **1053760000** 50

WQV 2.5/4 **1053860000** 50

see p. 262

WQV 2.5/10 **1054460000** 20

WQB A/24 **1579000000** 20

LS 2.8³⁾ **1056400000** 50

WAW 1 **9004500000** 1

TA 1 0535860000 20

PS 2.3(ø2.3) **0180400000** 20

StB 8.5(ø2.3) **0215700000** 50

ADP 3 **0485400000** 20x1m

HP 3 **0485760000** 20

WAD 4 **1072000000** 50

WT 4 **1341060000** 100

SF 10 **0332400000** 1000

SG 10 **0332500000** 1000

DEK 5 see "Accessories"

WS 8/5 **1640740000** 720

WS 8/5 **1773360000** 300

³⁾ When using the screening bar, rated voltage is reduced to 400 V!

415 A/2.5 mm²

36/100/131.5

40 mm/M 10²/-

1000 V/415 A/240 mm²

8 kV / 3

25...30

-

70...240

70...240

70...240

70...185

70...185

B 15 / A 15

382

382

600 V/380 A/500 MCM

600 V/400 A/1/0 AWG-500 MCM

Type Cat. No. Qty.

1802780000 2

Type Cat. No. Qty.

WQB 240/2 **1802780000** 20


WQB 240/3 **1802800000** 20

Comp. terminal WZAD 240 **1802810000⁴⁾** 1

SK **0235000000** 1

DEK 5 see "Accessories"

W-series terminals with clamping yoke and tension clamp



Note:

The insulation stripping length of the connection conductor is pre-defined. We advise to use hook-shaped cable lugs which are recommended by the relevant cable lug manufacturers. In this case, rated voltage is 250 V. If an end plate is inserted, rated voltage is 400 V.

Dimensions/approvals	
Width/length/height (mm)	with TS 35 x 7.5
Width/length/height (mm)	
Insulation stripping length/clamping screw/screwdriver blade	

Rated data	
Rated voltage/current/cross-section	
Rated impulse voltage/pollution severity	

Further technical data	
Tightening torque range	Nm
Torque setting with DMS 2 electric screwdriver	

Clampable conductors	
Solid H07V-U	mm ²
Stranded H07V-R	mm ²
Flexible H07V-K	mm ²
Max. clamping range in mm ² /Gauge pin acc. to IEC 60 947-7-1 Size	

Hook-shaped cable lugs acc. to ESI 50-18 Part 2	
Size 2 (x = 3 mm)	2 pieces
Size 1 (x = 4.6 mm)	2 pieces

Ordering data	Version
	Dark beige Wemid
	Dark beige Wemid
	PA 66 black
	PA 66 black

UL/CSA rated data	
Voltage/current/conductor size	UL
Voltage/current/conductor size	CSA

Hook-shaped cable lugs	
0.25–1.5 mm ² black	
1.25–2.5 mm ² black	

End plate/partition			
WAP	WTW	Wemid	
	Thickness	Wemid	
	1.5 mm	Black Wemid	
Thickness 1.5 mm		Black Wemid	

Cross-connection	
	WQV
	ZQV

Test adapter	
WTA 5	WTA 3


Test plug/socket	
PS 2.3	StB 8.5
	

Cover	
WAD with symbol	
WAD white	
Group marking	
WGB	
T 5	
Tag carrier	
for S 10 markers	

Marking tags	Print
	DEK Standard
	WS white neutral
	WS WS indiv. printed

Mounting rails, end brackets, further marking materials see "Accessories"

WDU 4 SL



UL/CSA	
6/60/47	
6/60/52	
15 mm/M 3/3.5 x 0.6	

IEC	
500 V/32 A/4mm ²	
6 kV/3	

0.5...1	
2	

Clampable conductors	
0.5...6	
1.5...6	
0.5...4	
0.13...6	A4

0.28...1.5	
------------	--

IEC	Qty.
9537440000	50
9537450000	50
9537500000	50
9537510000	50

600 V/30 A/22...10	
300 V/25 A/22...10	

9036290000	100
------------	-----

Type	Cat. No.	Qty.
WAP 2.5-10	1050000000	50
WTW 2.5-10	1050100000	20
WAP	1050010000	50
WTW	1050110000	20

WQV 4/2	1051960000	50
WQV 4/3	1054560000	50
WQV 4/4	1054860000	50
WQV 4/10	1052060000	20
WAW1	9004500000	1
ZQV 4N/2	1758250000	60
ZQV 4N/3	1762630000	60
ZQV 4N/4	1762620000	60
ZQV 4N/10	1758260000	20
ZQV 4N/41	1758270000	10

WTA 3	1632350000	50
WTA 3/ZA	1632360000	50
WTA 3/10	1632370000	5
ZE 1	1632150000	25

PS 2.3 (ø 2.3)	0180400000	20
StB 8.5 (ø 2.3)	0280600000	50


WAD 5	1053460000	50
WAD 5 white	1056060000	50

WGB 5	1050760000	50
T 5	0348500000	100
SF 10	0332400000	1000
SG 10	0332500000	1000

DEK 6	see "Accessories"	
WS 12/6	1609900000	600
WS 12/6	1609910000	120



WDU 6 SL



UL/CSA	
8/60/47	
8/60/52	
16 mm/M 3.5/4 x 0.8	

IEC	
500 V/24 A	
6 kV/3	

0.8...1.4	
3	

Clampable conductors	
0.5...10	
1.5...10	
0.5...6	
0.5...10	A4

0.28...1.5/1...2.5	
0.28...1.5/1...2.5	

ESI	IEC	Qty.
	9537460000	50
	9537470000	50
9537420000		50
9537430000		50

150 V/45 A/20...8	
300 V/45 A/20...8	

9036290000	100
9036300000	100

Type	Cat. No.	Qty.
WAP 2.5-10	1050000000	50
WTW 2.5-10	1050100000	20
WAP	1050010000	50
WTW	1050110000	2

WQV 6/2	1052360000	50
WQV 6/3	1054760000	50
WQV 6/4	1054860000	50
WQV 6/10	1052260000	20
WAW1	9004500000	1

WTA 5/1	1051260000	25
---------	------------	----


PS 2.3 (ø 2.3)	0180400000	20
PS 4 (ø 4)	0299600000	20
StB 8.5 (ø 2.3)	0280600000	50
StB 14 (ø 4)	0169900000	50

WAD 8	1053560000	50
WAD 8 white	1056160000	50

WGB 8	1050960000	50
T 5	0348500000	100
SF 10	0332400000	1000
SG 10	0332500000	1000

DEK 8	see "Accessories"	
WS 12/6.5	1609920000	540
WS 12/6.5	1609930000	108

WDU 10 SL



UL/CSA	
10/60/47	
10/60/52	
17 mm/M 4/5.5 x 1.0	

IEC	
500 V/36 A	
6 kV/3	

1.2...2.4	
4	

Clampable conductors	
1.5...16	
1.5...16	
1.5...10	
1.31...10	A5

0.28...1.5/1...2.5	
0.28...1.5/1...2.5	

ESI	IEC	Qty.
	9537480000	50
	9537490000	50
9537400000		50
9537410000		50

150 V/50 A/16...8	
300 V/65 A/16...6	

9036290000	100
9036300000	100

Type	Cat. No.	Qty.
WAP 2.5-10	1050000000	50
WTW 2.5-10	1050100000	20
WAP	1050010000	50
WTW	1050110000	20

WQV 10/2	1052560000	50
WQV 10/3	1054960000	50
WQV 10/4	1055060000	50
WQV 10/10	1052460000	20
WAW1	9004500000	1

WTA 5/1	1051260000	25
---------	------------	----

PS 2.3 (ø 2.3)	0180400000	20
PS 4 (ø 4)	0299600000	20
StB 8.5 (ø 2.3)	0280600000	50
StB 14 (ø 4)	0169900000	50

WAD 8	1053560000	50
WAD 8 white	1056160000	50

WGB 8	1050960000	50
T 5	0348500000	100
SF 10	0332400000	1000
SG 10	0332500000	1000

DEK 5	see "Accessories"	
WS 12/6.5	1609920000	540
WS 12/6.5	1609930000	108

W-series terminals with clamping yoke + spring

WTL 6 SL



WTD 6 SL



Dimensions/approvals

Width/length/height (mm)	with TS 35
Width/length/height (mm)	
Insulation stripping length/clamping screw/screwdriver blade	

Rated data

Rated voltage/current/cross-section	
Rated impulse voltage/pollution severity	

Further technical data

Tightening torque range	Nm
Torque setting with DMS 2 electric screwdriver	

Clampable conductors

Solid H07V-U	mm ²
Stranded H07V-R	mm ²
Flexible H07V-K	mm ²
Max. clamping range in mm ²	
Gauge pin acc. to IEC 60 947-1	

Hook-shaped cable lugs acc. to ESI 50-18 Part 2

Size 2 (x = 3 mm)	2 pieces
Size 1 (x = 4.6 mm)	2 pieces

UL/CSA rated data

Voltage/current/conductor size	UL
Voltage/current/conductor size	CSA

Ordering data

Version	
	Dark beige Wemid
	Dark beige Wemid
	Black PA 66
	Black PA 66

Hook-shaped cable lugs

0.25–1.5 mm ² black
1.25–2.5 mm ² black

End plate/partition



Dark beige Wemid
Black PA 66

Cross-connection



Test plug



Test socket screw

StB 25 GE	
StB 25 GN	
StB 25 VI	
StB 35 GE	
StB 35 GN	
StB 35 VI	
StB 14	

Disconnect lock

Marking tags



DEK	Standard
WS white	neutral
WS	indiv. printed

Print

DEK 8	see "Accessories"
WS 12/6.5	1609920000 540
WS 12/6.5	1609930000 108

Mounting rails, end brackets, further marking materials see "Accessories"

8/83/50
8/83/49
16 mm/M 3.5/4.0 x 0.8

ESI

500 V/24 A/6mm ²
6 kV/3

0.8...1.4
3

0.5...10
1.5...10
0.5...6
0.5...10
A4

0.28...1.5/1...2.5
0.28...1.5/1...2.5

Type	Cat. No.	Qty.
WTL 6 SL	9538070000	50
WTL 6 SL	9538080000	50
WTL 6 SL	9538020000	50
WTL 6 SL	9538030000	50

9036290000
9036300000

WAP	9538110000	20
WAP	9538060000	20

QL2	0194300000	50
QL3	0194400000	50
QL4	0194500000	50
QL10	0338300000	20
QVS	0292500000	100
VH 19	0318000000	100
QVS 2	0307300000	20
QVSK 2	1670360000	20
QVS 3	0329300000	20
QVS 4	0307400000	20

PS 4	0299600000	20
------	------------	----

StB 25 GE	0267200000	50
StB 25 GN	0271200000	50
StB 25 VI	0271300000	50
StB 35 GE	0389000000	50
StB 35 GN	0388900000	50
StB 35 VI	0389100000	50
StB 14	0169900000	50

SSP 3	0531760000	100
-------	------------	-----

8/83/50
8/83/49
16 mm/M 3.5/4.0 x 0.8

ESI

500 V/24 A/6mm ²
6 kV/3

0.8...1.4
3

0.5...10
1.5...10
0.5...6
0.5...10
A4

0.28...1.5/1...2.5
0.28...1.5/1...2.5

Type	Cat. No.	Qty.
WTD 6 SL	9538090000	50
WTD 6 SL	9538100000	50
WTD 6 SL	9538040000	50
WTD 6 SL	9538050000	50

9036290000
9036300000

WAP	9538110000	20
WAP	9538060000	20

QL 2	0194300000	50
QL 3	0194400000	50
QL 4	0194500000	50
QL 10	0338300000	20
QVS	0292500000	100
VH 19	0318000000	100
QVS 2	0307300000	20
QVSK 2	1670360000	20
QVS 3	0329300000	20
QVS 4	0307400000	20

PS 4	0299600000	20
------	------------	----

StB 25 GE	0267200000	50
StB 25 GN	0271200000	50
StB 25 VI	0271300000	50
StB 35 GE	0389000000	50
StB 35 GN	0388900000	50
StB 35 VI	0389100000	50
StB 14	0169900000	50

SSP 3	0531760000	100
-------	------------	-----

DEK 8	see "Accessories"
WS 12/6.5	1609920000 540
WS 12/6.5	1609930000 108

W-series terminals with clamping yoke + spring

WTR 4 SL



WTR 4 SI SL



Dimensions/approvals

Width/length/height (mm)	with TS 35
Width/length/height (mm)	
Insulation stripping length/clamping screw/screwdriver blade	



6/60/47

12.5/M3/3.5 x 0.6



6/60/52

12.5/M3/3.5 x 0.6

Rated data

Rated voltage/current/cross-section	
Rated impulse voltage/pollution severity	

500 V/24 A/4mm²
6 kV/3

400 V/6.3³⁾ A/4mm²
6 kV/3

Further technical data

Tightening torque range	Nm
Torque setting with DMS 2 electric screwdriver	

0.5...1
2

0.5...1
2

Clampable conductors

Solid H07V-U	mm ²
Stranded H07V-R	mm ²
Flexible H07V-K	mm ²
Max. clamping range in mm ²	
Gauge pin acc. to IEC 60 947-1	

0.5...6
1.5...4
0.5...4
0.13...6
A4

0.5...6
1.5...4
0.5...4
0.13...6
A4

Hook-shaped cable lugs acc. to ESI 50-18 Part 2

Size 2 (x = 3 mm)	2 pieces
Size 1 (x = 4.6 mm)	2 pieces

0.28...1.5/1...2.5

0.28...1.5/1...2.5

UL/CSA rated data

Voltage/current/conductor size	UL
Voltage/current/conductor size	CSA

300 V/22 A/22...10 AWG
300 V⁴⁾/24 A/22...10 AWG

300 V/6.3 A/22...12 AWG
300 V/6.3 A/22...10 AWG

Ordering data

Version
 Dark beige Wemid
 Blue Wemid
 Black PA 66
  Dark beige Wemid
  Blue Wemid
  Black PA 66

	With StB.2.3	Without StB	Qty.
WTR 4 SL	7910300000	7910270000	50
WTR 4 SL	7910310000	7910280000	50
WTR 4 SL	7910320000	7910290000	50
WTR 4 SL	7910390000	7910360000	50
WTR 4 SL	7910400000	7910370000	50
WTR 4 SL	7910410000	7910380000	50

	Without StB	Qty.
WTR 4 SI SL	7910330000	50
WTR 4 SI SL	7910350000	50
WTR 4 SI SL	7910420000	50
WTR 4 SI SL	7910440000	50


Hook-shaped cable lugs

0.25–1.5 mm² black

9036290000

9036290000

End plate/partition

	Dark beige Wemid
	Black PA 66
	Blue Wemid
WAP	Dark beige Wemid
WTW	Dark beige Wemid

WAP	1050000000	50
WAP	1050010000	50
WAP	1050080000	50
WTW	1050100000	20

WAP	1050000000	50
WAP	1050010000	50
WAP	1050080000	50
WTW	1050100000	20

Cross-connection

ZQV	2-pole
	3-pole
	4-pole
	10-pole
	41-pole
	neutral



ZQV 4N/2	1758250000	60
ZQV 4N/3	1762630000	60
ZQV 4N/4	1762620000	60
ZQV 4N/10	1758260000	20
ZQV 4N/41	1758270000	10
QB 75/6.2/15	0535200000	10
ISPF QB75 SW	0526700000	10
ISPF QB75 BL	0526780000	10
ISPF QB75 RT	0526760000	10

ZQV 4N/2	1758250000	60
ZQV 4N/3	1762630000	60
ZQV 4N/4	1762620000	60
ZQV 4N/10	1758260000	20
ZQV 4N/41	1758270000	10
QB 75/6.2/15	0535200000	10
ISPF QB75 SW	0526700000	10
ISPF QB75 BL	0526780000	10
ISPF QB75 RT	0526760000	10

Test plug

PS 2.3	
Test adapter 	WTA 6

	0180400000	20
	1632380000	25

	0180400000	20
	1632380000	25

Fuse holder

for 5x20 SIHA

	SIHA 2/G 20	400 V~
	SIHA 2/G 20	12 V-/24 V~
	SIHA 2/G 20	20-30 V-/40-60 V~
	SIHA 2/G 20	40-60 V-/80-220 V~
	SIHA 2/G 20	115 V-/230 V~

	9537600000	25
	9537610000	25
	9537620000	25
	9537630000	25
	9537640000	25

Marking tags

	DEK	Standard
	WS white	neutral
	WS	indiv. printed

DEK 6	see "Accessories"	
WS 12/6	1609900000	600
WS 12/6	1609910000	120

DEK 6	see "Accessories"	
WS 12/6	1609900000	600
WS 12/6	1609910000	120

Mounting rails, end brackets, further marking materials see "Accessories"

³⁾ Maximum power loss 1.6 W

⁴⁾ With WAP or WTW 600V/22 A

Terminals with electronic components

Incorporating electronic components into a terminal makes the connection point an active part of the installation. The unused space within a terminal can be sensibly used for signal indication, for suppressing sparks, or for signal conditioning. Weidmüller's range principally covers

Terminals with indicator

to display the switching state, signals and the operating voltage. This indication simplifies the start-up process, monitoring, servicing and repairs of the installation.


The range of terminals covers double-deck terminals for voltage/current monitoring, fuse terminals with outage display and disconnect test terminals for signalling disconnections.

Various coloured LEDs, glow lamps (low consumption) or regular bulbs are used for signal indication.

Typical applications are:

• Monitoring a ventilator motor


Displaying the current flow slows the operating status of the ventilator.



Typical example:

• Protecting a power supply

A lit LED shows a tripped fuse, whereby a small residual current is flowing through the terminal.



A status display without residual current is provided by the EGS fuse component.


Terminal with diode

for suppressing inductivity or for linking signals.

Typical example:

• Eliminating sparks on switching a DC valve

The electromagnetic energy stored in the coil fades through the diode on opening the contact.




Typical example:

• Protecting contacts on switching an inductive AC load

A varistor limits the peak voltage on switching off the load.


This prevents arcing and related burning of contacts.



Typical example:

• Test switch for LED display panels

The primary resistors for the LEDs are integrated into the terminal. Two diodes decouple control and test signals.




Compensating terminals

In measurement, control and regulation technology various cable lengths and tolerances in the sensors necessitate matching of the circuits.


For this, we offer a combination of terminal and potentiometer an: Type SAKL 4.

Typical example:

• Temperature measurement




A further variation provides a **voltage distributor** in a terminal.



Terminals with indicator


WDK 2.5 LD

Direct **voltage** indicator




WDK 2.5 LD

Direct **voltage** indicator




WDK 2.5 LD

Direct **voltage** indicator




WDK 2.5 LD

Alternating **voltage** indicator



WDK 2.5 GL

Alternating **voltage** indicator




Dimensions	mm				
Length	69	69	69	69	69
Height (incl. TS 35x7.5)	63	63	63	63	63
Terminal width					
(+ assembly tolerance 0.2)	5	5	5	5	5
Insulation stripping length	10	10	10	10	10
Connection data					
Screw connection, flexible	0.5...2.5 mm ²	0.5...2.5 mm ²	0.5...2.5 mm ²	0.5...2.5 mm ²	0.5...2.5 mm ²
Conductor cross-connection	AWG 26...12	AWG 26...12	AWG 26...12	AWG 26...12	AWG 26...12
VDE rated data					
Current of through-busbar	10 A	10 A	10 A	10 A	10 A
Cross-section	2.5 mm ²	2.5 mm ²	2.5 mm ²	2.5 mm ²	2.5 mm ²
LED current	< 5 mA	< 5 mA	< 5 mA	< 5 mA	< 5 mA

Terminals with diodes

(Other versions on request)


WDK 2.5 D

Diode terminal, e.g. reverse polarity protection




WDK 2.5 D

Arc suppression circuit for contactors and solenoid valves (DC voltage)



WDK 2.5 D

Arc suppression circuit for contactors and solenoid valves (DC voltage)




Dimensions								
Length	mm	69	69	69				
Height (incl. TS 35x7.5)	mm 	63	63	63				
Terminal width (+ assembly tolerance 0.2)	mm	5	5	5				
Insulation stripping length	mm	10	10	10				
Connection data								
Screw connection, flexible		0.5...2.5 mm²	0.5...2.5 mm²	0.5...2.5 mm²				
Conductor cross-connection		AWG 26...12	AWG 26...12	AWG 26...12				
VDE rated data								
Voltage		380 V~	380 V~	380 V~				
Diode reverse voltage		1000 V	1000 V	1000 V				
Diode current		1 A	1 A	1 A				
Current of through-busbar		10 A	10 A	10 A				
Diode		1 N 4007	1 N 4007	1 N 4007				
Terminal colour								
		Dark beige Wemid	Dark beige Wemid	Dark beige Wemid				
Ordering data		Type	Cat. No.	Type	Cat. No.			
		WDK 2.5 D	8025610000	WDK 2.5 D	1023400000			
Accessories		Type	Cat. No.	Qty.	Type	Cat. No.	Qty.	
Mounting rail (length 2 m)		TS 35 x 7.5	0383400000	2 m	TS 35 x 7.5	0383400000	2 m	
		slotted	0514500000	2 m	slotted	0514500000	2 m	
		TS 35 x 15	0498000000	2 m	TS 35 x 15	0498000000	2 m	
End bracket								
EW 35 (thickness 8.5 mm)		EW 35 (8.5)	0383560000	50	EW 35 (8.5)	0383560000	50	
End plate								
WAP (thickness 1.5 mm)		WAP	1059100000	100	WAP	1059100000	100	
Cross-connection (pre-assembled)								
2-pole		WQV 2.5	1053660000	50	WQV 2.5	1053660000	50	
3-pole		WQV 2.5	1053760000	50	WQV 2.5	1053760000	50	
4-pole		WQV 2.5	1053860000	50	WQV 2.5	1053860000	50	
10-pole		WQV 2.5	1054460000	50	WQV 2.5	1054460000	50	
Marking tags		Print						
		DEK	Standard	DEK 5	see "Accessories"	DEK 5	see "Accessories"	
		WS white	neutral	WS 8/5	1640740000	720	WS 8/5	1640740000
		WS	indiv. printed	WS 8/5	1773360000	300	WS 8/5	1773360000
Mounting rails, end brackets, further marking materials see "Accessories"								

Terminals with diodes


WDK 2.5 D

Diode terminal for lamp test circuits




WDK 2.5 D

Diode terminal for lamp test circuits



WDK 2.5 D


Diode terminal for lamp test circuits

[illegible]


(Other versions on request)

Diode terminal for lamp test circuits, with series resistor

Diode terminal for lamp test circuits, with series resistor

56 **Weldmüller** 

WDUL 4/...



Dimensions					
Length	mm	60			
Height (incl. TS 35 x 7.5)	mm	47			
Terminal width (+ assembly tolerance 0.2)	mm	6			
Insulation stripping length	mm	9/10			
Connection data					
Screw connection, solid		0.5...4 mm ²			
Screw connection, flexible		0.5...4 mm ²			
Conductor cross-connection		AWG 22...12			
VDE rated data					
Power		1 W			
Cross-section		4 mm ²			
Ordering data		Type	Cat. No.	Qty.	
Resistance	10 Ω	WDUL 4/10	1027000000	10	
	30 Ω	WDUL 4/30	1027100000	10	
	50 Ω	WDUL 4/50	1027200000	10	
	100 Ω	WDUL 4/100	1027300000	10	
	500 Ω	WDUL 4/500	1027400000	10	
	1 kΩ	WDUL 4/1K	1027500000	10	
	5 kΩ	WDUL 4/5K	1027600000	10	
	10 kΩ	WDUL 4/10K	1027700000	10	
	50 kΩ	WDUL 4/50K	1027800000	10	
	100 kΩ	WDUL 4/100K	1027900000	10	
	500 kΩ	WDUL 4/500K	1028000000	10	
	2 MΩ	WDUL 4/2M	1028100000	10	
		WDUL 4	8161820000	10	
		(without potentiometer)			
Accessories					
Mounting rail (length 2 m)		TS 35	0383400000	–	
End bracket (thickness mm)		EW 35 (8.5)	0383560000	50	
End plate (thickness mm)		WAP 2.5-10	1050000000	50	
Partition (thickness mm)		TW PA (1.5)	1050100000	20	
Screening bar		LS 2.8	1056400000	100	
Solder lug					

Technical data for the 30 Ω compensation resistor

Resistor material: "Cermet"

Resistor setting range: 0...30 Ω

Curve form: linear

Temperature coefficient: ± 100 ppm/°C

Mechanical service life: 200 actuations without permissible deviations throughout the entire resistance range

Resistance change per spindle turn: ≈ 1.2 Ω

Rated output for total resistance: 1 W at 70 °C

Rated current: 120 mA


Ambient temperature: –55 °C to +70 °C

Sealing:

1) Leak-tested in water with 70 °C without foaming

2) Storage in SFW 2.0 S acc. to DIN 50018, 9 cycles

Capacity in % of the
rated output



Ambient temperature in °C