




PRODUCT NO
SEE TABLE



mat'l. code				surface		tolerance		projection		product family			
				ISO 1302 ✓		ISO 406 ISO 1101				LATCH-N-LOK			
ltr	ecn	nodr	date	tolerances unless otherwise specified						title			
C	V00432	TFG	2/22/00	angles	linea	XXX±.01/0.XX±0.3		INCH/MM		2X3 LNL LOW PROFILE HEADER ASSEMBLY			
D	V01703	TFG	7/21/00			XXX±.005/0.XXX±0.13							
E	V10987	TFG	2/27/01			XXX±.0020/0.XXX±0.05							
F	M05-0050	MHT	3/16/05	dr	N. CORNMAN	6/25/90				dwg no		sheet 1 of 2	size
G	M06-0365	AGS	9/20/06	engr	D. HORCHLER	6/25/90				78097		A3	
H	M09-0048	MHT	3/12/09	chr	D. HORCHLER	6/25/90				type Product Customer Drawing			
J	BLX-N-00452	ZK	11/28/11	app	D. HORCHLER	6/25/90							
sheet		revision		J	J								
index		sheet		1	2								

PDS: Rev :J

STATUS: Released

Printed: Dec 27, 2011


78097-XXXXLF

LEAD FREE OPTION ⑥ ⑦

	COLOR ④	
1	70343 LT GRAY	OBS
2	80166 OFF WHITE	
3	70634 DK GRAY	OBS
4	701 BLACK	
5	70514 SLATE GRAY	OBS
7	70455 SILVER GRAY	
8	80189 PEARL WHITE	OBS
9	70419 PEBBLE GRAY	

	PLATING ③
0	30u" MIN OVER 50u"MIN Ni
3	30u" MIN OVER 50u"MIN Ni
5	50u" MIN OVER 50u"MIN Ni

	PIN LENGTH
	DIM L
0	.200/5.08
1	.130/3.30



RECOMMENDED PCB LAYOUT

NOTES:

- HEADER SHROUD
MAT'L: HIGH TEMPERATURE THERMOPLASTIC,
UL-94V-0 RATED.
- GROUND CONTACT
MAT'L: COPPER ALLOY
PLATING: 100-160u"/2.54-4.06u TIN.
- SIGNAL CONTACT
MAT'L: COPPER ALLOY
PLATING OPTION: PERFORMANCE PLATING WILL BE EITHER GOLD OR GXT
ON CONTACT AREA OR TAIL, OPTIONALLY (78-295u") TIN ON TAIL.
- NUMBERS SHOWN ARE FOR G.E. LEXAN AND
ARE FOR REFERENCE ONLY.
- THIS ASSEMBLY U.L. APPROVED PER FILE E66906 VOL. 1, SEC. 84
AND CSA APPROVED PER MASTER FILE LR46923.
- ADD LF SUFFIX AT THE END OF PART NUMBER FOR LEAD FREE OPTION.
- THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE
FOR 15 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.5mm
MINIMUM THICK CIRCUIT BOARD. SEE APPLICATION NOTES/PROCEDURES
IF THEY ARE AVAILABLE.
- THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER
COUNTRY REGULATION AS DESCRIBED IN GS-22-008.
- PRODUCT SPEC: GS-12-003

mat'l. code		surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection INCH/MM		product family LATCH-N-LOK	
ltr ecn nodr date		tolerances unless otherwise specified		title		dwg no		sheet 2 of 2 size	
J		angles	linea	2X3 LNL LOW PROFILE HEADER ASSEMBLY		78097		A3	
		0°±2°		scale 1:1					
		dr	N. CORNMAN	6/25/90					
		engr	D. HORCHLER	6/25/90					
		chr	D. HORCHLER	6/25/90					
		appd	D. HORCHLER	6/25/90					
sheet index		revision sheet							