



D (SEE NOTE 6)


.025
0.64 SQ TYP



PCB LAYOUT: COMPONENT SIDE
RECOMMEND PCB THICKNESS: .062/1.57

CKTS	A	B	C
02	.262 6.65	NA	.236 6.00
04	.380 9.65	.118 3.00	.354 9.00
06	.498 12.65	.236 6.00	.472 12.00
08	.616 15.65	.354 9.00	.591 15.00
10	.734 18.65	.472 12.00	.709 18.00
12	.852 21.65	.591 15.00	.827 21.00
14	.970 24.65	.709 18.00	.945 24.00
16	1.088 27.65	.827 21.00	1.063 27.00
18	1.206 30.65	.945 24.00	1.181 30.00
20	1.325 33.65	1.063 27.00	1.299 33.00
22	1.443 36.65	1.181 30.00	1.417 36.00
24	1.561 39.65	1.299 33.00	1.535 39.00

NOTE : (2) POLARIZATION PEGS ARE SHOWN.
HOWEVER, ASSEMBLIES MAY BE MANUFACTURED
WITH (1) PEG ONLY.




CIRCUIT "1" IDENTIFIED ON THIS SURFACE
(APPROX. LOCATION SHOWN FOR REF.)

NOTES:

- HOUSING MATERIAL: GLASS FILLED LIQUID CRYSTAL POLYMER, UL94V-0, COLOR-BLACK
TERMINAL MATERIAL: BRASS ALLOY
- FINISH: A = .000100/(0.00254) MIN. TIN OVER
.000050/(0.00127) MIN. NICKEL PLATE.
B = .000015/(0.00038) MIN. SELECT GOLD IN CONTACT AREA,
.000100/(0.00254) MIN. SELECT MATTE TIN ON SOLDER TAILS,
BOTH OVER .000050/(0.00127) MIN. NICKEL PLATE.
C = .000030/(0.00076) MIN. SELECT GOLD IN CONTACT AREA,
.000100/(0.00254) MIN. SELECT MATTE TIN ON SOLDER TAILS,
BOTH OVER .000050/(0.00127) MIN. NICKEL PLATE.
D = .000100/(0.00254) MIN. MATTE TIN OVER
.000050/(0.00127) MIN. NICKEL PLATE.
- PRODUCT SPECIFICATION: PS-43045
- TRAY PACKAGED: SEE MOLEX DRAWING PK-70873-0314
- MATES WITH MICRO FIT (3.0) RECEPTACLE SERIES 43025
- CIRCUIT SIZES 2-6: "D" IS .265/6.74 FOR .010/0.25 STEP
CIRCUIT SIZES 8-24: "D" IS .063/1.60 FOR .010/0.25 STEP.
- THIS PART CONFORMS TO CLASS B REQUIREMENTS OF COSMETIC SPECIFICATION
PS-45499-002.

	FINISH A	FINISH B	FINISH C	FINISH D
CKTS	MATERIAL NO:	MATERIAL NO:	MATERIAL NO:	MATERIAL NO:
02	43045-0227	43045-0228	43045-0229	43045-0298
04	43045-0427	43045-0428	43045-0429	43045-0498
06	43045-0627	43045-0628	43045-0629	43045-0698
08	43045-0827	43045-0828	43045-0829	43045-0898
10	43045-1027	43045-1028	43045-1029	43045-1098
12	43045-1227	43045-1228	43045-1229	43045-1298
14	43045-1427	43045-1428	43045-1429	43045-1498
16	43045-1627	43045-1628	43045-1629	43045-1698
18	43045-1827	43045-1828	43045-1829	43045-1898
20	43045-2027	43045-2028	43045-2029	43045-2098
22	43045-2227	43045-2228	43045-2229	43045-2298
24	43045-2427	43045-2428	43045-2429	43045-2498



ADD FINISH "D" EC NO: UCP2013-1199 2012/10/01 DRAWN: NGUYEN CHKD: SSOUSEK APPR: FSLTH 2012/10/12	QUALITY SYMBOLS  =0  =0  =0	GENERAL TOLERANCES (UNLESS SPECIFIED) <table><tr><th></th><th>mm</th><th>INCH</th></tr><tr><td>4 PLACES</td><td>± ---</td><td>± ---</td></tr><tr><td>3 PLACES</td><td>± ---</td><td>± .010</td></tr><tr><td>2 PLACES</td><td>± 0.25</td><td>± .014</td></tr><tr><td>1 PLACE</td><td>± 0.36</td><td>± ---</td></tr><tr><td>0 PLACE</td><td>±</td><td></td></tr><tr><td colspan="3">ANGULAR ±1/2°</td></tr><tr><td colspan="3">DRAFT WHERE APPLICABLE</td></tr><tr><td colspan="3">MUST REMAIN WITHIN DIMENSIONS</td></tr></table>		mm	INCH	4 PLACES	± ---	± ---	3 PLACES	± ---	± .010	2 PLACES	± 0.25	± .014	1 PLACE	± 0.36	± ---	0 PLACE	±		ANGULAR ±1/2°			DRAFT WHERE APPLICABLE			MUST REMAIN WITHIN DIMENSIONS			DIMENSION STYLE IN/MM <table><tr><td>DRAWN BY</td><td>DATE</td></tr><tr><td>SAMIEC</td><td>2000/03/15</td></tr><tr><td>CHECKED BY</td><td>DATE</td></tr><tr><td>MUELLER</td><td>2000/03/15</td></tr><tr><td>APPROVED BY</td><td>DATE</td></tr><tr><td>EDGELY</td><td>2000/03/15</td></tr><tr><td>MATERIAL NO.</td><td></td></tr></table>	DRAWN BY	DATE	SAMIEC	2000/03/15	CHECKED BY	DATE	MUELLER	2000/03/15	APPROVED BY	DATE	EDGELY	2000/03/15	MATERIAL NO.		SCALE ---	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION	TITLE MICRO FIT (3.0) DUAL ROW VERTICAL THRU HOLE HEADER ASS'Y molex	DOCUMENT NO. SD-43045-010	SHEET NO. 1 OF 1
				mm	INCH																																													
			4 PLACES	± ---	± ---																																													
			3 PLACES	± ---	± .010																																													
			2 PLACES	± 0.25	± .014																																													
			1 PLACE	± 0.36	± ---																																													
			0 PLACE	±																																														
			ANGULAR ±1/2°																																															
			DRAFT WHERE APPLICABLE																																															
			MUST REMAIN WITHIN DIMENSIONS																																															
DRAWN BY	DATE																																																	
SAMIEC	2000/03/15																																																	
CHECKED BY	DATE																																																	
MUELLER	2000/03/15																																																	
APPROVED BY	DATE																																																	
EDGELY	2000/03/15																																																	
MATERIAL NO.																																																		
	REV	DESCRIPTION	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																																															