

## Ferrule - AI-TWIN 2X 0,5-10 WH - 3203309

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Ferrule, Length: 15 mm, Color: white

### Key commercial data

|                  |               |
|------------------|---------------|
| package_quantity | 100           |
| GTIN             | 4046356345798 |

### Technical data

#### Dimensions

|                                              |         |
|----------------------------------------------|---------|
| Length (b)                                   | 15 mm   |
| Sleeve length                                | 10 mm   |
| Inner dimension of the insulating collar (d) | 2.5 mm  |
| Ferrule diameter                             | 1.5 mm  |
| Insulating collar thickness                  | 0.25 mm |
| Sleeve wall thickness                        | 0.15 mm |

#### Ambient conditions

|                            |        |
|----------------------------|--------|
| Short-term temperature     | 120 °C |
| Max. permanent temperature | 105 °C |

#### General

|                                         |                                |
|-----------------------------------------|--------------------------------|
| Color                                   | white                          |
| Components                              | free from silicone and halogen |
| Inflammability class according to UL 94 | HB                             |
| Material                                | E-CU                           |

### classifications

#### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 27060701 |
| eCl@ss 4.1 | 27060701 |
| eCl@ss 5.0 | 27400201 |
| eCl@ss 5.1 | 27400201 |
| eCl@ss 6.0 | 27400201 |
| eCl@ss 7.0 | 27400201 |

## Ferrule - AI-TWIN 2X 0,5-10 WH - 3203309

### classifications

#### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 8.0 | 27400201 |
|------------|----------|

#### ETIM

|          |          |
|----------|----------|
| ETIM 2.0 | EC000005 |
| ETIM 3.0 | EC000005 |
| ETIM 4.0 | EC000005 |
| ETIM 5.0 | EC000005 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30212109 |
| UNSPSC 7.0901 | 27121703 |
| UNSPSC 11     | 27121703 |
| UNSPSC 12.01  | 27121703 |
| UNSPSC 13.2   | 27121703 |

### approvals

CSA / CSAus / cCSAus /

#### Approval details

|                                                                                                |  |
|------------------------------------------------------------------------------------------------|--|
| <b>CSA</b>  |  |
|                                                                                                |  |
| Nominal voltage UN                                                                             |  |
| Nominal current IN                                                                             |  |
| mm²/AWG/kcmil                                                                                  |  |

|                    |  |
|--------------------|--|
| <b>CSAus</b>       |  |
|                    |  |
| Nominal voltage UN |  |
| Nominal current IN |  |
| mm²/AWG/kcmil      |  |

|               |
|---------------|
| <b>cCSAus</b> |
|---------------|

### Drawings