

PLL CLOCK MULTIPLIER WITH SS

IDT5V80024

Description


The IDT5V80024 is the most cost effective way to generate a high-quality, high-frequency clock output. The device also features a 27MHz output, making it ideal for systems to replace a high frequency oscillator along with a 1.8V 27MHz crystal.

Using Phase-Locked Loop (PLL) techniques, the device employs IDT's proprietary MEMs oscillator technology to produce common output frequencies for consumer, computing, and embedded applications that require spread spectrum to reduce system EMI.


Features

- Packaged in a small form factor 16-pin QFN
- Eliminates the need for an external crystal or input clock source
- Max. ± 50 ppm error on CLK and 27MHz output
- Typical ± 75 ps short term cycle-cycle jitter
- Down spread spectrum capability to reduce EMI
- Output voltage of 3.3 V
- Operating voltage of 1.8V
- Supports industrial temperature range
- Supports output frequency on CLK up to 130MHz
- Advanced, low-power CMOS process

Block Diagram



Pin Assignment



16-pin QFN

SS CLK Output Frequency/Part Number Table

Frequency	Orderable Part Number
27 MHz	5V80024-027NLGI
50 MHz	5V80024-050NLGI
66.6666 MHz	5V80024-666NLGI
122.8 MHz	5V80024-122NLGI

Note: Contact IDT for any other frequencies.

Spread Spectrum Selection Table

S1	S0	Spread Amount	Direction
0	0	No spread	—
0	1	-0.5%	Down
1	0	-1.0%	Down
1	1	-1.5%	Down

* Default setting is S1:S0 =00

Pin Descriptions

Pin Number	Pin Name	Pin Type	Pin Description
1	VDD	Power	Connect to +1.8V.
2	S1	Input	Input select pin for spread spectrum selection. See table above. Internal pull-down resistor.
3	S0	Input	Input select pin for spread spectrum selection. See table above. Internal pull-down resistor.
4	OE	Input	Output enable for SS CLK and 27M outputs.
5	VDDO	Power	Connect to +3.3V.
6	VDD	Power	Connect to +1.8V.
7	VDD	Power	Connect to +1.8V.
8	GND	Ground	Connect this pin to ground.
9	SS CLK	Output	Single-ended clock output with spread spectrum.
10	GND	Ground	Connect this pin to ground.
11	27M	Output	27MHz reference output at 1.8V.
12	GND	Ground	Connect this pin to ground.
13	VDD	Power	Connect to +1.8V.
14	CAP-IN	–	This pin should be connected to GND (pin 15) through a 10μF capacitor
15	GND	Ground	Connect this pin to ground.
16	VDD	Power	Connect to +1.8V.

External Components

Decoupling Capacitor

As with any high-performance mixed-signal IC, the IDT5V80024 must be isolated from system power supply noise to perform optimally.

A decoupling capacitor of 0.01 μ F must be connected between VDD and GND. It must be connected close to the IDT5V80024 to minimize lead inductance. No external power supply filtering is required for the IDT5V80024.

Series Termination Resistor

A 33 Ω terminating resistor can be used next to the CLK pin and 27M pin. The total on-chip capacitance is approximately 12 pF.

Absolute Maximum Ratings

Stresses above the ratings listed below can cause permanent damage to the IDT5V80024. These ratings, which are standard values for IDT commercially rated parts, are stress ratings only. Functional operation of the device at these or any other conditions above those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods can affect product reliability. Electrical parameters are guaranteed only over the recommended operating temperature range.

Item	Rating
Supply Voltage, VDD	5 V
All Inputs and Outputs	-0.5 V to VDD+0.5 V
Ambient Operating Temperature (industrial temperature)	-40 to +85° C
Storage Temperature	-65 to +150° C
Soldering Temperature	260° C

Recommended Operation Conditions

Parameter	Min.	Typ.	Max.	Units
Ambient Operating Temperature (commercial)	0	–	+70	° C
Ambient Operating Temperature (industrial)	-40	–	+85	° C
Power Supply Voltage (measured in respect to GND)	+1.71	+1.8	+1.89	V
Power Supply Voltage (VDDO)	+3.135	+3.3	+3.465	V

DC Electrical Characteristics

VDD=1.8 V $\pm$ 5% , VDDO = 3.3 V, Ambient temperature -40 to +85° C, unless stated otherwise

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Units
Operating Voltage	VDD		1.71	1.8	1.89	V
Output Voltage	VDDO	CLK	3.135	3.3	3.465	V
Input High Voltage	V _{IH}		0.65			V
Input Low Voltage	V _{IL}				0.35VDD	V
Output High Voltage*	V _{OH}	I _{OH} = -2 mA, 27M	VDD-0.45			V
Output Low Voltage*	V _{OL}	I _{OL} = 2 mA, 27M			0.45	V
Output High Voltage*	V _{OH}	I _{OH} = -2 mA, CLK	VDD-0.45			V
Output Low Voltage*	V _{OL}	I _{OL} = 2 mA, CLK			0.4	V
IDD Operating Supply Current		No load		15	22	mA
Input Capacitance				4		pF

*Note: Guaranteed by design.

AC Electrical Characteristics–CLK

VDD=1.8 V $\pm$ 5%, VDDO = 3.3 V, Ambient Temperature -40 to +85° C, unless stated otherwise

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Units
Output Frequency	F _{OUT}		See Page 2			MHz
Frequency Synthesis Error			-50		50	ppm
Output Clock Rise Time	t _{OR}	80% to 20%		1		ns
Output Clock Fall Time	t _{OF}	20% to 80%		1		ns
Output Clock Duty Cycle	t _{OD}	VDD/2	45	50	55	%
Short Term Cycle-to-Cycle Jitter	t _{ja}	CLK output		75	100	ps
Long Term Jitter		CLK output		TBD	TBD	ps
Aging		First year			5	ppm
Power-up Time				10	45	ms
Spread Spectrum Modulation Frequency				32		kHz

Note: Measured with a 7pF load.

AC Electrical Characteristics–27M

VDD=1.8 V $\pm$ 5%, Ambient Temperature -40 to +85° C, unless stated otherwise

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Units
Output Frequency	F_{OUT}		27			MHz
Frequency Synthesis Error			-50		50	ppm
Output Clock Rise Time	t_{OR}	80% to 20%		1		ns
Output Clock Fall Time	t_{OF}	20% to 80%		1		ns
Output Clock Duty Cycle	t_{OD}	VDD/2	45	50	55	%
Short Term Cycle-to-Cycle Jitter	t_{ja}	27M		50	75	ps
One Sigma Clock Period Jitter	t_{js}	27M		15		ps
Long Term Jitter		27M		TBD	TBD	ps
Aging		First year			TBD	ppm
Power-up Time				10	45	ms

Revision History

Rev.	Originator	Date	Description of Change
A	K.B.	07/12/11	Initial datasheet release
B	K.B.	10/21/11	1. Added 1.8V to 3.3 VDDO for CLK to Features 2. Added Power Supply Voltage (VDDO) spec to recommended Operating Conditions. 3. Updated DC char table. 4. Updated AC char table for CLK. 5. Added AC char table for 27M.
C	J.C.	02/03/12	1. Updated Features bullets 2. Updated minimum output voltage spec from 1.71V to 3.135V 3. Updated IDD Operating Supply Current Typ. and Max. values 4. Updated Short Term C-C Jitter Typ. and Max. values
D	J.C.	02/23/12	Update "CLK Output Frequency/Part Number Tree" table by removing erroneous/invalid part numbers and updating frequencies

Innovate with IDT and accelerate your future networks. Contact:

www.IDT.com

For Sales

800-345-7015

408-284-8200

Fax: 408-284-2775

For Tech Support

www.idt.com/go/clockhelp

Corporate Headquarters

Integrated Device Technology, Inc.

www.idt.com

