

LOC	DIST	P	F	REVISIONS				
				ZONE	LTR	DESCRIPTION	DATE	APPD
AA	27				K	REV; EC 0210-0840-94	3-14-95	LM NJ


- 1

DIMENSIONS ARE MAXIMUM UNLESS OTHERWISE SPECIFIED.
- 2

MATERIAL: POLYESTER FILM- 0.08 [0.003] THICK OVER PVC FILM 0.18 [0.007] THICK EACH SIDE. COPPER WIRE- 0.23 [0.009] THICK × 15.24 [0.600] WIDE. SHIELD- PVC, 0.25 [0.010] THICK.
- 3

CABLE MARKED WITH "AMP INC PN 553820 TYPE FCC UL CSA 12 AWG, CU 300V, 20 AMP 60°C" IN COLOR SPECIFIED FOR CONTINUOUS LENGTH OF ROLL AS SHOWN.
- 4

CAUTION: THE UNDERCARPET CABLE MAY NOT BE USED OUTDOORS OR IN WET LOCATIONS; WHERE THE CABLE WOULD BE SUBJECT TO CORROSIVE VAPORS; IN ANY HAZARDOUS (CLASSIFIED) LOCATION; OR IN RESIDENTIAL, SCHOOL, AND HOSPITAL BUILDINGS.



30.78	[101]	3-553820-4
15.54	[51]	3-553820-3
76.51	[251]	3-553820-1
LENGTH PER ROLL - M (FEET)		PART NO

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON : 2 PLC DEC ± - 3 PLC DEC ± - ANGLES ± -		DR 2-17-94 B. SIMPSON	AMP AMP Incorporated Harrisburg, PA 17105-3608		
MATERIAL		CHK 2-25-94 C. WHITT			
FINISH		APPD 3-3-94 B. MCNEIL	NAME		
-		APPD 3-3-94 D. MARGO	CABLE, FLAT, 5 CONDUCTOR, 12 AWG, ISOLATED GROUND, POWER, UNDERCARPET		
-		PRODUCT SPEC 108-6038	SIZE		
		APPLICATION SPEC 114-6008	D 00779 C=553820		
		WEIGHT -	SCALE -		
			SHEET 1 OF 1		

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.