



- NOTES:
1. MATERIALS AND FINISHES: (PLATING THICKNESS IN MICRO-INCHES)
OUTER CONTACT- PHOSPHOR BRONZE, NICKEL PLATING (.0001" THICK)
FRONT BODY - ZINC DIECAST, NICKEL PLATING (.00015" THICK)
CRIMP CONTACT - BRASS, GOLD PLATING (.00005" THICK)
INSULATOR - PTFE
2. ELECTRICAL:
A. IMPEDANCE: 75 OHM
B. FREQUENCY RANGE: DC - 3 GHz
C. VSWR(RETURN LOSS): 1.10 UP TO 2 GHz(-26.44 dB), 1.16 UP TO 3 GHz(-22.61 dB)
D. DIELECTRIC WITHSTANDING VOLTAGE: 1500 VRMS, MIN.
E. WORKING VOLTAGE: 500 VAC PEAK
3. MECHANICAL:
A. DURABILITY: 500 CYCLES MIN.
B. TEMPERATURE RANGE: -40° C TO +85° C
4. PACKAGING:
A. QUANTITY: SINGLE PACK
B. MARKING: BAG TO BE MARKED
"AMPHENOL, PN:7, AND DATE CODE"
5. FERRULE TO BE CRIMPED WITH A .178" HEX DIE.
CONTACT TO BE CRIMPED WITH A .042" SQUARE DIE
OR A 8 POINT CRIMPER AMPHENOL NUMBER 227-TI200

THIRD ANGLE PROJ. 

REVISIONS				
REV	DESCRIPTION	DATE	ECO	APPR
A	RELEASE TO MFG.	8/17/06	46206	GSA
B	NOTE 5 '8 PT CRIMPER AMPHENOL NUMBER CTL-TI200'	8/6/07	46681	TC
C	REMOVE STAMPING & REF TO 349- SPEC NOTE 5 \RD-DM11041802R3	27-Apr-11	48502	SCOTT
D	227-TI200 WAS CTL-TI200\RD-DM110704011	15-Jul-11	48649	SCOTT



SCALE 1.000



RECOMMENDED CABLE STRIPPING DIMENSIONS

SCALE 3.000

CUSTOMER OUTLINE DRAWING
ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE: <0.5mm ± 0.05mm 0.5 - 6mm ±0.1mm 6 - 30mm ±0.2mm 30 - 120mm ± 0.3mm ANGLES ±1° NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. the furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights to permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.	MATERIAL	DRAWN	DATE	TITLE BNC 90° ANGLE PLUG FOR RG-179 CABLE	Amphenol RF Danbury CT USA, Tainan, Taiwan, Shenzhen, China www.amphenolrf.com
	SEE NOTE	ENGINEER	DATE		
	REFERENCE	APPROVED	DATE		
	FINISH	CAD FILE		SCALE: 3.0:1.0	SHEET 2 OF 2
				DWG SIZE B	REV D
					DRAWING NO. 31-80901
					ITEM NO. 31-80901
					PART NO. 31-80901