




PRODUCT NUMBER
SEE TABLE

68682 - XXX - LF

LEAD FREE OPTION
PACKAGING OPTION. OMIT IF NOT REQUIRED
NO OF POSITIONS PER ROW
PLATING CODE
BASE PART NUMBER



mat'l. code				surface		tolerance		projection		product family			
-				ISO 1302		ISO 406		ISO 1101		DUBOX			
ltr	ecn no	dr	date	tolerances unless otherwise specified		linear		INCH/MM		title			
T	N-005184	SH	2011-08-18	angles		.XXX.01/.XXX.03		scale 4:1		DUBOX DBL. ROW DBL. ENTRY			
U	ELX-N-13980	DCS	2013-01-28	linear		.XXX.005/.XXX.013		scale 4:1		VERT. CARD CONN. ASS'Y.			
V	ELX-N-14177	DCS	2013-03-04	linear		.XXX.0020/.XXX.0051		scale 4:1		dwg no			
P	M06-0433	MN	06/17/06	dr	S. RAMP	02/25/91	02/25/91		02/25/91		sheet 1 of 3		size
R	M09-0121	MHT	7/24/09	chr	M. HAHN	02/25/91	02/25/91		02/25/91		68682		A3
S	M09-0124	MHT	9/07/09	appd	M. HAHN	02/25/91	02/25/91		02/25/91		type		Product Customer Drawing
sheet	revision	V	V	V	V	V	V	V	V	V	V	V	V
index	sheet	1	2	3	3	3	3	3	3	3	3	3	3

PRODUCT NO NOTE 8	PLATING CONTACT AREA MIN NOTE 11	PLATING SOLDER TAIL
68682-2XX	15u"/.38u Au DR GXT, OVER 50u"/1.27 Ni	100u"/160u" SN 2.54u/4.06u
68682-3XX	30u"/.76u Au DR GXT, OVER 50u"/1.27 Ni	100u"/160u" SN 2.54u/4.06u
68682-4XX	100u"/160u" SN 2.54u/4.06u	100u"/160u" SN 2.54u/4.06u
68682-5XX	50u"/1.27u Au OVER 50u"/1.27 Ni	100u"/160u" SN 2.54u/4.06u
68682-6XX	30u"/.76u Au DR GXT, OVER 50u"/1.27 Ni	100u"/160u" SN 2.54u/4.06u
68682-8XX	30u"/.76u Au OVER 50u"/1.27 Ni	100u"/160u" SnPb 2.54u/4.06u




FIGURE A

NOTES:

- MATERIAL TERMINAL: PHOSPHOR BRONZE.
- RECOMMENDED APPLICATION DATA:
 - RECOMMENDED HOLE PATTERN IS SHOWN IN FIGURE A.
 - ALL MATING PINS TO BE .025/.64 SQUARE ON TRUE CENTER OF GIVEN TERMINAL SPACINGS WITHIN .015/.38 DIA
 - SUGGESTED MATING PIN LENGTH .210±.020/5.33±.51
 - TERMINALS CAN ONLY BE USED FOR PC BOARD WITH NON PLATED THROUGH HOLES.
 - RECOMMENDED PC BOARD THICKNESS: .062/1.58
- MATERIAL HOUSING: PPS FILLED, COLOR BLACK, FLAME RETARDANT PER UL-94V-0.
PART WILL WITHSTAND EXPOSURE TO 260° C PEAK TEMPERATURE FOR 20 SEONDS IN WAVE SOLDER, INFRA-RED OR VAPOR PHASE SOLDER PROCESS.
- FCI, FCI FINAL PART NUMBER AND DATE CODE TO BE MARKED ON TUBE LABEL.
- PREPLATED, STAMPED TERMINALS.
- PART NUMBER WITH SUFFIX "U" IS FOR SAWING PURPOSES ONLY.
- STANDARD TUBE PACKAGE PER BUS-14-097/3.
- ADD LF SUFFIX AT THE END OF PART NUMBER FOR LEAD FREE OPTION.
- THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATION AS DESCRIBED IN GS-22-008.
- "THIS PRODUCT HAS 100% TIN PLATING IN THE INTERFACE AND HAS NOT BEEN TESTED FOR WHISKER GROWTH IN ALL INTERCONNECT ENVIRONMENTS".

mat'l. code				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection ISO 1101	product family DUBOX
ltr	ecn	no	dr	date	tolerances unless otherwise specified	INCH/MM scale 4:1	title
v					angles		DUBOX DBL. ROW DBL. ENTRY
					linear		VERT. CARD CONN. ASS'Y.
					0°±2'		
			dr	S. RAMP	02/25/91	FCI	dwg no
			enr	M. HAHN	02/25/91		sheet 2 of 3
			chr	M. HAHN	02/25/91		size
			appd	M. HAHN	02/25/91		A3
sheet index	revision	sheet					type Product Customer Drawing

