




Pillow blocks cast housing Set screw type



Pressed steel dust cover type

Open end

S-UCP...D1

Closed end

SM-UCP...D1






Shaft dia.	Unit number ¹⁾	Nominal dimensions											Bolt size	Bearing number
		mm inch												
mm inch		<i>H</i>	<i>L</i>	<i>J</i>	<i>A</i>	<i>N</i>	<i>N</i> ₁	<i>H</i> ₁	<i>H</i> ₂	<i>L</i> ₁	<i>B</i>	<i>S</i>	mm inch	
12	UCP201D1	30.2	127	95	38	13	16	14	62	42	31	12.7	M10	UC201D1
½	UCP201-008D1	1⅜	5	3¾	1½	½	⅝	⅞	2⅞	1⅜	1.2205	0.500	⅜	UC201-008D1
15	UCP202D1	30.2	127	95	38	13	16	14	62	42	31	12.7	M10	UC202D1
⅞	UCP202-009D1	1⅜	5	3¾	1½	½	⅝	⅞	2⅞	1⅜	1.2205	0.500	⅜	UC202-009D1
⅝	UCP202-010D1	1⅜	5	3¾	1½	½	⅝	⅞	2⅞	1⅜	1.2205	0.500	⅜	UC202-010D1
17	UCP203D1	30.2	127	95	38	13	16	14	62	42	31	12.7	M10	UC203D1
1⅛	UCP203-011D1	1⅜	5	3¾	1½	½	⅝	⅞	2⅞	1⅜	1.2205	0.500	⅜	UC203-011D1
20	UCP204D1	33.3	127	95	38	13	16	14	65	42	31	12.7	M10	UC204D1
¾	UCP204-012D1	1⅝	5	3¾	1½	½	⅝	⅞	2⅞	1⅜	1.2205	0.500	⅜	UC204-012D1
25	UCP205D1	36.5	140	105	38	13	16	15	71	42	34	14.3	M10	UC205D1
1⅜	UCP205-013D1													UC205-013D1
⅞	UCP205-014D1	1⅞	5½	4⅛	1½	½	⅝	⅞	2⅝	1⅜	1.3386	0.563	⅜	UC205-014D1
1⅝	UCP205-015D1													UC205-015D1
1	UCP205-100D1													UC205-100D1
30	UCP206D1	42.9	165	121	48	17	20	17	83	54	38.1	15.9	M14	UC206D1
1⅛	UCP206-101D1													UC206-101D1
1⅞	UCP206-102D1	1⅞	6½	4¾	1⅞	⅜	⅝	⅞	3⅞	2⅛	1.5000	0.626	½	UC206-102D1
1⅜	UCP206-103D1													UC206-103D1
1¼	UCP206-104D1													UC206-104D1
35	UCP207D1	47.6	167	127	48	17	20	18	93	54	42.9	17.5	M14	UC207D1
1¼	UCP207-104D1													UC207-104D1
1⅝	UCP207-105D1	1⅞	6⅞	5	1⅞	⅜	⅝	⅞	3⅜	2⅛	1.6890	0.689	½	UC207-105D1
1⅞	UCP207-106D1													UC207-106D1
1⅞	UCP207-107D1													UC207-107D1
40	UCP208D1	49.2	184	137	54	17	20	18	98	52	49.2	19	M14	UC208D1
1½	UCP208-108D1	1⅝	7¼	5⅜	2⅛	⅜	⅝	⅞	3⅞	2⅛	1.9370	0.748	½	UC208-108D1
1⅞	UCP208-109D1													UC208-109D1
45	UCP209D1	54	190	146	54	17	20	20	106	60	49.2	19	M14	UC209D1
1⅝	UCP209-110D1													UC209-110D1
1⅞	UCP209-111D1	2⅛	7⅜	5¾	2⅛	⅜	⅝	⅞	4⅜	2⅜	1.9370	0.748	½	UC209-111D1
1¾	UCP209-112D1													UC209-112D1

Remarks: 1) These numbers indicate relubricatable type. If maintenance free type is needed, please order without suffix "D1".
Note: Please refer to page 21 for size of grease fitting.

S
V

SM



Cast dust cover type
Open end C-UCP...D1
Closed end CM-UCP...D1

Housing number	Unit number pressed steel dust cover type ✱	Unit number cast dust cover type	Nominal dimensions				Mass of unit		
			t max.	mm A ₄	inch H ₃	A ₅	UCP	S(SM)	C(CM)
P203D1	S(SM)-UCP201D1	C(CM)-UCP201D1	2	51	67	62	0.7	0.7	1.0
P203D1	S(SM)-UCP201-008D1	C(CM)-UCP201-008D1	5/64	2	2 1/64	2 7/16	1.5	1.5	2.2
P203D1	S(SM)-UCP202D1	C(CM)-UCP202D1	2	51	67	62	0.7	0.7	1.0
P203D1	S(SM)-UCP202-009D1	C(CM)-UCP202-009D1	5/64	2	2 1/64	2 7/16	1.5	1.5	2.2
P203D1	S(SM)-UCP202-010D1	C(CM)-UCP202-010D1							
P203D1	S(SM)-UCP203D1	C(CM)-UCP203D1	2	51	67	62	0.7	0.7	1.0
P203D1	S(SM)-UCP203-011D1	C(CM)-UCP203-011D1	5/64	2	2 1/64	2 7/16	1.5	1.5	2.2
P204D1	S(SM)-UCP204D1	C(CM)-UCP204D1	2	51	70	62	0.7	0.7	1.0
P204D1	S(SM)-UCP204-012D1	C(CM)-UCP204-012D1	5/64	2	2 3/4	2 7/16	1.5	1.5	2.2
P205D1	S(SM)-UCP205D1	C(CM)-UCP205D1	2	57	76	70	0.8	0.9	1.2
P205D1	S(SM)-UCP205-013D1	C(CM)-UCP205-013D1							
P205D1	S(SM)-UCP205-014D1	C(CM)-UCP205-014D1	5/64	2 1/4	3	2 3/4	1.8	2.0	2.6
P205D1	S(SM)-UCP205-015D1	C(CM)-UCP205-015D1							
P205D1	S(SM)-UCP205-100D1	C(CM)-UCP205-100D1							
P206D1	S(SM)-UCP206D1	C(CM)-UCP206D1	2	62	88	75	1.3	1.4	1.9
P206D1	S(SM)-UCP206-101D1	C(CM)-UCP206-101D1							
P206D1	S(SM)-UCP206-102D1	C(CM)-UCP206-102D1	5/64	2 7/16	3 15/32	2 15/16	2.9	3.1	4.2
P206D1	S(SM)-UCP206-103D1	C(CM)-UCP206-103D1							
P206D1	—	—							
P207D1	S(SM)-UCP207D1	C(CM)-UCP207D1	3	72	99	80	1.6	1.7	2.3
P207D1	S(SM)-UCP207-104D1	C(CM)-UCP207-104D1							
P207D1	S(SM)-UCP207-105D1	C(CM)-UCP207-105D1	1/8	2 7/32	3 29/32	3 5/32	3.5	3.7	5.1
P207D1	S(SM)-UCP207-106D1	C(CM)-UCP207-106D1							
P207D1	—	—							
P208D1	S(SM)-UCP208D1	C(CM)-UCP208D1	3	82	105	90	1.9	2.1	3.2
P208D1	S(SM)-UCP208-108D1	C(CM)-UCP208-108D1	1/8	3 7/32	4 1/8	3 17/32	4.2	4.6	7.1
P208D1	S(SM)-UCP208-109D1	C(CM)-UCP208-109D1							
P209D1	S(SM)-UCP209D1	C(CM)-UCP209D1	3	82	113	95	2.2	2.4	3.5
P209D1	S(SM)-UCP209-110D1	C(CM)-UCP209-110D1							
P209D1	S(SM)-UCP209-111D1	C(CM)-UCP209-111D1	1/8	3 7/32	4 7/16	3 3/4	4.9	5.3	7.7
P209D1	S(SM)-UCP209-112D1	C(CM)-UCP209-112D1							