







PCB LAYOUT/TOP VIEW

**Materials and Finish**

Housing Material—
PBT Thermoplastic
UL 94V-0 Rated
Color: Black

Contact Material—
Phosphor Bronze

Contact Plating Options—
Standard: 0.0001" Nickel
Plating, Selective Plating
0.000015" Gold on Contact
Area

50: 0.0001" Nickel Plating,
Selective Plating 0.000050"
Gold on Contact Area to
Comply with FCC Requirements
Under No. 47 C.F.R. Part 68,
Subpart F

Electrical Characteristics

Insulation Resistance—
500 Megohms Min.

Dielectric Withstanding Voltage—
1000V rms, 60Hz

Contact Resistance—
20 milliohms Max.

Current Rating—
1.5 Amps

Part Number	t_gold
GDL-A-66	Flash
GDL-A-66-50	50u"

CSA NRTL/C Certified File No. LR78160

REVISION	DATE	DESCRIPTION	DRAWN BY	DESIGNED BY	UNITS
A	9/20/96	New Drawing	K. Wallace		mm
A1	1/21/2000	Add Dims	CHECKED BY	APPROVED BY	DATE
B1	11/30/00	ECD #00-206			11/29/00

GDL-A-66

Modular Jack, Right angle

6 Pos, 6 Contacts, non-shielded



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kycon:](#)

[GDL-A-66](#)