

30 Watt POE+ Power Transformers



EFD20 Package for Akros Silicon AS1135



Product Features:


- Designed for PoE+ isolated flyback DC/DC converter applications using the Akros Silicon AS1135
- Utilizes industry standard style footprint
- UL/EN60950 recognized
- Fully compliant to IEEE802.3at standard
- Isolation Voltage (PRI-SEC) 1,500Vrms
- Operating Temperature Range -40 to +85C

Part Number	Turns Ratio N1:N2:N3:N4:N5:N6	DCR (mΩ max)	PRI/OCL (μH ±10%)	PRI LL (μH ±10%)	Output Voltage	Circuit
TGSP-P026EFD20LF	1:1:0.25:0.2:0.2:0.25	50,300,10,300	40	0.8	5V	A
TGSP-P027EFD20LF	1:1:0.25:0.125:0.125:0.25	60,350,8,350	57	1.2	3.3V	A
TGSP-P028EFD20LF	1:1:0.167:0.333:0.333	150,300,50	112	1.5	12V	B




30 Watt POE+ Power Transformers

EFD20 Package



Dimensions: Inch [mm]
Tolerances: 0.006 Inch if not specified



Recommended
Solder Pad Layout



2880 Lakeside Drive #116
Santa Clara, CA 95054
(650) 903-3800
www.haloelectronics.com

HALO® Electronics is a leading supplier of high quality communication magnetics including signal transformers, filters, CMR chokes, PoE power transformers, DC/DC converters, and integrated Ethernet connectors. HALO's leading edge technology solutions are manufactured in ISO9001 and ISO14001 factories offering high quality products at a competitive price.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HALO Electronics:](#)

[TGSP-P028EFD20LF](#) [TGSP-P026EFD20LF](#) [TGSP-P028EFD20LFTR](#) [TGSP-P026EFD20LFTR](#) [TGSP-P027EFD20LF](#)