



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	REVISED PER ECR-17-008705	14NOV2017	FV	SK



- 1
- CONTINUOUS STRIP ON REELS WITH TERMINALS LOCATED ON 8.38±0.076[.330±.003] CENTERS
- 2
- SLOT ACCEPTS 0.64–0.81 mm [#22–#20] SINGLE OR DOUBLE COPPER MAGNET WIRE ONLY
SLOT ACCEPTS 0.72–0.91 mm [#21–#19] SINGLE OR DOUBLE ALUMINUM MAGNET WIRE ONLY
- 3
- REFER TO DWG 87–1039–3 FOR ADDITIONAL CAVITY INFORMATION (MODIFIED DEPTH)
- 4
- PRELIMINARY – NOT FOR PRODUCTION.
- 5
- 0.002540 [.000100] MIN TIN PLATE
- 6
- 0.002032 [.000080] MIN SILVER PLATE OVER 0.001270 [.000050] MIN NICKEL PLATE



6	WELD	4 2232237–2
5	WELD	2232237–1
FINISH	SPLICE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R.GRZYBOWSKI 24JUN97	TE Connectivity		
DIMENSIONS: mm		CHK M.S.FEHER 24JUN97			
		APVD N.E.NEFF 24JUN97	NAME TAB, 6.30[.250] CONNECTING, MAG-MATE		
		PRODUCT SPEC 108–2012			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC 114–2046 3	SIZE A2	CAGE CODE 00779	DRAWING NO C=2232237
MATERIAL PRE-MILLED BRASS		FINISH SEE TABLE	WEIGHT 0.000000	SCALE 6:1	SHEET 1 of 1
			CUSTOMER DRAWING	RESTRICTED TO	REV B