

Duratool V Bending Tool Set



A 'V' bending tool having a 160 mm length base plate with a 90° 'V' groove.
Five blades are supplied with lengths 50, 75, 100, 125 and 150 mm.
The blades are not hardened so that the use may cut to required length.
Thus many forms of bend up to 90° can be made to fabricate small panels, brackets and boxes, etc.
Box sizes made using the 'V' bending tool and lever press cover the range L. 20 W. 20 D. 10 mm to L. 155 W. 155 D. 130 bending capacity:
Aluminium 2.5 mm maximum mild steel 16 S.W.G. max.

Technical Specification:

Bending capacity - aluminium 2.5 mm.
Bending capacity - mild steel 16 mm.

Part Number Table

Description	Part Number
V Bending Tool Set	901-0050

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. DURATOOL is the registered trademark of the Group. © Premier Farnell plc 2011.

www.element14.com
www.farnell.com
www.newark.com
www.cpc.co.uk
www.mcmelectronics.com

