

CLE-125-01-G-DV

CLE SERIES

(0.80 mm) .0315"

COST-EFFECTIVE MICRO SOCKET

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?CLE

Insulator Material:

Black Liquid Crystal Polymer

Contact Material:

BeCu

Plating:

Au over 50 μ " (1.27 μ m) Ni

Current Rating (CLE/FTE):

2.7 A per pin
(2 pins powered)

Operating Temp Range:

-55 °C to +125 °C

Insertion Depth:

Top Entry = (1.73 mm) .068"

to (3.18 mm) .125" with

(0.38 mm) .015" wipe, or

pass-through

Bottom Entry = (3.23 mm) .127"

minimum plus board thickness

Normal Force:

75 grams (0.73 N)

Max Cycles:

100 with 10 μ " (0.25 μ m) Au

RoHS Compliant:


Yes

Mates with:
FTE, AW

TIGERTM
BEAM
CONTACT

Ideal for
pass-through
applications

OPTIONS



(0.80 mm) .0315"
micro pitch

Surface
Mount

PROCESSING

Lead-Free Solderable:

Yes

SMT Lead Coplanarity:

(0.10 mm) .004" max (04-65)


(0.15 mm) .006" max (66-90)*

*(.004" stencil solution

may be available; contact
IPG@samtec.com)

RECOGNITIONS

For complete scope of
recognitions see
www.samtec.com/quality



Note:
Some lengths, styles and
options are non-standard,
non-returnable.

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

All parts within this catalog are built to Samtec's specifications.

Customer specific requirements must be approved by Samtec and identified in a Samtec customer-specific drawing to apply.