





NOTE:
MATERIAL:
HOUSING:PBT+30% G.F. UL 94V-0
CONTACT 5P:PHOSPHOR BRONZE
CONTACT 4P:BRASS
SHELL:SPCC
PLATING:
CONTACT: GOLD FLASH AND TIN OVER NICKEL PLATED
SHELL: NICKEL PLATED OVER ALL
SPECIFICATION:
CURRENT RATING:1.0A AT 30V AC MIN
WITHSTANDING VOLTAGE:500V AC FOR ONE MIN
INSULATION RESISTANCT:1000MΩ MIN
CONTACT RESISTANCE:30mΩ MAX
MATING FORCE:3.57KgF MAX
UNMATING FORCE:1.02KgF MIN

09/08/11	SYSTEM		NEW DWG					A0		
DATE	DR.BY	ECN.NO.	DESCRIPTION				MARK		VER.	
-TOLERANCES- UNLESS OTHERWISE SPECIFIED			CnC Tech . LLC							
					TITLE: USB 3.0 A/M SOLDER 15U"BLUE					
X.X	±0.38	X.X°	±3.00°	APPD:		PRODUCT NO: 1003-023-01300				
X.XX	±0.25	X.XX°	±1.00°	CHECK:		DATE	SCALE	UNIT	TYPE	PAGE
X.XXX	±0.13	X.XXX°	±0.500°	DRAW:		2009.08.11	1:1	mm	CD	1 / 1