







mat'l. code —				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family RIBCAGE				
ltr	ecn no	dr	date	tolerances unless otherwise specified						 INCH/MM		title RIBCAGE III SMT VERT. HEADER ASS'Y		
AA	M08-0245	MHT	8/27/08	angles linear		.XX±.01/0.3								
AB	M09-0058	MHT	4/04/09			.XXX±.005/0.13								
AC	M09-0087	MHT	06/10/09	±2'		.XXXX±.0020/0.05'				scale 3:1		dwg no sheet 1 of 8 size 95781 A3		
AD	N10-0174	YO	6/17/10	dr	M. CORNMAN	6/07/95								
AE	ELX-N-004143	YO	06/20/11	engr	D. WHITING	6/07/95								
AF	ELX-N-004665	YO	07/27/11	chr	D. WHITING	6/07/95								
AG	ELX-N-009746	YO	1/20/12	appd	D. WHITING	6/07/95				type		Product	Customer	Drawing
sheet	revision	AG	AG	AG	AG	AG	AG	AG	AG					
index	sheet	1	2	3	4	5	6	7	8					

SIZE	DIM H	DIM J	DIM K	DIM L
2X5	.275/6.99	.200/5.08	.372/9.45	.320/8.13
2X10	.525/13.34	.450/11.43	.622/15.80	.570/14.48
2X15	.775/19.68	.700/17.78	.872/22.15	.820/20.83
2X20	1.025/26.03	.950/24.13	1.122/28.50	1.070/27.18
2X25	1.275/32.38	1.200/30.48	1.372/34.85	1.320/33.53
2X30	1.525/38.74	1.450/36.83	1.622/41.20	1.570/39.88
2X35	1.775/45.08	1.700/43.18	1.872/47.55	1.820/46.23
2X40	2.025/51.43	1.950/49.53	2.122/53.90	2.070/52.58
2X45	2.275/57.78	2.200/55.88	2.372/60.25	2.320/58.93
2X50	2.525/64.14	2.450/62.23	2.622/66.60	2.570/65.28






SECTION X-X
ROTATED 90° CW









SECTION Y-Y

mat'l. code —				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection INCH/MM	product family RIBCAGE			
ltr	ecn	no	dr	date	tolerances unless otherwise specified		title			
AG					angles	linear	RIBCAGE III SMT VERT. HEADER ASS'Y			
					±2°	.XX±.01/0.3 .XXX±.005/0.13 .XXXX±.0020/0.051	scale 3:1			
				dr	M. CORNMAN	6/07/95	FCI			
				enr	D. WHITING	6/07/95				
				chr	D. WHITING	6/07/95				
				appd	D. WHITING	6/07/95	type Product Customer Drawing			
sheet index	revision sheet									



LOCATOR/HOLDDOWN VARIATIONS





$\phi .0520$ [1.321]
 $\phi .040$ [1.02]
 $\phi .004/0.10$ (M) A (S) B (S) (ALL PEG CONFIGURATIONS)



$.0470 \pm .0005$ [1.194 $\pm .013$]
 $.040 \pm .001$ [1.02 $\pm .03$]
 $.0470 \pm .0005$ [1.194 $\pm .013$]
 $.040 \pm .001$ [1.02 $\pm .03$]



$.0520 \pm .0005$ [1.321 $\pm .013$]
 $.040 \pm .001$ [1.02 $\pm .03$]
 $.0520 \pm .0005$ [1.321 $\pm .013$]
 $.040 \pm .001$ [1.02 $\pm .03$]



$.0065 \pm .001$ [0.165 $\pm .025$]
 $\phi .0400$ [1.02]
 $.052 \pm .001$ [1.32 $\pm .025$]
R.002 [0.05] MAX

mat'l. code				surface	tolerance	projection	product family
-				ISO 1302	ISO 406	ISO 1101	RIBCAGE
ltr	ecn	no	dr	date	tolerances unless otherwise specified	INCH/MM	title
AG					linear	scale 3:1	RIBCAGE III SMT
					angles		VERT. HEADER ASS'Y
					±2'		
					dr		dwg no
					enr		sheet 3 of 8
					chr		size
					appd		A3
sheet	revision						type
index	sheet						Product Customer Drawing


PDS: Rev :AG

STATUS: Released


Printed: Feb 17, 2012

RECOMMENDED PCB MOUNTING PAD PATTERN


STYLE 1




STYLE 5




STYLE 4




STYLE 2




STYLE 7




STYLE 6



STYLE 3



mat'l. code				surface	tolerance	projection	product family
-				ISO 1302 ✓	ISO 406 ISO 1101	ISO 1101	RIBCAGE
ltr	ecn	no	dr	date	tolerances unless otherwise specified		title
AG					angles	linear	RIBCAGE III SMT
					±2'	linear	VERT. HEADER ASS'Y
					dr	M. CORNMAN	6/07/95
					enr	D. WHITING	6/07/95
					chr	D. WHITING	6/07/95
					appd	D. WHITING	6/07/95
sheet	revision						dwg no
index	sheet						95781
							type
							Product Customer Drawing



Copyright FCI

FCIconnect.com

PRODUCT NUMBER NOTE 11,4C	QTY. REEL	TAPE WIDTH PITCH MM	CONNECTOR ORIENTATION IN TAPE POCKET
87409-135TR	500	72/12	VIEW 1
87409-140TR	↑	72/12	↑
87409-145TR		72/12	
87409-150TR		88/12	
87849-105TR		24/12	
87849-110TR		24/12	
87849-115TR		44/12	
87849-120TR		44/12	
87849-125TR		56/12	
87849-130TR		56/12	
87849-135TR		72/12	
87849-140TR		72/12	
87849-145TR		72/12	
87849-150TR		88/12	
88566-110TR		24/12	
88566-115TR	↓	44/12	
88566-130TR	500	56/12	
90098-105TR	400	24/12	
90098-110TR	400	32/12	
90098-115TR	500	44/12	
90098-120TR	500	44/12	
90098-125TR	400	56/12	
90098-130TR	500	56/12	
90098-135TR	↑	72/12	
90098-140TR	↓	72/12	
90098-145TR		72/12	
90098-150TR		88/12	
90863-110	↓	24/12	↓
90863-115	500	44/12	VIEW 1

TABLE C

mat'l. code				surface		tolerance		projection		product family	
-				ISO 1302 ✓		ISO 406 ISO 1101				RIBCAGE	
ltr	ecn	no	dr	date		tolerances unless otherwise specified					
AG						angles	linear	.XX±.01/0.3		INCH/MM	
								.XXX±.005/0.13			
						±2°		.XXXX±.0020/0.051		scale 3:1	
						dr	M. CORNMAN	6/07/95		FCI	
						enrg	D. WHITING	6/07/95		dwg no	
						chr	D. WHITING	6/07/95		sheet 7 of 8	
						appd	D. WHITING	6/07/95		size	
sheet index		revision sheet								type	
										Product Customer Drawing	

form: A3

1

2

3

4

5

6

PDS: Rev :AG

STATUS:Released

Printed: Feb 17, 2012

