



CONTACT CONFIGURATION
TIMING (BBM) NON-SHORTING




ISOMETERIC



NOTE:

1. ALL DIMENSIONS IN MM[INCH].
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERM. NOS. FOR REFERENCE ONLY.
4. CONTACT MATERIAL: SILVER
5. CONTACT RATING: 0.3A 125VAC
6. OPERATING FORCE 800±300CM/STANDARD
7. OPERATING TEMP: -30°C TO 85°C
- ▲ 8. CIRCUIT SP: 12 POSITION 30° INDEX (NO-STOP)
9. DIELECTRIC STRENGTH: 500VAC FOR 1 MIN..
- ▲ 10. HARDWARE SUPPLIED ON SWITCH:
LOCKWASHER, HEXNUT, STOPRING
11. ▲ DENOTES CRITICAL PARAMETER.
12. 2002/95/EC (ROHS) COMPLIANT



E-SWITCH®

TITLE KC10B7.002NPS

A	15619	RELEASED FOR PRODUCTION	12/20/05	PH
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

SCALE	1.5:1	DATE	12/20/2005	DR	PH	DWG	G510257	REV	A
-------	-------	------	------------	----	----	-----	---------	-----	---