

ILAPS™ AN101101



INTRINSICALLY LINEAR ANGULAR POSITION SENSOR




FEATURES:

- Patented non-contact angular position sensor
- Magnet/sensor orientation provides intrinsically linear output over 100 degrees of electrical rotation (120 degrees mechanical rotation) without need for electrical compensation
- Provided with programmed output or end-user re-programmable to eliminate mechanical and process tolerances in your final assembly
- Adjustable rising or falling output slope with programmable offset, gain, temperature compensation, and clamping voltage
- Return spring provides resistance to CCW motion
- Provided with EMI/ESD protection
- Fully encapsulated electronics to IEC 529 IP67
- ILAPS™ technology can be custom packaged to meet your exact requirements (minimum quantities apply)

APPLICATIONS:

- Throttle and valve position sensing
- User interface controls (vehicles, gaming)
- Pedal position sensing
- Implement position sensing
- Gear selection
- Joystick position



AN101101



INTRINSICALLY LINEAR ANGULAR POSITION SENSOR

MECHANICAL SPECIFICATIONS:

MECHANICAL TRAVEL	120° CCW maximum rotational sensing range
ROTATION TORQUE:	0.12N-m max with return spring
MASS:	12 grams
LIFE:	+10 million full cycles
DITHER: (2° TRAVEL)	+80 million cycles
MATING CONNECTION	Connector: Packard metri-pack 150 12162185 Terminal: 12124075

ELECTRICAL SPECIFICATIONS:


EFFECTIVE ROTATIONAL SENSING RANGE:	0° to 100° functional output (with no overtravel)
INPUT VOLTAGE:	5.0V $\pm$ 10%
INPUT CURRENT:	10mA, max. at 5 VDC
INPUT CURRENT, OUTPUT(S) SHORTED TO GROUND:	25mA, max, per output
MAX. OVERVOLTAGE:	24V DC
SENSOR OUTPUT @ 5VDC: (RATIOMETRIC TO INPUT VOLTAGE)	0.5V TO 4.5V max. Programmable within 5% to 95% of the nominal voltage with positive or negative slopes
OUTPUT LINEARITY @ 5VDC: (ANALOG OUTPUT)	$\pm$ 2.0%
RESOLUTION:	Analog
RESPONSE TIME:	.23mSEC
BULK CURRENT INJECTION	SAE J1113-4, 250kHz TO 500MHz., 60mA/m
CONDUCTION AND COUPLING	SAE J1113-12, $\pm$ 200V
ELECTRONIC DISCHARGE	SAE J1113-13, $\pm$ 15kV
RADIATED IMMUNITY	SAE J1113-21, 10kHz TO 18GHz, 100V/m
IMMUNITY TO MAGNETIC FIELDS	SAE J1113-22, 600uT AC Field, 5Hz to 2kHz, .2mT & 1mT DC Field
IMMUNITY TO AC FIELDS	SAE J1113-25, 15,000V/m
RADIATED EMISSIONS	SAE J1113-41, Class 4

ENVIRONMENTAL SPECIFICATIONS:

VIBRATION:	10 G's peak, 20 Hz TO 1000 Hz
SHOCK:	20 G's, half sine pulse, 13 ms duration
OPERATING TEMPERATURE:	-40° C to +85° C (-40° C to +125° C optional)
STORAGE TEMPERATURE:	-55° C to +150° C

Specifications subject to change without notice.

AN101101 120 degree Sensor Output



Contact

Call, fax or visit our website for more information.

Cherry Electrical Products

11200 88th Avenue
Pleasant Prairie, WI 53158

Phone: 262 942 6500
Fax: 262 942 6566
Web: www.cherrycorp.com

© Cherry Corporation 2/2007