






CUSTOMER DRAWING

NOTES

1. AVOID ANY DEFECT: BURR, FRACTURE, CHIP
2. GATE SHOULD NOT BE POSITIONED ON SEALED AREA.
3. EVERY OUTSIDE RECTANGULAR EDGE EXCEPT FOR SEALED OR PARTITION EDGE: R=0.3
4. OUTSIDE R=0.2 EXCEPT AS NOTED
5. INSIDE R=1 EXCEPT AS NOTED
6. FINISH OF BLADE TERMINAL: GALV 3-5um Cu
GALV 5-10um SnPb 90/10

- △ RECYCLE MARKING
 △ DATE CODE
 △ CIRCUIT NO.
 △ APPLIED ONLY P/N : 1-85265-1.

SECTION C-C
SCALE : 1/1

33	33	85249-6	1.6mm TAB(LONG)	BRASS T-4	---	⑦
14	14	85249-4	1.6mm TAB(MIDDLE)	BRASS T-4	---	⑥
15	15	85249-2	1.6mm TAB(SHORT)	BRASS T-4	---	⑤
13	13	85248-4	2.8mm TAB(LONG)	BRASS T-4	---	④
13	13	85248-2	2.8mm TAB(SHORT)	BRASS T-4	---	③
1	1	85270-1	JOINTER HSG	NYLON 66 GF50%	NATURAL	②
1	1	1-85266-1	HEADER HSG	NYLON 66 GF50%	NATURAL	①
	1	85266-1	HEADER HSG	NYLON 66 GF50%	NATURAL	①
Q'TY PER ASS'Y		PART NO.	DESCRIPTION	MATERIAL	COLOR	ITEM NO.

1-85265-1	85265-1	© 19 AMP MFG KOREA ALL RIGHT RESERVED AMP PRODUCTS COVERED BY PATENTS AND OR PATENTS PENDING			AMP MFG KOREA			
		WIRE RANGE -----	INSULATION DIA -----	NAME JR+MICRO TIMER 88P HEADER ASS'Y				
		MATERIAL SEE TABLE	FINISH/COLOR SEE TABLE					
		DR	APP	TOLERANCES 0KXXK10 ±0.2 10KXXK30 ±0.25 30KXXK100±0.3 ANGLES ±3°	SIZE A2	LOC DS	NUMBER 85265	
		ASS'Y P/N	CHK	REL	SCALE 0.8/1	REV A	SHEET 1/1	

A	REVISED(ECN RD97-206)	JW	CS	18/01
□	RELEASED	JC	JK	4/15
LTR	REVISION RECORD	DR	CHK	DATE