

Zener Diodes with Surge Current Specification



FEATURES

- Silicon planar Zener diodes
- Low profile surface-mount package
- Zener and surge current specification
- Low leakage current
- Excellent stability
- High temperature soldering: 260 °C/10 s at terminals
- AEC-Q101 qualified
- Compliant to RoHS Directive 2002/95/EC and in accordance to WEEE 2002/96/EC


RoHS
COMPLIANT

PRIMARY CHARACTERISTICS

PARAMETER	VALUE	UNIT
V _Z range nom.	3.6 to 200	V
Test current I _{ZT}	5 to 100	mA
V _Z specification	Pulse current	
Int. construction	Single	

ORDERING INFORMATION

DEVICE NAME	ORDERING CODE	TAPED UNITS PER REEL	MINIMUM ORDER QUANTITY
BZD27C3V6P to BZD27C200P	BZD27C3V6P to BZD27C200P-series-GS08	3000 per 7" reel (8 mm tape)	15 000/box
BZD27C3V6P to BZD27C200P	BZD27C3V6P to BZD27C200P-series-GS18	10 000 per 13" reel (8 mm tape)	10 000/box

PACKAGE

PACKAGE NAME	WEIGHT	MOLDING COMPOUND FLAMMABILITY RATING	MOISTURE SENSITIVITY LEVEL	SOLDERING CONDITIONS
DO-219AB (SMF)	15 mg	UL 94 V-0	MSL level 1 (according J-STD-020)	260 °C/10 s at terminals

ABSOLUTE MAXIMUM RATINGS (T_{amb} = 25 °C, unless otherwise specified)

PARAMETER	TEST CONDITION	SYMBOL	VALUE	UNIT
Power dissipation	T _L = 80 °C	P _{tot}	2300	mW
	T _A = 25 °C ⁽¹⁾	P _{tot}	800	mW
Non repetitive peak surge power dissipation ⁽²⁾	100 µs square pulse	P _{ZSM}	300	W
	10/1000 µs waveform (BZD27-C7V5P to BZD27-C100P)	P _{RSM}	150	W
	10/1000 µs waveform (BZD27-C100P to BZD27-C200P)	P _{RSM}	100	W
Junction to lead		R _{thJL}	30	K/W
Junction to ambient air	Mounted on epoxy-glass PCB with 3 mm x 3 mm Cu pads (≥ 40 µm thick)	R _{thJA}	180	K/W
Junction temperature		T _j	150	°C
Storage temperature range		T _{stg}	- 55 to + 150	°C

Notes

⁽¹⁾ Mounted on epoxy-glass PCB with 3 mm x 3 mm Cu pads (≥ 40 µm thick)

⁽²⁾ T_j = 25 °C prior to surge

**ELECTRICAL CHARACTERISTICS** ($T_{amb} = 25\text{ }^{\circ}\text{C}$, unless otherwise specified)

PART NUMBER	MARKING CODE	ZENER VOLTAGE RANGE ⁽¹⁾			TEST CURRENT	REVERSE CURRENT		DYNAMIC RESISTANCE		TEMPERATURE COEFFICIENT	
		V_Z at I_{ZT1}			I_{ZT1}	I_R at V_R		Z_Z at I_{ZT1}		α_{VZ} at I_{ZT1}	
		V			mA	μA	V	Ω		%/ $^{\circ}\text{C}$	
		MIN.	NOM.	MAX.		MAX.		TYP.	MAX.	MIN.	MAX.
BZD27C3V6P	D0	3.4	3.6	3.8	100	100	1	4	8	- 0.14	- 0.04
BZD27C3V9P	D1	3.7	3.9	4.1	100	50	1	4	8	- 0.14	- 0.04
BZD27C4V3P	D2	4	4.3	4.6	100	25	1	4	7	- 0.12	- 0.02
BZD27C4V7P	D3	4.4	4.7	5	100	10	1	3	7	- 0.1	0
BZD27C5V1P	D4	4.8	5.1	5.4	100	5	1	3	6	- 0.08	0.02
BZD27C5V6P	D5	5.2	5.6	6	100	10	2	2	4	- 0.04	0.04
BZD27C6V2P	D6	5.8	6.2	6.6	100	5	2	2	3	- 0.01	0.06
BZD27C6V8P	D7	6.4	6.8	7.2	100	10	3	1	3	0	0.07
BZD27C7V5P	D8	7	7.5	7.9	100	50	3	1	2	0	0.07
BZD27C8V2P	D9	7.7	8.2	8.7	100	10	3	1	2	0.03	0.08
BZD27C9V1P	E0	8.5	9.1	9.6	50	10	5	2	4	0.03	0.08
BZD27C10P	E1	9.4	10	10.6	50	7	7.5	2	4	0.05	0.09
BZD27C11P	E2	10.4	11	11.6	50	4	8.2	4	7	0.05	0.1
BZD27C12P	E3	11.4	12	12.7	50	3	9.1	4	7	0.05	0.1
BZD27C13P	E4	12.4	13	14.1	50	2	10	5	10	0.05	0.1
BZD27C15P	E5	13.8	15	15.6	50	1	11	5	10	0.05	0.1
BZD27C16P	E6	15.3	16	17.1	25	1	12	6	15	0.06	0.11
BZD27C18P	E7	16.8	18	19.1	25	1	13	6	15	0.06	0.11
BZD27C20P	E8	18.8	20	21.2	25	1	15	6	15	0.06	0.11
BZD27C22P	E9	20.8	22	23.3	25	1	16	6	15	0.06	0.11
BZD27C24P	F0	22.8	24	25.6	25	1	18	7	15	0.06	0.11
BZD27C27P	F1	25.1	27	28.9	25	1	20	7	15	0.06	0.11
BZD27C30P	F2	28	30	32	25	1	22	8	15	0.06	0.11
BZD27C33P	F3	31	33	35	25	1	24	8	15	0.06	0.11
BZD27C36P	F4	34	36	38	10	1	27	21	40	0.06	0.11
BZD27C39P	F5	37	39	41	10	1	30	21	40	0.06	0.11
BZD27C43P	F6	40	43	46	10	1	33	24	45	0.07	0.12
BZD27C47P	F7	44	47	50	10	1	36	24	45	0.07	0.12
BZD27C51P	F8	48	51	54	10	1	39	25	60	0.07	0.12
BZD27C56P	F9	52	56	60	10	1	43	25	60	0.07	0.12
BZD27C62P	G0	58	62	66	10	1	47	25	80	0.08	0.13
BZD27C68P	G1	64	68	72	10	1	51	25	80	0.08	0.13
BZD27C75P	G2	70	75	79	10	1	56	30	100	0.08	0.13
BZD27C82P	G3	77	82	87	10	1	62	30	100	0.08	0.13
BZD27C91P	G4	85	91	96	5	1	68	60	200	0.08	0.13
BZD27C100P	G5	94	100	106	5	1	75	60	200	0.09	0.13
BZD27C110P	G6	104	110	116	5	1	82	80	250	0.09	0.13
BZD27C120P	G7	114	120	127	5	1	91	80	250	0.09	0.13
BZD27C130P	G8	124	130	141	5	1	100	110	300	0.09	0.13
BZD27C150P	G9	138	150	156	5	1	110	130	300	0.09	0.13
BZD27C160P	H0	153	160	171	5	1	120	150	350	0.09	0.13
BZD27C180P	H1	168	180	191	5	1	130	180	400	0.09	0.13
BZD27C200P	H2	188	200	212	5	1	150	200	500	0.09	0.13

Notes

- Maximum $V_F = 1.2\text{ V}$, at $I_F = 0.2\text{ A}$
- Electrical characteristics when used as voltage regulator diodes

⁽¹⁾ Pulse test: $t_p \leq 5\text{ ms}$

**ELECTRICAL CHARACTERISTICS** ($T_{amb} = 25\text{ }^{\circ}\text{C}$, unless otherwise specified)

PART NUMBER	MARKING CODE	ZENER VOLTAGE RANGE			TEST CURRENT	REVERSE CURRENT		CLAMPING VOLTAGE		TEMPERATURE COEFFICIENT	
		V_Z at I_{ZT1}			I_{ZT1}	I_R at V_R		V_C at $I_{RSM}^{(1)}$		α_{VZ} at I_{ZT1}	
		V			mA	μA	V	V	A	% / $^{\circ}\text{C}$	
		MIN.	NOM.	MAX.		MAX.		MAX.		MIN.	MAX.
BZD27C7V5P	D8	7	7.5	7.9	100	1500	6.2	11.3	13.3	0	0.07
BZD27C8V2P	D9	7.7	8.2	8.7	100	1200	6.8	12.3	12.2	0.03	0.08
BZD27C9V1P	E0	8.5	9.1	9.6	50	100	7.5	13.3	11.3	0.03	0.08
BZD27C10P	E1	9.4	10	10.6	50	20	8.2	14.8	10.1	0.05	0.09
BZD27C11P	E2	10.4	11	11.6	50	5	9.1	15.7	9.6	0.05	0.1
BZD27C12P	E3	11.4	12	12.7	50	5	10	17	8.8	0.05	0.1
BZD27C13P	E4	12.4	13	14.1	50	5	11	18.9	7.9	0.05	0.1
BZD27C15P	E5	13.8	15	15.6	50	5	12	20.9	7.2	0.05	0.1
BZD27C16P	E6	15.3	16	17.1	25	5	13	22.9	6.6	0.06	0.11
BZD27C18P	E7	16.8	18	19.1	25	5	15	25.6	5.9	0.06	0.11
BZD27C20P	E8	18.8	20	21.2	25	5	16	28.4	5.3	0.06	0.11
BZD27C22P	E9	20.8	22	23.3	25	5	18	31	4.8	0.06	0.11
BZD27C24P	F0	22.8	24	25.6	25	5	20	33.8	4.4	0.06	0.11
BZD27C27P	F1	25.1	27	28.9	25	5	22	38.1	3.9	0.06	0.11
BZD27C30P	F2	28	30	32	25	5	24	42.2	3.6	0.06	0.11
BZD27C33P	F3	31	33	35	25	5	27	46.2	3.2	0.06	0.11
BZD27C36P	F4	34	36	38	10	5	30	50.1	3	0.06	0.11
BZD27C39P	F5	37	39	41	10	5	33	54.1	2.8	0.06	0.11
BZD27C43P	F6	40	43	46	10	5	36	60.7	2.5	0.07	0.12
BZD27C47P	F7	44	47	50	10	5	39	65.5	2.3	0.07	0.12
BZD27C51P	F8	48	51	54	10	5	43	70.8	2.1	0.07	0.12
BZD27C56P	F9	52	56	60	10	5	47	78.6	1.9	0.07	0.12
BZD27C62P	G0	58	62	66	10	5	51	86.5	1.7	0.08	0.13
BZD27C68P	G1	64	68	72	10	5	56	94.4	1.6	0.08	0.13
BZD27C75P	G2	70	75	79	10	5	62	103.5	1.5	0.08	0.13
BZD27C82P	G3	77	82	87	10	5	68	114	1.3	0.08	0.13
BZD27C91P	G4	85	91	96	5	5	75	126	1.2	0.09	0.13
BZD27C100P	G5	94	100	106	5	5	82	139	1.1	0.09	0.13
BZD27C110P	G6	104	110	116	5	5	91	139	0.72	0.09	0.13
BZD27C120P	G7	114	120	127	5	5	100	152	0.65	0.09	0.13
BZD27C130P	G8	124	130	141	5	5	110	169	0.59	0.09	0.13
BZD27C150P	G9	138	150	156	5	5	120	187	0.53	0.09	0.13
BZD27C160P	H0	153	160	171	5	5	130	205	0.48	0.09	0.13
BZD27C180P	H1	168	180	191	5	5	150	229	0.43	0.09	0.13
BZD27C200P	H2	188	200	212	5	5	160	254	0.39	0.09	0.13

Notes

- Maximum $V_F = 1.2\text{ V}$, at $I_F = 0.2\text{ A}$
 - Electrical characteristics when used as protection diodes
- (1) Non-repetitive peak reverse current in accordance with "IEC 60-1, section 8" (10/1000 μs pulse); see fig. 5

BASIC CHARACTERISTICS ($T_{amb} = 25\text{ }^{\circ}\text{C}$, unless otherwise specified)




Fig. 1 - Forward Current vs. Forward Voltage




Fig. 4 - Maximum Pulse Power Dissipation vs. Zener Voltage




Fig. 2 - Typ. Diode Capacitance vs. Reverse Voltage




Fig. 5 - Non-Repetitive Peak Reverse Current Pulse Definition






Fig. 3 - Power Dissipation vs. Ambient Temperature



PACKAGE DIMENSIONS in millimeters (inches): DO219-AB (SMF)




Foot print recommendation:



Created - Date: 15. February 2005
Rev. 3 - Date: 13. March 2007
Document no.:S8-V-3915.01-001 (4)
17247



Blisertape Dimensions for SMF in millimeters



Mat:	A0	B0	K0	W	T	P0	P2	P1	D0	D1	E	F
PS	1.9	4.0	1.5	8.0	0.235	4.0	2.0	4.0	1.5	1	1.75	3.5

Document-No.: S8-V-3717.02-001 (3)

18513



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.