


2		1				
LOC	DIST	REVISIONS				
G	14	P	LTR	DESCRIPTION	DATE	APVD
		H		REV PER ECR 09-025674	01DEC09	JR




- 1
- 2
- 3
- 4
- 5
- 6
- 7
- 8
- 9
- STAMP AMP 14-12, LOCATION AS SHOWN.
- WIRE INSULATION DIA RANGE IS 2.0-3.2 DIA.
- TONGUE MATERIAL THK IS 0.75±0.05
- DIMENSION APPLIES FROM CENTER OF STUD HOLE TO EDGE OF WIRE BARREL.
- MATERIAL: BODY - COPPER PER ASTM B-152
SLEEVE - NYLON, COLOR WHITE
- FINISH: BODY - TIN PLATE PER ASTM B-545
- MAX RECOMMENDED OPERATING TEMP 105°C
- VOLTAGE RATING: 300 V MAX
- WIRE CROSS SECTIONAL AREA RANGE:
1.65-3.45mm² [3,260-6,800] CMA

AMP
WIRE RANGE

14-12 AWG
SOLID OR STRANDED

500	LOOSE PIECE	152874
QTY	PACKAGING TYPE	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN jr ruth 05MAY06		 Tyco Electronics Tyco Electronics Corporation Harrisburg, PA 17105-3608		
DIMENSIONS: mm		CHK T MICHIELUTTI 05MAY06				
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .008 4 PLC ± - ANGLES ± 5°		APVD T MICHIELUTTI 05MAY06		NAME TERMINAL, RING TONGUE, PIDG, WIRE SIZE 14-12 AWG -	
			PRODUCT SPEC -			
			APPLICATION SPEC -			
			WEIGHT -			
MATERIAL 	FINISH 	SIZE A3		CAGE CODE 00779	DRAWING NO C-152874	RESTRICTED TO -
CUSTOMER DRAWING				SCALE 5:1	SHEET 1 OF 1	REV H