


5 Amp. Glass Passivated Fast Recovery Rectifier

<p>Dimensions in mm.</p> 	<p>Voltage 50 to 1000 V.</p> <p>Current 5.0 A. at 55 °C.</p> 
<p>Mounting instructions</p> <ol style="list-style-type: none"> 1. Min. distance from body to soldering point, 4 mm. 2. Max. solder temperature, 350 °C. 3. Max. soldering time, 3.5 sec. 4. Do not bend lead at a point closer than 4 mm. to the body. 	<ul style="list-style-type: none"> • Glass passivated junction • High surge capability • The plastic material carries U/L recognition 94 V-0 • Terminals: Axial Leads • Polarity: Color band denotes cathode

Maximum Ratings, according to IEC publication No. 134

		RGP 50A	RGP 50B	RGP 50D	RGP 50G	RGP 50J	RGP 50K	RGP 50M
V_{RRM}	Peak recurrent reverse voltage (V)	50	100	200	400	600	800	1000
$I_{F(AV)}$	Forward current at $T_{amb} = 55^\circ C$					5 A		
I_{FRM}	Recurrent peak forward current					60 A		
I_{FSM}	8.3 ms. peak forward surge current (Jedec Method)					300 A		
t_{rr}	Max. reverse recovery time from $I_F = 0.5 A$ $I_R = 1 A$ $I_{RR} = 0.25 A$			150 ns		250 ns	500 ns	
T_j	Operating temperature range				– 65 to + 175 °C			
T_{stg}	Storage temperature range				– 65 to + 175 °C			
E_{RSM}	Maximum non repetitive peak reverse avalanche energy. $I_R = 1 A$; $T_j = 25^\circ C$				20 mJ			

Electrical Characteristics at $T_{amb} = 25^\circ C$

V_F	Max. forward voltage drop at $I_F = 5 A$	1.3 V
I_R	Max. reverse current at V_{RRM} at $25^\circ C$	5 μA
R_{thj-a}	Max. thermal resistance ($I = 10$ mm.)	10 °C/W

Rating and Characteristic Curves

