

27 WATT

DUAL OUTPUT SWITCHING ADAPTOR

DTA27-0512FWX-W

GENERAL SPECIFICATION

This specification describes the performance characteristics of a single phase 27 Watts, Dual Output Switching Adaptor.



1) INPUT

Description	Min.	Nominal	Max.	Condition
Input Voltage	90VAC	115/230V	264VAC	Auto Range; 50/60Hz
Input Current(rms)	1A@264Vac 2A@90Vac			
Line Frequency	47Hz	50/60Hz	63Hz	-
Efficiency	>70% 115VAC at full load (DC Conversion)			
EMI: FCC Class B; CISRP22 Class B; EN 55022 Class B				

2) OUTPUT

2.1) ***Voltage Regulation:** $\pm 5\%$

***Hold up time:** 10ms typical at full load @ 115VAC

Model Name		Nominal Voltage	Max. Power	Output Current		Ripple & Noise
AC INLET 2PIN	AC INLET 3PIN			MIN.	MAX.	
DTA27-0512FWX-W-2	DTA27-0512FWX-W-3	+5	27W	0.5A	2A~5A	50mV
		+12		0.1A	0.2A~1.5A	120mV

NOTE: 1. Peak to Peak with 20MHz bandwidth and 10uF in parallel with a 0.1uF capacitor.

2. +5V and +12V combined load should not exceed 27W.

3) PROTECTION:

- OVER VOLTAGE PROTECTION(OVP)
- OUTPUT SHORT CIRCUIT PROTECTION
- AUTO RECOVERY

4) ENVIRONMENT

Operating Temperature

0°C to 40°C

Storage Temperature

-10°C to +70°C

MTBF: >100'000 hours at full load and 25°C ambient temperature.

5) SAFETY REQUIREMENTS

UL 1950

CSA 22.2-234

TUV EN60950

IEC 950

CE: EMC & LVD


6) DIMENTION DIAGRAM

Dimension: 106(L) × 60(W) × 30(H)mm


Input connector: IEC320-C7(2 PIN).

Output connector: Depends on your requirements.

AC INLET: 2PIN



AC INLET: 3PIN



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ETA-USA:](#)

[DTA27-0512FWX-W-3-047](#)