




B



1. WIRE RANGE : AWG #18 ~ #24
(0.75 ~ 0.2 mm²)
INSULATION RANGE : ϕ (1.3) ~ 3



SECT. "A"-"A"



SECT. "B"-**"B"**

GENERAL TOLERANCES	
10 UNDER	± 0.2
10 OVER 30 UNDER	± 0.25
30 OVER	± 0.3
ANGLE	$\pm 3^\circ$

LOOSE	GOLD PLATING	08-70-1012	5005GL
CHAIN		08-70-1011	↑ G
LOOSE	PRE- TINNED	08-70-0042	↓ TL
CHAIN		08-70-0001	5005T
FORM	FINISH	EDP NO.	ENG. NO.

				公差 (Tolerances)	所要数 (Req)	DRWG.
G	REVISED (J91011)	6/11/70	H.Y. 67	.000 → ±0.005 .00 → ±0.05		DSN'D
F	REVISED ECN NO. 1465	7/18/70	K.H. 600	.0 → ±0.1 → ±0.3	CHK'D	
E	REVISED PER ECN 1173	3/20/70		材料 (MAT'L)	APP'D	
D	REVISED PER ECN 1070	1/21/70	108	BRASS, 0.2t	MOLEX-JAPAN CO., LTD. 日本モレックス株式会社	
C	REVISED PER ECN 912	2/4/70	108	熱処理 (H.T.)		
B ₁	Revised Stopper	6/7/70	108	HRe		
B	REMOVED * ECN NO. 748	3/10/70	108	仕上げ (Finish)		
A	REVISED	10/21/70	108	SEE TABLE		
0	PROPOSED	10/1/77	108	Scale 4 1	No.	
記号 LTR	変更内容 (Rev.)	Date	Name	名称 (Name)		
				MINI.FIT	SD-5005 *	
					RECEPTACLE	

F




E

D


C

B

A



SECT. "A"- "A"



SECT. "B"- "B"

注)

1. 通用電線 範囲 AWG #18 - #24
0.75 ~ 0.2 mm² 被覆外径 中 (1.3) ~ φ3

一般公差	
10 未満	±0.2
10以上30未満	±0.25
30 以上	±0.3
角度	±3°

バラ状	金メッキ	08-70-1012	5005 GL
連鎖状	金メッキ	08-70-1011	↑ G
バラ状	錫メッキ	08-70-0042	↓ TL
連鎖状	錫メッキ	08-70-0001	5005T
形状	表面処理	EDP NO.	ENG. NO.

G	変更 (J91011)	89/11/30	H.H.	公差 (Tolerances)	所要数	DRWG.
F	REVISED ECN NO. 1445	10/12/79	K.H.	.000 → ±0.005 .00 → ±0.05	(Req)	DSN'D
E	REVISED PER ECN 1173	7/28/79	H.	.0 → ±0.1 . → ±0.3		CHK'D
D	REVISED PER ECN 1070	7/24/79	H.	材料 (MAT'L)		APP'D
C	REVISED PER ECN 912	9/4/79	H.	7/3 黄銅 0.2t		
B ₁	Revised Stopper	9/7/79	H.	熱処理 (H.T.)		
B	REMOVED * ECN NO. 748	7/28/79	H.	HRe		
A	REVISED	10/29/79	H.	仕上げ (Finish)		
O	PROPOSED	9/21/79	H.	表参照		
記号 (LTR)	変更内容 (Rev.)	Date	Name	Scale	名称 (Name)	No.
				4 1	MINI FIT	SD-5005*
					RECEPTACLE	

molex

MOLEX-JAPAN CO., LTD.
日本モレックス株式会社