





RECOMMENDED P.C.B. PATTERN LAYOUT

ハウジング:PA, ガラス充填, 灰色, UL94V-0
HOUSING:PA, GLASS FILLED, GRAY, UL94V-0

シールド ケース:銅合金 ($t=0.4$)

メツキ仕様

PLATING
ターミナル

接点部：3
CONTACT


SOLDER TAIL AREA: TIN 1.0MICRO METER MIN.
 予地部:ニッケルメッキ 1.0MICRO METER MIN.

シールド ケース

: TIN 1.0MICRO METER MIN.

UNDER PLATING: NICKEL 1.0 MICRO METER MIN.
本製品は50570、0511の鉛コイル品である。

THIS PRODUCT IS LEAD FREE OF 56579-0511



MODEL	No.56579-**19
-------	---------------

EN-02JA(021)

10

9

8

7

6

5

4

3

2

1

F


E

D


C

B

A



SECTION



MATING

MODEL No.56579-**-19

THIRD ANGLE
PROJECTION

REVISED EC NO: J2009-1533 DRAWN: SATO CHKD: MATSUMOTO APPR: NUKITA	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
		10 UNDER	± 0.2	DRAWN BY M. NAGATA	DATE 2004/03/10	TITLE USB SERIES MINI-AB REC. HS'G ASS'Y (DIP) -LEAD FREE-				
		10 OVER 30 UNDER	± 0.25	CHECKED BY K. TOJO	DATE 2004/03/10					
		30 OVER	± 0.3	APPROVED BY M. SASAO	DATE 2004/03/10	MOLEX INCORPORATED				
		ANGULAR ±3 °		MATERIAL NO. SEE SHEET1		DOCUMENT NO. SD-56579-014		SHEET NO. 2 OF 2		
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						
A	REV									

9

8

7

6

5

4

3

2