




REV. J

DIMENSIONS ARE IN INCHES		UNLESS OTHERWISE NOTED	TOLERANCES ARE:
ONE PLACE DECIMALS: $\pm .1$ [2.5]	THREE PLACE DECIMALS: $\pm .005$ [.127]	ANGLES $\pm 2^\circ$	
TWO PLACE DECIMALS: $\pm .01$ [.25]	FOUR PLACE DECIMALS: $\pm .0020$ [.0508]		

TITLE: SSA-SOLDER TAIL ASSEMBLY	DWG NO: SSA-1XX-S-X SHEET 1 OF 1
---------------------------------------	--



Do not scale
from this print

NOTES:

1. MINIMUM CONTACT PUSH-OUT FORCE: 16 oz.
2. INSERTION FORCE: 3.0 oz. AVG. PER CONTACT USING .018 [.46] DIA PIN.
3. WITHDRAWAL FORCE: 1.5 oz. AVG. PER CONTACT USING .018 [.46] DIA PIN.
4. C_1 REPRESENTS A CRITICAL DIMENSION.

PROPRIETARY NOTE
THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC INC. AND SHALL NOT BE
REPRODUCED OR TRANSFERRED TO
OTHER DOCUMENTS OR DISCLOSED TO
OTHERS OR USED FOR ANY PURPOSE
OTHER THAN THAT FOR WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED
WRITTEN CONSENT OF SAMTEC INC.

MATERIAL

MATERIAL:
INSULATOR:
DUPONT FR-530 RYNITE
CONTACT:
PHOSPHOR BRONZE

samtec

520 PARK EAST BLVD. NEW ALBANY, INDIANA 47150
PHONE (812) 944-6733 P.O. BOX 1147
CODE 55322

MISC\MKTG
SSAS-ASM

MADE BY:
MARK CHILTON 11-21-88

SSA-1XX-S-X
SHEET 1 OF 1