

SMD Power Inductor

CDRH129B



Description

- Ferrite drum core construction.
- Magnetically shielded.
- Winding to Winding voltage rating: 220Vrms.
- L × W × H:12.5 × 12.5 × 9.0 mm Max.
- Product weight: 4.5g(Ref.)
- Moisture Sensivity Level: 1
- RoHS compliance.

Environmental Data

- Operating temperature range: -40℃ ~ +125℃ (including coil's self temperature rise)
- Storage temperature range: -40℃ ~ +125℃
- Solder reflow temperature: 260 ℃ peak.



Packaging

- Carrier tape and reel packaging.
- 13" diameter reel.
- 300pcs per reel.



Applications

- Ideally used in LED lighting, DC/DC Converters and Transformer etc.

Dimension - [mm]



Land pattern and Schematics - [mm]



Electrical Characteristics


		Measuring condition	
Inductance	(1-2)	150μH ± 20% Within	1kHz, 1V
	(4-3)	40μH ± 20% Within	1kHz, 1V
D.C.R.	(1-2)	0.23Ω Max.(0.18Ω Typ.)	at 20℃
	(4-3)	0.66Ω Max.(0.53Ω Typ.)	at 20℃
Saturation Current ※1	(1-2)	2.1A	
	(4-3)	3.5A	
Temperature rise Current ※2	(1-2)	2.0A	
	(4-3)	1.0A	

※1 The saturation current: This indicates the value of DC current when the inductance decreases to 70% of it's nominal.
※2 Temperature rise current: The value of DC current when the temperature rise is ΔT=40℃ (Ta=20℃).


SMD Power Inductor CDRH129B



Saturation Current & Temperature Rise Graph



Solder Reflow Condition



Please refer to the sales offices on our website - <http://www.sumida.com>

Hong Kong

Tel.+852-2880-6781
FAX.+852-2565-9600
sales@hk.sumida.com

Saitama(Japan)

Tel.+81-48-691-7300
FAX.+81-48-691-7340
sales@jp.sumida.com

Chicago

Tel.+1-847-545-6700
FAX. +1-847-545-6720
sales@us.sumida.com

Shanghai

Tel.+86-21-5836-3299
FAX.+86-21-5836-3266
shanghai.sales@cn.sumida.com

Seoul

Tel.+82-2-6237-0777
FAX.+82-2-6237-0778
sales@kr.sumida.com

Obernzell

Tel.+49-8591-937-0
FAX. +49-8591-937-103
contact@eu.sumida.com

Shenzhen

Tel.+86-755-8291-0228
FAX.+86-755-8291-0338
shenzhen.sales@cn.sumida.com

Singapore

Tel.+65-6296-3388
FAX.+65-6841-4426
sales@sg.sumida.com

Neumarkt

Tel.+49-9181-4509-110
FAX. +49-9181-4509-310
infocomp@eu.sumida.com

Taipei

Tel.+886-2-8751-2737
FAX.+886-2-8751-2738
sales@tw.sumida.com

San Jose

Tel.+1-408-321-9660
FAX.+1-408-321-9308
sales@us.sumida.com