




SOLDER PAD LAYOUT




REPLACES PART #: SSL-LX223GD-TR11



PART NUMBER	SSL-LXA228GD-TR11	REV.	H
DATE	E.C.N. NUMBER AND REVISION COMMENTS		REV.
08.03.94	CHG'D SPECS. WHERE NOTED.		A
11.29.94	CHG'D WHERE NOTED.		B
11.07.95	ADDED LEAD WIDTHS, UPDATED LEAD O.A.L.		C
10.21.99	E.C.N. #10550. & #10BRDR.		D
05.05.04	E.C.N. #11122. & #10BRDR.		E
07.08.04	E.C.N. #11146.		F
11.14.06	E.C.N. #11148.		G
09.22.11	E.C.N. #10BRDR. & REDRAWN.		H

ELECTRO-OPTICAL CHARACTERISTICS $T_A=25^\circ\text{C}$ $I_f=20\text{mA}$					
PARAMETER	MIN	TYP	MAX	UNITS	TEST COND
PEAK WAVELENGTH		565 (GREEN)		nm	
FORWARD VOLTAGE		2.1	2.8	V_f	
REVERSE VOLTAGE	5.0			V_r	$I_r=100\mu\text{A}$
AXIAL INTENSITY		4		mcd	$I_f=20\text{mA}$
VIEWING ANGLE		50		2x theta	
EMITTED COLOR:	GREEN				
EPOXY LENS FINISH:	GREEN DIFFUSED				

LIMITS OF SAFE OPERATION AT 25°C		
PARAMETER	MAX	UNITS
PEAK FORWARD CURRENT*	160	mA
STEADY CURRENT	25	mA
POWER DISSIPATION	100	mW
DERATE FROM 25°C	- 1.2	mW/ $^\circ\text{C}$
OPERATING, STORAGE TEMP.	- 40 TO + 85	$^\circ\text{C}$

* $t < 10\mu\text{s}$ 

NOTES:

1. 1K PER REEL.

*UNLESS OTHERWISE SPECIFIED TOLERANCES PER DECIMAL PRECISION ARE: X=±1 (±0.039), X.X=±0.5 (±0.020), X.XX=±0.25 (±0.010), X.XXX=±0.127 (±0.005). LEAD SIZE=±0.05 (±0.002), LEAD LENGTH=±0.75 (±0.030). MIN.= +DECIMAL PRECISION MAX.= +DECIMAL PRECISION

UNCONTROLLED DOCUMENT