




	1	2	3	4	5	6	7																																																																																	
A	  <table><tr><td>②</td><td>Number of poles</td><td>Nx5,0</td><td><N-1>x5,0</td></tr><tr><td></td><td>2~6P</td><td>±0,15</td><td>±0,10</td></tr><tr><td></td><td>7~12P</td><td>±0,20</td><td>±0,20</td></tr><tr><td></td><td>13~18P</td><td>±0,30</td><td>±0,25</td></tr><tr><td></td><td>19~24P</td><td>±0,40</td><td>±0,30</td></tr></table>  P.C.B LAYOUT							②	Number of poles	Nx5,0	<N-1>x5,0		2~6P	±0,15	±0,10		7~12P	±0,20	±0,20		13~18P	±0,30	±0,25		19~24P	±0,40	±0,30																																																													
②	Number of poles	Nx5,0	<N-1>x5,0																																																																																					
	2~6P	±0,15	±0,10																																																																																					
	7~12P	±0,20	±0,20																																																																																					
	13~18P	±0,30	±0,25																																																																																					
	19~24P	±0,40	±0,30																																																																																					
B	Material - Terminal body (metal housing): Brass(CuZn) - Terminal screw:Steel Zinc plating"-slot type - Contacts: Brass - Surface of solder tail: Tin plated - Insulator (housing): Thermoplastic (UL94V-0), Green Electrical <table><tr><td>1. Voltage rating:</td><td>cULus/ FIMKO 300VAC/300VAC</td></tr><tr><td>2. Current rating:</td><td>16A /17,5A</td></tr><tr><td>3. Wire range:</td><td>0.5-1.5mm</td></tr><tr><td>4. Solid wire(AWG):</td><td>12-28</td></tr><tr><td>5. Stranded wire(AWG):</td><td>12-28</td></tr><tr><td>6. Torque:</td><td>3.5 Lb-In/ 0.4N.m</td></tr><tr><td>7. Screw:M3</td><td></td></tr><tr><td>8. Wire strip length:</td><td>6-7mm</td></tr><tr><td>9. Withstanding Voltage:</td><td>1.6KV / 2.5KV</td></tr><tr><td>10. Operating temperature:</td><td>-30°C to +105°C</td></tr><tr><td>11. Soldering temperature:</td><td>250°C±10°C/5 Sec</td></tr><tr><td>12. Safety Approval:</td><td>cULus Ⓟ</td></tr></table>							1. Voltage rating:	cULus/ FIMKO 300VAC/300VAC	2. Current rating:	16A /17,5A	3. Wire range:	0.5-1.5mm	4. Solid wire(AWG):	12-28	5. Stranded wire(AWG):	12-28	6. Torque:	3.5 Lb-In/ 0.4N.m	7. Screw:M3		8. Wire strip length:	6-7mm	9. Withstanding Voltage:	1.6KV / 2.5KV	10. Operating temperature:	-30°C to +105°C	11. Soldering temperature:	250°C±10°C/5 Sec	12. Safety Approval:	cULus Ⓟ																																																									
1. Voltage rating:	cULus/ FIMKO 300VAC/300VAC																																																																																							
2. Current rating:	16A /17,5A																																																																																							
3. Wire range:	0.5-1.5mm																																																																																							
4. Solid wire(AWG):	12-28																																																																																							
5. Stranded wire(AWG):	12-28																																																																																							
6. Torque:	3.5 Lb-In/ 0.4N.m																																																																																							
7. Screw:M3																																																																																								
8. Wire strip length:	6-7mm																																																																																							
9. Withstanding Voltage:	1.6KV / 2.5KV																																																																																							
10. Operating temperature:	-30°C to +105°C																																																																																							
11. Soldering temperature:	250°C±10°C/5 Sec																																																																																							
12. Safety Approval:	cULus Ⓟ																																																																																							
C																																																																																								
D																																																																																								
E																																																																																								
F																																																																																								
G	RoHS compliant Unit:mm <table><tr><td>Scale</td><td>1:1</td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>TOLERANCE</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>X.</td><td>±0.50</td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>X.X</td><td>±0.30</td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>X.XX</td><td>±0.10</td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>DIM</td><td>TOL</td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>X.°</td><td>±1°</td><td>②</td><td>Add the tolerance table</td><td>06.05.2014</td><td>Winnie</td><td></td><td></td></tr><tr><td>X.X°</td><td>±X°</td><td>①</td><td>Drawn</td><td>27.05.2009</td><td>Dean</td><td></td><td></td></tr><tr><td>Angle</td><td>TOL</td><td>Id.</td><td>Modification</td><td>Date</td><td>Name</td><td></td><td></td></tr></table> <table><tr><td>Customer-No.</td><td></td></tr><tr><td>ASSMANN WSW-No.</td><td>A-TB500-VIxxH</td></tr><tr><td>Drawing-No.</td><td>ASS 3525 CO</td></tr><tr><td>Replace</td><td>rev02</td></tr></table>							Scale	1:1							TOLERANCE								X.	±0.50							X.X	±0.30							X.XX	±0.10							DIM	TOL							X.°	±1°	②	Add the tolerance table	06.05.2014	Winnie			X.X°	±X°	①	Drawn	27.05.2009	Dean			Angle	TOL	Id.	Modification	Date	Name			Customer-No.		ASSMANN WSW-No.	A-TB500-VIxxH	Drawing-No.	ASS 3525 CO	Replace	rev02	
Scale	1:1																																																																																							
TOLERANCE																																																																																								
X.	±0.50																																																																																							
X.X	±0.30																																																																																							
X.XX	±0.10																																																																																							
DIM	TOL																																																																																							
X.°	±1°	②	Add the tolerance table	06.05.2014	Winnie																																																																																			
X.X°	±X°	①	Drawn	27.05.2009	Dean																																																																																			
Angle	TOL	Id.	Modification	Date	Name																																																																																			
Customer-No.																																																																																								
ASSMANN WSW-No.	A-TB500-VIxxH																																																																																							
Drawing-No.	ASS 3525 CO																																																																																							
Replace	rev02																																																																																							
H	<table><tr><td>1</td><td>2</td><td>3</td><td>4</td><td>5</td><td>6</td><td>7</td></tr></table>							1	2	3	4	5	6	7																																																																										
1	2	3	4	5	6	7																																																																																		