



LOC	DIST	REVISIONS					
AA	22	P	LTR	DESCRIPTION	DATE	DWN	APVD
			0	RLSD; NPR C97-014	24APR97	DLD	JT




1 MATERIAL: HOUSING - HIGH TEMPERATURE NYLON, BLACK,
IR COMPATIBLE, UL 94V-0.
TERMINALS - 0.33 [0.013] THICK PHOS BRONZE
PLATED WITH 1.27 μ m [0.00050] THICK HARD
GOLD IN LOCALIZED AREA AND 3.81 μ m [0.000150]
THICK TIN-LEAD IN SOLDER AREA OVER 1.27 μ m
[0.000050] THICK NICKEL UNDERPLATE.
SHIELD - 0.254 [0.010] THICK COPPER ALLOY
PLATED WITH 2.03 μ m [0.000080] MINIMUM
TIN-LEAD OVER 2.54 μ m [0.000100] MINIMUM
COPPER.

2 JACK CAVITY COMFORMS TO FCC RULES AND REGULATIONS, PART 68 SUBPART F.


3. ALL DIMENSIONS SHOWN ARE NOMINAL UNLESS OTHERWISE SPECIFIED.

 THIS HOLE REQUIRED FOR -2 ONLY.

 REAR GROUND TAB NOT REQUIRED FOR -1.



SUGGESTED PANEL CUTOUT
SCALE 2:1



SUGGESTED PC BOARD LAYOUT
COMPONENT SIDE
SCALE 2:1

WITH REAR PCB GROUND TAB	406562-2
5 WITHOUT REAR PCB GROUND TAB	406562-1
DESCRIPTION	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN DL DRUMMOND 24APR97 CHK DL DRUMMOND 25APR97 APVD J. TONEY 25APR97		AMP AMP Incorporated Harrisburg, PA 17105-3608	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME MODULAR JACK ASSEMBLY, 2 PORT, 8 POSITION, RIGHT ANGLE, SHIELDED, CAT 4	
		0 PLC ±- 1 PLC ±- 2 PLC ±0.25 [.011] 3 PLC ±0.13 [.005] 4 PLC ±- ANGLES ±-			
MATERIAL		FINISH		SIZE A2	
				CAGE CODE 00779	
		WEIGHT -		DRAWING NO C-406562	
CUSTOMER DRAWING				SCALE 4:1	
				SHEET 1 OF 1	
				REV 0	