



FCIconnect.com


Copyright FCI

PRODUCT NUMBER
XXXXX-YYYHPLF


- LEAD FREE OPTION
SEE NOTE 1,13
- SPECIAL OPTIONS
SEE NOTE 1 OR 10
- HIGH TEMPERATURE PLASTIC
SEE NOTE 1
- NO OF
POSITIONS
SEE NOTE 1
- PIN PLATING
SEE SHEET 2
- BASE PART NO.

67996-X XX-XXX XXX LF

- TAIL LENGTH (EXAMPLE BELOW)
3.0mm=030 12.8mm=128
(SEE NOTE 16 & 17)
- MATING LENGTH (EXAMPLE BELOW)
5.0mm=050 25.5mm=255
(SEE NOTE 16 & 17)
- TOTAL NUMBER OF POSITIONS
FROM 2 (2X1) THRU 72 (2X36) POS.
- PIN PLATING (SEE NOTE 14)
1=0.76µm Au
4= PURE TIN
8=0.36µm Au
- BASE PART NO.
DOUBLE ROW




TOP VIEW




SIDE VIEW

END VIEW



RECOMMENDED HOLE PATTERN



DETAIL P
SCALE 5:1
TYP BOTH ENDS

mat'l. code				surface		tolerance		projection		product family					
NOTE 2 & 3				ISO 1302 ✓		ISO 406 ISO 1101				BERGSTIK					
ltr	ecn no	dr	date	tolerances unless otherwise specified						title					
DF	N11-0180	J.Z	2011-05-31	angles	linear	XX±01/XX±3				BERGSTIK II HEADER D/R					
DG	ELX-N-13471	J.Z	2011-11-16			XXX±0.005/XXX±13		.100/2.54cc STRAIGHT							
DH	ELX-N-16105	ZK	2013-10-22			0°±2'		XXXX±0.020/XXX±.051		scale 2:1					
				dr	T.BREWBAKER		12/21/94				dwg no		sheet 1 of 8	size	
				enrg	T.HANNA		12/21/94				67996		A3		
				chr	J.MURPHY		12/21/94								
				appd	T.HANNA		12/21/94								
sheet index	revision sheet	DH	...	DH							type		Product	Customer	Drawing
		1	...	8											

PIN PLATING CODES:	
XXXX-1YY	30u"/0.76u MIN (SEE NOTE 14) OVER 50u"/1.27u MIN Ni
XXXX-2YY	15u"/0.38u MIN (SEE NOTE 14) OVER 50u"/1.27u MIN Ni
XXXX-3YY	50u"/1.27u MIN (SEE NOTE 14) OVER 50u"/1.27u MIN Ni
XXXX-4YY	100u"/2.54u MIN Sn OVER 50u"/1.27u MIN Ni (SEE NOTE 15)
XXXX-4YYHLF	
XXXX-5YY	15u"/0.38u MIN (SEE NOTE 14) OVER 50u"/1.27u MIN Ni
XXXX-6YY	30u"/0.76u MIN (SEE NOTE 14) OVER 50u"/1.27u MIN Ni
XXXX-7YY	30u"/0.76u MIN (SEE NOTE 14) OVER 50u"/1.27u MIN Ni
XXXX-8YY	15u"/0.38u MIN (SEE NOTE 14) OVER 50u"/1.27u MIN Ni
XXXX-9YY	15u"/0.38u MIN (SEE NOTE 14) OVER 50u"/1.27u MIN Ni
XXXX-0YY	30u"/0.76u MIN (SEE NOTE 14) OVER 50u"/1.27u MIN Ni

NOTES

1. PART NUMBER OPTIONS:
PIN PLATING CODES (SEE ABOVE)

HIGH TEMPERATURE MATERIAL:

PART NUMBERS WITH AND WITHOUT "H" WILL BE SUPPLIED WITH HIGH TEMPERATURE PLASTIC.

NUMBER OF POSITIONS :

EVEN NUMBER OF POSITIONS FROM 2 (2X1) THROUGH 72 (2X36).
-X00H INDICATES BERGSTRIIP PRODUCT. SEE PAGE 3
FOR SPECIAL GEOMETRY OF THIS CONTINUOUS STRIP PRODUCT.
AUTOMATED REELS WILL CONTAIN 45,000 PINS.
SEE SPECIFIC PART NUMBERS FOR AVAILABILITY.

PACKAGING:

PACKAGED IN POLY BAGS.
EIGHT DIGIT PART NUMBERS FOLLOWED BY A "T" ARE PACKAGED
IN TUBES. SEE SPECIFIC PART NUMBERS FOR AVAILABILITY.
EIGHT DIGIT PART NUMBERS FOLLOWED BY A "G" ARE PACKAGED
IN GPAX FOR IBM ONLY. SEE SPECIFIC PART NUMBERS FOR AVAILABILITY.
PART NUMBERS FOLLOWED BY A "C" ARE PACKAGED IN TUBES
WITH A PICKUP CAP APPLIED.
EIGHT DIGIT PART NUMBERS FOLLOWED BY A "A" ARE PACKAGED 
IN TAPE/REEL WITH PICKUP CAP P/N 95730-003 APPLIED, PER BUS-14-345.

LEAD FREE:

ADD "HLF" SUFFIX AT THE END OF PART NUMBER FOR LEAD FREE
OPTION, NOT AVAILABLE FOR -5YY,-5YYH, -6YY & -6YYH

2. BODY MATERIAL:

BODY MATERIAL : MANUFACTURER'S OPTION OF NYLON, PCT GLASS FIBER
REINFORCED OR MINERAL FILLED LCP FLAME RETARDENT PER UL-94V-0.
COLOR: BLACK

BERGSTRIIP™ PRODUCED WITH HIGH TEMPERATURE LCP
THERMOPLASTIC, FLAME RETARDENT PER UL-94V-0.
COLOR: BLACK

PART NUMBERS WITH "H" AND WITHOUT SUFFIX WILL WITHSTAND EXPOSURE
TO 260° C PEAK TEMPERATURE FOR 20 SECONDS IN
WAVE SOLDER, INFRA-RED OR VAPOR PHASE SOLDER PROCESS.

3. PIN MATERIAL: PHOS BRONZE.

4. MEASURED WITH PART IN RESTRAINED CONDITION.

5. TWO SIDES OF PIN TIPS NOT PLATED. TYPICAL BOTH ENDS.

6. 2LBS/0.9KG MIN PIN RETENTION IN EITHER DIRECTION.

7. MILITARY BERGSTIK HEADER
P/N XXXXX-XY-MIL
NOT AVAILABLE.

8. ±.010/0.25 TOL APPLIES TO ALL "G" TAILS EXCEPT
INDICATED PARTS ON TABLE WHERE +.010/0.25 -.000/0.00
APPLIES.

9. NOTCH CONFIGURATION WILL VARY PER VENDOR'S DISCRETION.

10. BERGSTRIIP™ PART NUMBERS FOLLOWED BY
BY A "B" ARE BULK PRICED.

11. TAIL LENGTH (DIM. G) TO BE ±.008/.020.

12. POSITIONS PER ROW 37 TO 50 CAN BE PRODUCED,
BUT FLATNESS AND CURVATURE MAY NOT BE
HELD AS CLOSE AS 36 POSITIONS.

13. THESE PRODUCTS MEETS EUROPEAN UNION DIRECTIVES AND OTHER
COUNTRY REGULATION AS DESCRIBED IN GS-22-008.

14. PLATING OPTIONS:
PERFORMANCE PLATING WILL BE EITHER GOLD OR GXT ON POST OR TAIL,
OPTIONALLY (78~295u"/2~7.5u) TIN ON TAIL.

15. "THIS PRODUCT HAS 100% TIN PLATING IN THE INTERFACE AND
HAS NOT BEEN TESTED FOR WHISKER GROWTH IN ALL INTERCONNECT
ENVIRONMENTS."

16. THE OAL DON'T EXCEED 34.5mm



17. INCREMENTS BY 0.1mm IN LENGTHS ONLY

18. FOR SPECIAL PACKAGING REQUEST PLEASE CONTACT PRODUCT MANAGER FOR AVAILABILITY

19. TO DETERMINE DIMENSIONS:
N=NUMBER OF POSITION PER ROW
EXAMPLE: 10 POS. N X .100/2.54

mat'l. code				surface		tolerance		projection		product family				
NOTE 2 & 3				ISO 1302 ✓		ISO 406 ISO 1101				BERGSTIK				
ltr	ecn	no	dr	date		tolerances unless otherwise specified				title				
DG						angles	linear	XXX±01/XX±3		BERGSTIK II HEADER D/R				
								XXX±0.005/XXX±.13		.100/2.54cc STRAIGHT				
						0°±2°		XXX±0020/XXX±.05		scale 2:1				
				dr	T.BREWBAKER	12/21/94				dwg no		sheet 2 of 8		size
				engr	T.HANNA	12/21/94				67996		A3		
				chr	J.MURPHY	12/21/94								
				appd	T.HANNA	12/21/94				type Product Customer Drawing				
sheet index		revision sheet												

REEL PACKING DIMENSIONS



mat'l. code NOTE 2 & 3				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family BERGSTIK			
ltr	ecn no	dr	date	tolerances unless otherwise specified						title			
DH				angles		linear		INCH/MM		BERGSTIK II HEADER D/R			
										.100/2.54cc STRAIGHT			
				0°±2'		XXXX±.0020/XXX±.051		scale 2:1					
				dr	T.BREWBAKER	12/21/94				dwg no		sheet 3 of 8	size
				enr	T.HANNA	12/21/94				67996		A3	
				chr	J.MURPHY	12/21/94							
				appd	T.HANNA	12/21/94							
sheet index		revision sheet								type Product Customer Drawing			

1				2		3							4		5		6										
PRODUCT NUMBER		TOT. PIN LGTH.		TAIL LENGTH		MATING LENGTH						BERGSTRIPTM		LF													
		DIM F		DIM G		DIM H		PACKAGING		NOTES		AVAILABLE		OPTION													
		ENGLISH		METRIC		ENGLISH		METRIC																			
69132-XYX		0.760		19.30		0.120		3.05		0.540		13.72		POLY BAGS/TUBES		---		---		NO		OB NOTE 1,13					
69133-XYX		0.615		15.62		0.285		7.24		0.230		5.84		POLY BAGS		---		---		NO							
69157-XYX		0.410		10.41		0.110		2.79		0.200		5.08		POLY BAGS		---		---		NO							
71217-XYXH		1.000		25.40		0.450		11.43		0.450		11.43		POLY BAGS		---		---		NO				OB			
71222-XYXH		0.850		21.59		0.250		6.35		0.500		12.70		POLY BAGS		---		---		NO				OB			
72273-XYXH		0.725		18.42		0.110		2.79		0.515		13.08		POLY BAGS		---		---		NO				OB			
72448-XYXH		0.658		16.71		0.172		4.37		0.386		9.80		POLY BAGS		---		---		NO				OB			
72455-XYXH		0.598		15.19		0.180		4.57		0.318		8.08		POLY BAGS		---		---		NO				OB			
72455-632HG		0.598		15.19		0.180		4.57		0.318		8.08		GPAX		NOTE 1		---		---				NO		OB	
73503-XYXH		0.420		10.67		0.120		3.05		0.200		5.08		POLY BAGS		---		---		NO				OB			
73596-XYXH		0.795		20.19		0.110		2.79		0.585		14.86		POLY BAGS		---		---		NO				OB			
74317-XYXH		0.532		13.51		0.309		7.85		0.123		3.12		POLY BAGS		NOTE 11		---		---				NO		OB	
74318-XYXH		0.592		15.04		0.369		9.37		0.123		3.12		POLY BAGS		NOTE 11		---		---				NO		OB	
74999-XYXH		0.508		12.90		0.090		2.29		0.318		8.08		POLY BAGS		---		---		NO				OB			
78212-XYX		0.710		18.03		0.350		8.89		0.260		6.60		POLY BAGS		---		---		NO				OB			
78233-XYX		0.568		14.43		0.150		3.81		0.318		8.08		POLY BAGS		---		---		---				NO			
78269-XYX		0.385		9.78		0.095		2.41		0.190		4.83		POLY BAGS		---		---		NO				OB			
78286-XYX		0.500		12.70		0.160		4.06		0.240		6.10		POLY BAGS/TUBES		---		---		NO				OB			
78932-XYX		UNAVAILABLE		UNAVAILABLE		UNAVAILABLE		UNAVAILABLE		UNAVAILABLE		UNAVAILABLE		UNAVAILABLE		---		---		---		---					
78933-XYX		0.695		17.65		0.285		7.24		0.310		7.87		POLY BAGS		---		---		NO		OB					
78988-XYX		0.540		13.72		0.135		3.43		0.305		7.75		POLY BAGS		---		---		NO		OB					
78989-XYX		UNAVAILABLE		UNAVAILABLE		UNAVAILABLE		UNAVAILABLE		UNAVAILABLE		UNAVAILABLE		UNAVAILABLE		---		---		---		---					
78990-XYX		UNAVAILABLE		UNAVAILABLE		UNAVAILABLE		UNAVAILABLE		UNAVAILABLE		UNAVAILABLE		UNAVAILABLE		---		---		---		---					
78991-XYX		UNAVAILABLE		UNAVAILABLE		UNAVAILABLE		UNAVAILABLE		UNAVAILABLE		UNAVAILABLE		UNAVAILABLE		---		---		---		---					
78992-XYX		UNAVAILABLE		UNAVAILABLE		UNAVAILABLE		UNAVAILABLE		UNAVAILABLE		UNAVAILABLE		UNAVAILABLE		---		---		---		---					
78993-XYX		UNAVAILABLE		UNAVAILABLE		UNAVAILABLE		UNAVAILABLE		UNAVAILABLE		UNAVAILABLE		UNAVAILABLE		---		---		---		---					
78994-XYX		UNAVAILABLE		UNAVAILABLE		UNAVAILABLE		UNAVAILABLE		UNAVAILABLE		UNAVAILABLE		UNAVAILABLE		---		---		---		---		NOTE 1,13			

A

B

C

mat'l. code				surface		tolerance		projection		product family			
NOTE 2 & 3				ISO 1302		ISO 406				BERGSTIK			
litr		ecn no		dr		date		tolerances unless otherwise specified		title			
DH								linear		BERGSTIK II HEADER D/R			
								0°±2'		.100/2.54cc STRAIGHT			
								dr		T.BREWBAKER		12/21/94	
								engr		T.HANNA		12/21/94	
								chr		J.MURPHY		12/21/94	
								appd		T.HANNA		12/21/94	
sheet index		revision sheet											

FCI										dwg no				sheet 5 of 8				size			
										67996										A3	
type		Product		Customer		Drawing															

PRODUCT NUMBER	TOT. PIN LGTH.		TAIL LENGTH		MATING LENGTH		PACKAGING	NOTES	BERGSTRIPTM AVAILABLE	LF OPTION
	DIM F	DIM F	DIM G	DIM G	DIM H	DIM H				
	ENGLISH	METRIC	ENGLISH	METRIC	ENGLISH	METRIC				
78995-YYY	UNAVAILABLE		UNAVAILABLE		UNAVAILABLE			-	-	NOTE 1,13
78996-YYY	UNAVAILABLE		UNAVAILABLE		UNAVAILABLE			-	-	
79242-YYY	0.930	23.62	0.340	8.64	0.490	12.45	POLY BAGS	-	NO	OB
79243-YYY	1.230	31.24	0.390	9.91	0.740	18.80	POLY BAGS	-	NO	OB
79244-YYY	UNAVAILABLE		UNAVAILABLE		UNAVAILABLE			-	-	
79268-YYY	1.020	25.91	0.120	3.05	0.800	20.32	POLY BAGS	-	NO	OB
79271-YYY	1.100	27.94	0.500	12.70	0.500	12.70	POLY BAGS	-	NO	OB
79425-YYY	0.410	10.41	0.120	3.05	0.190	4.83	POLY BAGS	-	NO	
79821-YYY	0.730	18.54	0.200	5.08	0.430	10.92	POLY BAGS	-	NO	
84610-YYYH	0.380	9.65	0.120	3.05	0.160	4.06	POLY BAGS	-	NO	OB
84760-YYYH	0.870	22.09	0.150	3.81	0.620	15.74	POLY BAGS	-	NO	OB
84784-YYYH	1.130	28.70	0.122	3.09	0.908	23.06	POLY BAGS	-	NO	OB
84934-YYYH	1.375	34.93	0.625	15.88	0.650	16.51	POLY BAGS	-	NO	OB
84976-YYYH	0.730	18.54	0.400	10.16	0.230	5.84	POLY BAGS	-	NO	OB
86503-YYY	0.470	11.94	0.120	3.05	0.250	6.35	POLY BAGS	-	NO	
86581-YYY	0.450	11.43	0.120	3.05	0.230	5.84	POLY BAGS	NOTE 8	NO	OB
86817-YYY	0.925	23.50	0.120	3.05	0.705	17.91	POLY BAGS	-	NO	OB
86827-YYY	0.700	17.78	0.120	3.05	0.480	12.19	POLY BAGS	-	NO	OB
86832-YYY	0.525	13.34	0.100	2.54	0.325	8.26	POLY BAGS	-	NO	
86834-YYY	1.335	33.91	0.585	14.86	0.650	16.51	POLY BAGS	-	NO	OB
86836-YYY	0.870	22.10	0.120	3.05	0.650	16.51	POLY BAGS	-	NO	OB
86837-YYY	0.600	15.24	0.120	3.05	0.380	9.65	POLY BAGS	-	NO	
87037-YYY	1.240	31.50	0.120	3.05	1.020	25.91	POLY BAGS	-	NO	OB
87052-YYY	0.990	25.15	0.120	3.05	0.770	19.56	POLY BAGS	-	NO	
87203-YYY	0.545	13.84	0.150	3.81	0.295	7.49	POLY BAGS	-	NO	
87344-YYY	1.375	34.93	0.219	5.56	1.056	26.82	POLY BAGS	-	NO	OB

NOTE 1,13



FCJ  FCJconnect.com

Copyright FCI

D

mat'l. code					surface			tolerance			projection			product family																																																																																																																																																																																																																																																																																																																																																																																																																																																																							
NOTE 2 & 3					ISO 1302 ✓			ISO 406 ISO 1101						BERGSTIK																																																																																																																																																																																																																																																																																																																																																																																																																																																																							
ltr		ecn no		dr	date		tolerances unless otherwise specified								title																																																																																																																																																																																																																																																																																																																																																																																																																																																																						
DH							angles		linear		$.XXX \pm .01 / .X \pm .3$		INCH/MM		BERGSTIK II HEADER D/R																																																																																																																																																																																																																																																																																																																																																																																																																																																																						
											$.XXX \pm .005 / .XX \pm .13$				.100/2.54cc STRAIGHT																																																																																																																																																																																																																																																																																																																																																																																																																																																																						
							$0 \pm .2"$				$.XXX \pm .0020 / .XXX \pm .05$		scale 2:1																																																																																																																																																																																																																																																																																																																																																																																																																																																																								
							dr		T.BREWBAKER		12/21/94				dwg no				sheet 6 of 8				size																																																																																																																																																																																																																																																																																																																																																																																																																																																														
							engr		T.HANNA		12/21/94				67996				A3																																																																																																																																																																																																																																																																																																																																																																																																																																																																		
							chr		J.MURPHY		12/21/94																																																																																																																																																																																																																																																																																																																																																																																																																																																																										
							appd		T.HANNA		12/21/94				type				Product Customer Drawing																																																																																																																																																																																																																																																																																																																																																																																																																																																																		
sheet index		revision sheet																																																																																																																																																																																																																																																																																																																																																																																																																																																																																			

