




REV. 3
DCO 63333

COIL: @ 25°C
 RESISTANCE _____ 390 OHMS $\pm 10\%$
 NOMINAL VOLTAGE _____ 26.5 VDC
 MUST OPERATE _____ 14.0 VDC @ 25°C


 MUST RELEASE _____ 1.4 VDC @ 25°C

ENVIRONMENT:

VIBRATION _____ 10 _____ CPS TO _____ 2000 _____ CPS @ _____ 15 _____ g's
 SHOCK _____ 100 _____ g's _____ 6 _____ MS. DURATION
 TEMPERATURE _____ -65 _____ °C TO _____ +125 _____ °C

NOTES: _____ OPERATE & RELEASE 7 MS. MAX.
 _____ (INCLUDING BOUNCE)

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: _____ LOW LEVEL TO
 _____ 2 AMP 28 VDC RESISTIVE

DR. R.B. 2/25/93

CK.TLG 10-24-00

CI Technologies
 advanced control electronic solutions

CUST. _____ QPL
 CUST. NO. M39016/40-001 REV. _____

'SR' RELAY

SR-7601