


8	7
NO	ITEM
1	Resistance
2	Torque
3	Terminals
4	Adjustment Tool
5	Flammability
6	Wiper
7	Insulation Resistance
8	Standard Packaging
9	Temperature Range
10	Weight

SPECIFICATION
10000ohm
3.0oz-in max
Solderable pins
H-90
UL 94V-0
50%(Actual TR) ± 10%
500VDC 1000megohms min
50pcs. per tube
-55° C-+125° C
0.020z.



Rev.	Revision	Date
01	Update	10/14/2010

TOLERANCES: ± 0.25(.010) EXCEPT WHERE NOTED

DIMENSIONS ARE: _____ MM _____ (INCHES)

DRAWN	David	10/14/2010	UNIT: mm
CHECKED	Sara	10/14/2010	
ENG APPR.			
MFG APPR.			
Sinotech			
SIZE		DWG. NO.	REV
A4		241146	01
SCALE: 6:1		Weight(oz): 0.02	SHEET 1 OF 1

3362P-103