


[Skip to content](#)Search By: Part Number Text [Tips](#)

Sunday, April 30, 2006

[Sign In](#)[Home](#) > [Products](#) > [By Type](#) > [Terminal Blocks & Strips](#) > [Product Feature Selector](#) > Product Details

Product Details for 0625

**0625
(625)**

Tyco Part Number: 1-1437393-2

[Superseded Search for Replacement Parts](#)

NEMA Terminal Blocks

[RoHS Compliant](#)

Product Highlights:

- 600 Series Block Series
- Terminal Block
- Block Type = Dovetail Base
- Mount Style = Channel Mount (Dovetail Base)
- Contact Type = Tubular Clamp

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages / Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Additional Product Images:

- [Line Drawing](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Terminal Block
- Screw Size = 10-32 Slotted Pan Head

Electrical Characteristics:

- Voltage Rating (VAC) = 300

Body Related Features:

- [Block Series](#) = 600 Series
- [Block Type](#) = Dovetail Base
- Mount Style = Channel Mount (Dovetail Base)
- [Wire Range \(Solid and Stranded\)\[MCM\]\(AWG\)](#) = 22-10
- [Blown Fuse Indicator](#) = Without
- [Blown Fuse Indicator Type](#) = None
- Amperes (Amps.) = 30.0
- Wire Strip Length (mm [in]) = 8.74 [0.344]

Contact Related Features:

- Contact Type = Tubular Clamp
- Pitch (mm [in]) = 9.53 [0.375]

Housing Related Features:

- [Housing Material](#) = Nylon (Painted)

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Operation / Application:

- Application = Medium Duty

Packaging Related Features:

- Terminals Per Foot = 30

Other:

- Brand = Buchanan

Languages: English | [Deutsch](#) | [Español](#) | [Português \(do Brasil\)](#) | [Italiano](#) | [正體中文 \(繁體\) \(Chinese\)](#) | [中文 \(•体\) \(Simplified Chinese\)](#) | [日本語 \(Japanese\)](#)

Country Sites: [China](#) | [Japan](#)

© 2006 Tyco Electronics All Rights Reserved

[Home](#) | [Customer Support](#) | [Supplier](#) | [Site Map](#) | [Privacy Policy](#) | [Browser Support](#)