






PRODUCT NUMBER	DIM "A"	DIM "L"	DIM "H"	DIM "R"	DIM "X"	PLATING CONTACT AREA	PLATING REMAINDER OF PIN
76772-101	6.28/.247	8.76/.345	5.97/.235	1.22/.048	5.30/.209	1.27µm/50µ" Au OVER 1.27µm/50µ" Ni	0.2µm/8µ" Au OVER 1.27µm/50µ" Ni
76772-101LF	6.28/.247	8.76/.345	5.97/.235	1.22/.048	5.30/.209	1.27µm/50µ" Au OVER 1.27µm/50µ" Ni	0.2µm/8µ" AU OVER 1.27µm/50µ" Ni

REELING PRODUCT TO CUSTOMER




NOTES:

- BURNISH MARKS PERMITTED ON PIN.
- BASE MATERIAL PIN: 3/4 HARD PHOSPER BRONZE A.S.T.M. B-159-66.
- CARRIER STRIP MATERIAL: 1/2 HARD BRASS A.S.T.M. B-36-67 ALLOY 260.
- MAX. BURRS PERMITTED IN AREA "Y" IS 0.01/0.04 OVER AREA "Z" 0.04/0.016.
- PIN TIP NOT PLATED ON THIS SIDE.
- WITH THE EXCEPTION OF STAR AREA. RADIUS AT 4 PIN CORNERS MAX. 0.05/0.002.
- PART NUMBERS WITH A LF SUFFIX MEET EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.




SECTION B-B
SCALE 50:1

TYP. 0.25 MAX.
0.010 MAX.



DETAIL P
SCALE 50:1



DETAIL Q
SCALE 50:1

mat'l. code NOTE 2 & 3				surface ISO 1902 ✓		tolerance ISO 406 ISO 1101		projection mm/inch		product family PIN PRODUCTS	
lfr	ecn no	dr	date	tolerances unless otherwise specified		.X±.3/.XX±.01		scale 1:1		title SELECTIVE PLATED BERG PIN	
F	V05-1138	VS	2/23/06	angles	linear	.00±.13/.000±.005		FCI		dwg no 76772	
				0°±2°		.000±.001/.0000±.0002				sheet 1 of 1 size A3	
				dr	V.SEBASTIAN	2/23/06				type Product Customer Drawing	
				engr	T.BREWBAKER	2/23/06					
				chr	T.BREWBAKER	2/23/06					
				appd	T.BREWBAKER	2/23/06					
sheet	revision	F									
index	sheet	1									