



HHR-300SCP/FT Cylindrical SC size (HR23/43)

Dimensions (with tube) (mm)



Typical charge characteristics



Specifications

Diameter	23.0+0 / -1.0mm
Height	43.0+0 / -1.5mm
Approximate Weight	57g

Nominal Voltage		1.2V
Discharge Capacity ^{*1}	Average ^{*2}	3,050mAh
	Rated (min)	2,800mAh
Approx. Internal impedance at 1000Hz at charged state		4mΩ
	Charge	Standard 300mA x 16hrs.
		Rapid ^{*3} 3,000mA x 1.2hrs.
Ambient Temperature	Charge	Standard 0°C to 45°C
		Rapid 0°C to 40°C
	Discharge -10°C to 65°C	
	Storage	<1 year -20°C to 35°C
		<3 months -20°C to 45°C
		<1 month -20°C to 55°C

^{*1} After charging at 0.1It for 16 hours, discharging at 0.2It.
^{*2} For reference only.
^{*3} Need specially designed control system. Please contact Panasonic for details.

Battery performance and cycle life are strongly affected by how they are used. In order to maximize battery safety, please consult Panasonic when determining charge/discharge specs, warning label contents and design.

^{*}The data in this document are for descriptive purposes only and are not intended to make or imply any guarantee or warranty.

Typical discharge characteristics

