

**HIGH VOLTAGE ASSEMBLED RECTIFIER**

**VOLTAGE RANGE 5000 to 16000 Volts CURRENT 0.75 Amperes**

**FEATURES**

- \* Low cost
- \* Low leakage
- \* Isolated case
- \* Surge overload rating - 50 amperes peak
- \* Mounting position: Any
- \* Low forward voltage drop

**MECHANICAL DATA**


- \* Epoxy: Device has UL flammability classification 94V-O

**MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS**

Ratings at 25 °C ambient temperature unless otherwise specified.  
Single phase, half wave, 60 Hz, resistive or inductive load.  
For capacitive load, derate current by 20%.



**HVP**



Dimensions in inches and (millimeters)

**MAXIMUM RATINGS** (At  $T_A = 25^\circ\text{C}$  unless otherwise noted)

| RATINGS                                                                                           | SYMBOL         | HVP5         | HVP8 | HVP10 | HVP12 | HVP14 | HVP15 | HVP16 | UNITS            |
|---------------------------------------------------------------------------------------------------|----------------|--------------|------|-------|-------|-------|-------|-------|------------------|
| Maximum Recurrent Peak Reverse Voltage                                                            | $V_{RRM}$      | 5            | 8    | 10    | 12    | 14    | 15    | 16    | K Volts          |
| Maximum RMS Voltage                                                                               | $V_{RMS}$      | 3.5          | 5.6  | 7.0   | 8.4   | 9.8   | 10.5  | 11.2  | K Volts          |
| Maximum DC Blocking Voltage                                                                       | $V_{DC}$       | 5            | 8    | 10    | 12    | 14    | 15    | 16    | K Volts          |
| Maximum Average Forward Rectified Current at $T_A = 50^\circ\text{C}$                             | $I_O$          | 750          |      |       |       |       |       |       | mAmps            |
| Peak Forward Surge Current 8.3 ms single half sine-wave superimposed on rated load (JEDEC method) | $I_{FSM}$      | 50           |      |       |       |       |       |       | Amps             |
| Operating and Storage Temperature Range                                                           | $T_J, T_{STG}$ | -20 to + 135 |      |       |       |       |       |       | $^\circ\text{C}$ |

**ELECTRICAL CHARACTERISTICS** (At  $T_A = 25^\circ\text{C}$  unless otherwise noted)

| CHARACTERISTICS                                         | SYMBOL | HVP5 | HVP8 | HVP10 | HVP12 | HVP14 | HVP15 | HVP16 | UNITS            |
|---------------------------------------------------------|--------|------|------|-------|-------|-------|-------|-------|------------------|
| Maximum Instantaneous Forward Voltage at 0.35A DC       | $V_F$  | 8.0  |      |       | 14.0  |       |       |       | Volts            |
| Maximum DC Reverse Current at Rated DC Blocking Voltage | $I_R$  |      |      |       | 5.0   |       |       |       | $\mu\text{Amps}$ |

NOTES: Enough heat sink must be considered in application.

## RATING AND CHARACTERISTIC CURVES ( HVP5 THRU HVP16 )

FIG. 1 - TYPICAL FORWARD CURRENT DERATING CURVE




FIG. 2 - MAXIMUM NON-REPETITIVE FORWARD SURGE CURRENT




FIG. 3 - TYPICAL REVERSE CHARACTERISTICS




FIG. 4 - TYPICAL INSTANTANEOUS FORWARD CHARACTERISTICS

