




887329302	USB 28#/22#	3340+0/-50	887808229	887800019
887329002	USB 28#/28#	820+0/-30	887808218	887800019
887329220	USB 28#/24#	2090+0/-40	887808234	887800043
887329120	USB 28#/24#	1320±25	887808243	887800043
887329020	USB 28#/24#	820±15	887808243	887800043
887329402	USB 28#/20#	5010+0/-80	887808230	887800019
887329202	USB 28#/24#	2090+0/-40	887808239	887800019
887329102	USB 28#/26#	1320+0/-30	887808228	887800019
887328102	USB 28#/24#	1800+0/-30	887808239	887800019
887328100	USB 28#/24#	1800+0/-30	887808238	887800043
887328000	USB 28#/26 #	1000+0/-30	887808204	887800043
887328002	USB 28#/26#	1000+0/-30	887808228	887800019
MOLEX P/N	DESCRIPTION	LENGTH	CABLE P/N	PVC P/N

ENTER DESCRIPTION EC NO: DG2006-0163 DRWN:PDAI CHKD: APPR:TKAN B		2006/01/20 2006/01/20 2006/01/20		QUALITY SYMBOLS ▽=0 ▽C=0		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE ---		DESIGN UNITS METRIC		THIRD ANGLE PROJECTION			
								DRAWN BY XHLEI		DATE 2006/01/20		TITLE USB A-B CABLE ASSY					
						4 PLACES ± ---		± ---		CHECKED BY ZXDENG						DATE 2006/01/20	
						3 PLACES ± ---		± ---		APPROVED BY BORON		DATE 2006/01/20		MOLEX INCORPORATED			
						2 PLACES ± ---		± ---		MATERIAL NO. SEE TABLE		DOCUMENT NO. SD-88732-002					
						1 PLACE ± ---		± ---		SIZE A/4		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					
						ANGULAR ± ---°											
						DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS											

7	6	5	4	3	2	1	
E	NOTE:1 1.MOLDED WITH PVC RESIN P/N:SEE TABLE						E
D	2.ELECTRICAL PERFORMANCE: 2.1 DIELECTRIC STRENGTH 2.2 INSULATION RESISTANCE 2.3 CONDUCTIVE RESISTANCE 2.4 CABLE IMPEDANCE 2.5 ATTENUATION 2.6 PROPAGATION DELAY 2.7 SIGNAL PAIR SKEW						D
	RETER TO ES-003 ELECTRICAL SPECIFICATION FOR DETAILS						
	3.THIS PRODUCT MUST MEET MX RoHS COMPLIANCE.						
C							C
B							B
A							A

ENTER DESCRIPTION
EC NO: DG2006-0163
DRWN:POAI
CHKD:
APPR:TKAN

2006/01/20
2006/01/20
2006/01/20

DESCRIPTION
REV

QUALITY SYMBOLS
=0
=0

GENERAL TOLERANCES (UNLESS SPECIFIED)
mm INCH
4 PLACES ± --- ± ---
3 PLACES ± --- ± ---
2 PLACES ± --- ± ---
1 PLACE ± --- ± ---
ANGULAR ± ---°
DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

DIMENSION STYLE
MM ONLY
DRAWN BY DATE
XHLEI 2006/01/20
CHECKED BY DATE
ZXDENG 2006/01/20
APPROVED BY DATE
BORON 2006/01/20
MATERIAL NO.
SEE TABLE
SIZE A 4

SCALE

DESIGN UNITS
METRIC

THIRD ANGLE PROJECTION

TITLE
USB A-B CABLE ASSY

MOLEX INCORPORATED

DOCUMENT NO.
SD-88732-002

SHEET NO.
2 OF 2

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

J	COPPER FOIL 877801083		2		
H	TERMINAL		8		
G	HOUSING 887809085		1		
F	REAL SHELL 887809082		1		
E	FRONT SHELL 887809081		1		
D	USB CABLE SEE TABLE				
C	REAR SHELL 887809084		1		
B	FRONT SHELL 887809083		1		
A	CRIMP HOUSING 887809086		1		
PIN ASSIGNMENTS		ITEM	DESCRIPTION	L	QTY.

tb_frame_A4_P_ME_T
Rev. D 2004/04/02

6	5	4	3	2	1
---	---	---	---	---	---