


# Pushbutton, Double Pole



| NTE<br>Type No. | Circuitry | Action |    | Actuator  |       | Diag<br>No. |
|-----------------|-----------|--------|----|-----------|-------|-------------|
|                 |           |        |    | Material  | Color |             |
| 54-393          | DPDT      | ON     | ON | Polyamide | Black | S68         |

SPECIAL NOTE: ( ) = Momentary Function

S68



## Specifications

**Current Rating:** 3A 125VAC  
**Insulation Resistance:** 100 Megohms (min.)  
**Dielectric Strength:** 1000V RMS (min.)  
**Temperature Rating:** +14° to +131°F (-10° to +55°C)  
**Electrical Life:** 10,000 cycles  
**Mechanical Life:** 30,000 cycles  
**Terminal Type:** Solder Lug  
**Mounting Hole:** .244 (6.2)

# Pushbutton, Starter Button, Single Pole



## Features


- Heavy Duty Die Cast Construction
- Rubber Dust and Moisture Resistant Boot Nut Included
- Starter Button Applications



| NTE<br>Type No. | Circuitry | Action |      | Actuator |       | Diag<br>No. |
|-----------------|-----------|--------|------|----------|-------|-------------|
|                 |           |        |      | Material | Color |             |
| 54-576          | SPST      | OFF    | (ON) | Nylon 66 | Black | S87         |

SPECIAL NOTE: ( ) = Momentary Function

S87



## Specifications

**Current Rating:** 25A 6VDC, 50A 12VDC  
**Insulation Resistance:** 100 Megohms (min.) at 500VDC  
**Dielectric Strength:** 1500V RMS (min.)  
**Temperature Rating:** +0° to +150°F (-18° to +65°C)  
**Electrical Life:** 25,000 cycles  
**Mechanical Life:** 100,000 cycles  
**Terminal Type:** Screw Terminals  
**Mounting Hole:** .630 (16.0)