

PRODUCT NUMBER
SEE TABLE

NOTES:

- ①. PRODUCT NUMBERING CODE:
50388 - X YYY Z LF
LEAD FREE (OPTIONAL)
TAIL LENGTH SEE TABLE
NO. OF POSITIONS SEE NOTE 2
PLATING SEE TABLE
BASE NUMBER

- PRODUCT NUMBERING CODE FOR
SELECT LOAD PARTS:
50388 - XX YYY
LEAD FREE (OPTIONAL)
SEQUENCE NUMBER
ALWAYS XX
BASE NUMBER

- ②. THIS PRODUCT IS CONFIGURED IN SIZES OF
10 THRU 80 COLUMNS IN INCREMENTS OF ONE.
i.e.: 10,11,12,13,.....79,80.

- ③. HOUSING MATERIAL: GLASS AND MINERAL FILLED
HIGH TEMP. THERMOPLASTIC. FLAME RETARDANT
PER UL94V-0. COLOR: BLACK.
CONTACT MATERIAL: BeCu


- ④. MANUFACTURE'S NAME, P/N AND LOT CODE TO APPEAR
ON THIS SURFACE AS PER BUS-12-108.

- ⑤. LENGTH FORMULAS
DIM A = $.100/2.54 \times \text{NO. OF COLUMNS} + .75/19.1$
DIM B = $.100/2.54 \times \text{NO. OF COLUMNS} + .45/11.4$
DIM C = $.100/2.54 \times \text{NO. OF COLUMNS} - .10/2.5$


6. THIS PRODUCT (WITH "LF" SUFFIX) MEETS EUROPEAN
UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS
AS DESCRIBED IN GS-22-008.

7. THIS HOUSING WILL WITHSTAND EXPOSURE TO 260° C PEAK
TEMPERATURE FOR 10-30 SECONDS IN A CONVECTION,
INFRA-RED OR VAPOR PHASE REFLOW OVEN.


- ⑧. PLATING OPTION:
MAY BE EITHER GOLD OR GXT PLATED AT MANUFACTURER'S OPTION.



SECTION X-X



SECTION U-U



RECOMMENDED PCB LAYOUT
(ALL HOLES LOCATED ON $.100/2.54$ GRID
UNLESS OTHERWISE SPECIFIED)

mat'l. code NOTE 3				surface ISO 1902	tolerance ISO 406 ISO 1101	projection	product family HPC
ltr	ecn no	dr	date	tolerances unless otherwise specified		INCH/MM scale 1:1	title
T				angles	linear		4 ROW VERTICAL RECEPTACLE
							SOLDER TO BOARD, 0 GUIDE PIN
				dr	D.SHEAFFER 10/7/92		dwg no
				engr	S.CLARK 10/7/92		sheet 2 of 3 size
				chr	S.CLARK 10/7/92		A3
				appd	S.CLARK 10/7/92		type
sheet	revision						Product Customer Drawing
index	sheet						

PRODUCT NUMBER	NUMBER OF POSITIONS SEE NOTE 2	TAIL LENGTH	TAIL PLATING	CONTACT PLATING NOTE 8
50388 -1YYYE	YYY	.125±.010/3.18±0.25	TIN LEAD	30u"/.76u Au
50388 -1YYYF	YYY	.145±.010/3.68±0.25	TIN LEAD	30u"/.76u Au
50388 -1YYYH	YYY	.180±.010/4.57±0.25	TIN LEAD	30u"/.76u Au
50388 -1YYYZ	YYY	.220±.010/5.59±0.25	TIN LEAD	30u"/.76u Au
50388 -3YYYE	YYY	.125±.010/3.18±0.25	TIN LEAD	50u"/1.27u Au
50388 -3YYYF	YYY	.145±.010/3.68±0.25	TIN LEAD	50u"/1.27u Au
50388 -3YYYH	YYY	.180±.010/4.57±0.25	TIN LEAD	50u"/1.27u Au
50388 -3YYYZ	YYY	.220±.010/5.59±0.25	TIN LEAD	50u"/1.27u Au
50388 -5YYYE	YYY	.125±.010/3.18±0.25	TIN LEAD	30u"/.76u GXT
50388 -5YYYELF	YYY	.125±.010/3.18±0.25	TIN	30u"/.76u GXT
50388 -5YYYF	YYY	.145±.010/3.68±0.25	TIN LEAD	30u"/.76u GXT
50388 -5YYYFLF	YYY	.145±.010/3.68±0.25	TIN	30u"/.76u GXT
50388 -5YYYH	YYY	.180±.010/4.57±0.25	TIN LEAD	30u"/.76u GXT
50388 -5YYYHLF	YYY	.180±.010/4.57±0.25	TIN	30u"/.76u GXT
50388 -5YYYZ	YYY	.220±.010/5.59±0.25	TIN LEAD	30u"/.76u GXT
50388 -5YYYZLF	YYY	.220±.010/5.59±0.25	TIN	30u"/.76u GXT

mat'l. code				surface ISO 1902		tolerance ISO 406 ISO 1101		projection		product family HPC	
NOTE 3										title	
ltr	ecn no	dr	date	tolerances unless otherwise specified				 INCH/MM scale 1:1		4 ROW VERTICAL RECEPTACLE SOLDER TO BOARD, 0 GUIDE PIN	
T				angles	linear	.XX±.01/XX±0.3 .XXX±.005/XX±0.13 .XXX±.0020/XXX±0.051					
				0'±2'						dwg no	
				dr	D.SHEAFFER	10/7/92			sheet 3 of 3		size
				engr	S.CLARK	10/7/92			50388		A3
				chr	S.CLARK	10/7/92					
				appd	S.CLARK	10/7/92					
sheet	revision									type Product Customer Drawing	
index	sheet										