


**GE Sensing**

A COMMITMENT TO EXCELLENCE

GE Sensing, Crown Industrial Estate, Priorswood Road, Taunton, Somerset, TA2 8QY, UK
Tel +44 (0) 1823 335200 Fax +44 (0) 1823 332637

TEST SPECIFICATION	PART No. YQS5868PTF	ISSUE: A
CUSTOMER: Various	DATE: 22nd February, 2011	QUANTITY:
Customer P/N:	ORIGINATOR: M.J.Roberts	PAGE 1 OF 1

DESCRIPTION: PTC THERMISTOR INTENDED FOR USE AS A CURRENT LIMITING PROTECTION DEVICE**MECHANICAL SPECIFICATION****CONSTRUCTION:** BARE CERAMIC DISC. THICK SILVER FILM ELECTRODES
UNINSULATED LEADWIRES.**TERMINATIONS:** STRAIGHT TYPE, TIN COATED COPPER WIRE**DIMENSIONS in mm:** SEE DRAWING AND TABLE BELOW.

	D	T	H	F	d	L
Max	13.5	5.1	14.0	6.0	0.66	
Min				4.0	0.55	25

ELECTRICAL SPECIFICATION

RESISTANCE AT 25°C, R_{25} : 50Ω ± 20% (1)
 SWITCHING TEMPERATURE, T_b : 110 ± 10°C (2)
 MAXIMUM CURRENT AT 25°C, WITHOUT TRIPPING, I_{nt} : 80mA
 MINIMUM SWITCHING CURRENT AT 25°C, I_t : 170mA
 MAXIMUM OPERATING VOLTAGE, V_{max} : 120V
 AMBIENT TEMPERATURE RANGE:

STORAGE: -25 to +155°C
 AT MAXIMUM VOLTAGE: +10 to +55°C

NOTES:

- (1) Measuring current: 5mA max.
 (2) Resistance = 2 × Resistance minimum

CHANGES SINCE LAST ISSUE: Δ							
Issue :	A						
Date :	22/02/11						