








△ MATERIAL:
HOUSING — PCT POLYESTER, BLACK, UL94V-0.
OVERMOLDED TERMINAL ARRAY — PBT, BROWN.
TERMINALS — 0.33 [0.13] THICK PHOS BRONZE
PLATED WITH 1.27 μ m [0.00050] MIN THICK
HARD GOLD IN LOCALIZED AREA AND 3.81 μ m
[0.00150] MIN THICK MATTE TIN IN SOLDER
AREA OVER 1.27 μ m [0.00050] MIN THICK
NICKEL UNDERPLATE.
SHIELDS — 0.25 [0.10] THICK COPPER ALLOY
PLATED WITH 1.27 μ m [0.00050] MINIMUM NICKEL
AND 2.03 μ m [0.00080] MINIMUM HOT TIN DIP
ON PCB GROUND TABS.

△ JACK CAVITY CONFORMS TO FCC RULES AND
REGULATIONS, PART 68 SUBPART F.

△ DATE CODE LOCATED ON REAR OF PART
APPROXIMATELY AS SHOWN:
FIRST 2 DIGITS ARE LAST 2 DIGITS OF YEAR,
SECOND 2 DIGITS ARE MANUFACTURING
WORK WEEK,
LAST DIGIT IS DAY OF WEEK, WITH SUNDAY = 1.



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 25MAY2005 T. SPRINKLE / L.A. MAYER CHK 25MAY2005 J. WESTMAN		 Tyco Electronics Corporation Harrisburg, Pa 17105-3608		PART NUMBER	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.25 [0.1] 3 PLC ± 0.13 [0.05] 4 PLC ± ± - ANGLES ± ± -		NAME APVC 25MAY2005 S. FLICKINGER		STACKED MODULAR JACK ASSEMBLY, 2x6 PORT, 8 POSITION, SHIELDED, PANEL GROUND, CATEGORY 5	
		PRODUCT SPEC 108-1163-2		SIZE 114-2048		CAGE CODE DRAWING NO RESTRICTED TO	
MATERIAL SEE NOTE 1		FINISH SEE NOTE 1		WEIGHT -		A1 00779 C=5569263 -	
CUSTOMER DRAWING				SCALE 4:1 SHEET 1 of 1 REV B			