



SHOULDER ELECTRONICS LIMITED

BANDPASS FILTER

Type	Center Frequency (MHz)	Insertion Loss	Passband Width		Spurious Response(dB)		Package	Overseas Type	SAMPLE DIMENSIONS TEST CIRCUIT
			±3dB	±30dB	Lower	Upper			
BF36A2D	36.00	21±2	8.1	9.4	32	32	SIP5D	X6857D	
BF43A2D	43.75	15±2	6	7.6	35	35	SIP5D	X6864D	
BF43A1D	43.75	15.2±2	6.2	7.6	35	35	SIP5D	X6964D	
BF44A2D	44.00	15.1±2	6.2	7.6	35	38	SIP5D	X6866D	
BF23A1D	23.40	11.8±2	1.8	3.1	33	36	SIP5D	X6863D	
BF36A1M	36.125	20.3±2	8	9.4	30	30	SIP5K	X6966M	
BF43A1M	43.75	15±2	6	7.6	35	35	SIP5K	X6964M	
BF44A1M	44.00	14.7±1.5	6	7.6	35	35	SIP5K	X6965M	
BF44A2M	44.00	15±2	1.7	2.9	35	32	SIP5K	X6959M	
BF46A1M	46.59	14.3±2	6	7.6	35	35	SIP5K	X6852M	
BF49A1M	49.125	12.2±2	0.72	1.95	34	34	SIP5K	X6921M	
BF44A3M	44.00	14.5±2	1.8	2.7	32	24	SIP5K	X9650M	
	44.00	15.0±2	1.2	2.4	32	25			
BF389A1M	38.912	18.7±2	1.52	2.62	36	38	SIP5K	X6922M	

ii



[\[Home | About SDE | Request Info | Saw Filter | Saw Resonator | Ceramic Resonator | Ceramic Discriminator |](#)
[Ceramic Filter1 | Ceramic Filter2 | Ceramic Trap | Crystal Unit | Clock Oscillator | Dielectric Filter | Dielectric Resonator\]](#)

Copyright 2001 by Shoulder Electronics Limited
 Contact Us: Tel: 86-755-2979884 Fax:86-755-2979885
 Questions or comments: info@china-shoulder.com