

www.vishay.com

Vishay General Semiconductor


Ultrafast Plastic Rectifier




PRIMARY CHARACTERISTICS							
I _{F(AV)}	1.0 A						
V_{RRM}	50 V, 100 V, 200 V, 400 V, 600 V, 800 V, 1000 V						
I _{FSM}	30 A						
t _{rr}	50 ns, 75 ns						
V_{F}	1.0 V, 1.7 V						
T _J max.	150 °C						
Package	DO-204AL (DO-41)						
Diode variations	Single die						

FEATURES







· Low switching losses, high efficiency

• High forward surge capability

Solder dip 275 °C max. 10 s, per JESD 22-B106

 Material categorization: For definitions of compliance please see <u>www.vishay.com/doc?99912</u>

TYPICAL APPLICATIONS

For use in high frequency rectification and freewheeling application in switching mode converters and inverters for consumer, computer, and telecommunication.

MECHANICAL DATA

Case: DO-204AL (DO-41)

Molding compound meets UL 94 V-0 flammability rating Base P/N-E3 - RoHS-compliant, commercial grade

Terminals: Matte tin plated leads, solderable per

J-STD-002 and JESD 22-B102

E3 suffix meets JESD 201 class 1A whisker test **Polarity:** Color band denotes cathode end

MAXIMUM RATINGS (T_A = 25 °C unless otherwise noted) **PARAMETER SYMBOL** UF4001 UF4002 UF4003 UF4004 UF4005 **UF4006 UF4007** UNIT Maximum repetitive peak 50 100 200 400 600 800 1000 ٧ V_{RRM} reverse voltage Maximum RMS voltage 35 70 140 280 420 560 700 ٧ V_{RMS} Maximum DC blocking voltage $V_{\text{DC}} \\$ 50 100 200 400 600 800 1000 ٧ Maximum average forward rectified current 1.0 Α I_{F(AV)} 0.375" (9.5 mm) lead length at $T_A = 55$ °C Peak forward surge current 8.3 ms single half 30 Α I_{FSM} sine-wave superimposed on rated load °C - 55 to + 150 Operating junction and storage temperature range T_J , T_{STG}

www.vishay.com

Vishay General Semiconductor

ELECTRICAL CHARACTERISTICS (T _A = 25 °C unless otherwise noted)											
PARAMETER	TEST CONDITIONS		SYMBOL	UF4001	UF4002	UF4003	UF4004	UF4005	UF4006	UF4007	UNIT
Maximum instantaneous forward voltage	1.0 A		V _F ⁽¹⁾			1.0		1.7			V
Maximum DC reverse current at rated DC		T _A = 25 °C	1_	10						μА	
blocking voltage		T _A = 100 °C	I _R	50							
Maximum reverse recovery time	I _F = 0.5 A, I _R = 1.0 A, I _{rr} = 0.25 A			50			75			ns	
Typical junction capacitance	4.0 V,	1 MHz	СЈ	17						рF	

Note

⁽¹⁾ Pulse test: 300 µs pulse width, 1 % duty cycle

THERMAL CHARACTERISTICS (T _A = 25 °C unless otherwise noted)									
PARAMETER	SYMBOL UF4001 UF4002 UF4003 UF4004 UF4005 UF4006 UF4007				UF4007	UNIT			
Typical thermal resistance	R _{θJA} ⁽¹⁾	60							°C/W
Typical trieffial resistance	R _{0JL} (1)	15						•	C/VV

Note

⁽¹⁾ Thermal resistance from junction to ambient at 0.375" (9.5 mm) lead length

ORDERING INFORMATION (Example)								
PREFERRED P/N	UNIT WEIGHT (g)	INIT WEIGHT (g) PREFERRED PACKAGE CODE		DELIVERY MODE				
UF4007-E3/54	0.33	54	5500	13" diameter paper tape and reel				
UF4007-E3/73	0.34	73	3000	Ammo pack packaging				

RATINGS AND CHARACTERISTICS CURVES (T_A = 25 °C unless otherwise noted)




Fig. 1 - Maximum Forward Current Derating Curve




Fig. 2 - Maximum Non-Repetitive Peak Forward Surge Current



www.vishay.com

Vishay General Semiconductor




Fig. 3 - Typical Instantaneous Forward Characteristics




Fig. 6 - Typical Reverse Leakage Characteristics




Fig. 4 - Typical Reverse Leakage Characteristics




Fig. 7 - Typical Junction Capacitance





Fig. 5 - Typical Instantaneous Forward Characteristics



www.vishay.com

Vishay General Semiconductor

PACKAGE OUTLINE DIMENSIONS in inches (millimeters)





Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.