


# FLT CONNECTOR





## 0.5mm pitch/Connectors for FPC



- Heat resisting design suitable for surface mounting
- · Staggered surface mount tails
- Embossed tape for automatic mounting
- FPC insertion is easy
- Compact design

## Specifications -

• Current rating: 0.5A AC, DC • Voltage rating: 50V AC, DC • Temperature range: -25°C to +85°C

(including temperature rise in applying

electrical current)

• Contact resistance: Initial value/50m  $\Omega$  max.

After environmental testing/20m  $\Omega$  max.

(variation from initial value)

 Insulation resistance: 500M  $\Omega$  min. Withstanding voltage: 200V AC/minute · Applicable FPC: Conductor pitch/0.5mm Conductor width/0.35mm

Mating part thickness/0.30±0.05mm

Note: FPC to be actually used should be checked for applicability.


- \* RoHS compliant products are published.
- \* Refer to "General Instruction and Notice when using Terminals and Connectors" at the end of this catalog.
- \* Contact JST for details.

#### Standards -

Recognized E60389

Certified LR20812

#### PC board layout (viewed from component side) and Assembly layout




Note: 1. Tolerances are non-cumulative: ±0.05mm for all centers.

2. The dimensions above should serve as a guide line. Contact JST for details.

# **FLT CONNECTOR**

#### Connector




Circuits	Model No.	Dimensions (mm)			Q'ty /
		А	В	С	reel
6	06FLT-SM2-TB	4.9	3.5	2.5	2,500
8	08FLT-SM2-TB	5.9	4.5	3.5	2,500
10	10FLT-SM2-TB	6.9	5.5	4.5	2,500
12	12FLT-SM2-TB	7.9	6.5	5.5	2,500
14	14FLT-SM2-TB	8.9	7.5	6.5	2,500
16	16FLT-SM2-TB	9.9	8.5	7.5	2,500
18	18FLT-SM2-TB	10.9	9.5	8.5	2,500
20	20FLT-SM2-TB	11.9	10.5	9.5	2,500
22	22FLT-SM2-TB	12.9	11.5	10.5	2,500
24	24FLT-SM2-TB	13.9	12.5	11.5	2,500
26	26FLT-SM2-TB	14.9	13.5	12.5	2,500
28	28FLT-SM2-TB	15.9	14.5	13.5	2,500
30	30FLT-SM2-TB	16.9	15.5	14.5	2,500
32	32FLT-SM2-TB	17.9	16.5	15.5	2,500
40	40FLT-SM2-TB	21.9	20.5	19.5	2,500

#### Material and Finish

Contact: Phosphor bronze, copper-undercoated, tin-plated (reflow treatment) Housing: PA 6T, UL94V-0

**RoHS compliance** This product displays (LF)(SN) on a label. Note: The products listed above are supplied on embossed-tape.


#### Lead section dimensions of FPC



Note: N --- Number of circuits

# **FLT** CONNECTOR

### Taping specifications -



#### Note

- 1. Specifications conform to JIS C 0806. The tape width, connector recess hole dimensions, etc. are determined by the number of circuits and external shape of the connector to be loaded.
- 2. Specifications are subject to change without prior notice.