

JJLV0UT840NOPPRTB

✓ ACTIVE

ALCOSWITCH | ALCOSWITCH JJ

TE Internal #: 2331397-1

5 mA Tactile Switch, Top Actuator, Off (On), Stainless Steel, Silver Contact Plating, ALCOSWITCH JJ

[View on TE.com >](#)



Switches > Tactile Switches



Actuator Style: **Top Actuator**
Operating Function: **Off (On)**
Contact Base Material: **Stainless Steel**
Switch Contact Plating Material: **Silver**
Contact Current Rating: **5 mA**

Features

Product Type Features

Leg Style	Kinked
Illuminated	Without
Actuator Style	Top Actuator

Configuration Features

Switch Feedback Type	Non-Tactile
ESD Grounding Terminal	Without
Ganged	Without
Operating Function	Off (On)
Configuration (Pole-Throw)	Single Pole - Single Throw
Number of Actuators	Single

Body Features

Actuator Material	Thermoplastic
Actuator Force	35 g[1.23 oz]
Product Orientation	Vertical



Actuator Color	Black
----------------	-------

Contact Features

Contact Base Material	Stainless Steel
Switch Contact Plating Material	Silver
Contact Current Rating	5 mA

Termination Features

Termination Method to PCB	Through Hole - Solder
---------------------------	-----------------------

Housing Features

Process Sealed	No
----------------	----

Usage Conditions

Operating Temperature Range	-20 – 70 °C[-4 – 158 °F]
-----------------------------	--------------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts



TE Part # 2331393-1
DET SW5.7X4.0X2.0 GW HORZ. NO AG RL



TE Part # 2331394-1
DET SW4.7X3.5X2.25 GW VERT. NOH AG RL



TE Part # 2331398-1
DET SW6.5X3.9X6.0 GW VERT. NO AG TB



TE Part # 2331370-1
DET SW4.7X3.8X2.3 GW VERT. NO AG RL




TE Part # 2331365-1
DET SW4.7X3.8X2.3 GW VERT. NO AG RL

Also in the Series | [ALCOSWITCH JJ](#)




Tactile Switches(52)

Customers Also Bought



TE Part #215309-8
2X8P HV100 REC CON. TE, 8.5MM



TE Part #1-215309-6
2X16P HV100 REC CON. TE, 8.5MM



TE Part #2-320571-2
PIDG R 22-16 COMM 22-18MIL 1/4



TE Part #CAT-C339-H85913
Power Resistors: Aluminum Housed, HSA



TE Part #1-1630027-8
HSC300 680R 5%



TE Part #4-1879140-2
RN 0603 49K9 0.1% 10PPM 5K RL



TE Part #1-2176327-9
CRGP 0805 330R 1%



TE Part #6-2176429-4
MPT100 560R 1%



TE Part #4-2176430-2
MPT35 6R8 1%

Documents

Product Drawings

DET SW6.5X3.9X6.0 TH VERT. NO AG TB

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2331397-1_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2331397-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2331397-1_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

JJ Series Detector Switches Data Sheet

English