


REV.	MODIFICATION.	DATE	DRN
01	PRODUCTION RELEASE	13/11/07	NJB
02	ECN2007-229	10/12/07	OW
03	ECN2007-236	14/12/07	NJB
04	ECN2008-014	22/01/08	SF
05	CO-2010036	11/02/08	OW
06	CO-2010179	09/04/08	MT
07	CO-2010232	14/05/08	SF




- NOTES:
- 1) TO FIT IN A Ø6.0 - 6.5 [.236 - .255] HOLE.
 - 2) PANEL THICKNESS 0.6 - 2.5 [.023 - .098] IN 0.2 [.008] INCREMENTS.
 - 3) OTHER MATERIALS AVAILABLE BY SPECIAL ORDER. ADD -HS, -V0 OR UVB TO THE END OF THE PART NUMBER, EXAMPLE WIT-30RCA-4-V0-M
- a) HEAT STABILIZED NYLON 6/6 UL94-V2, RMS-47, COLOUR: BLACK.
b) NYLON 6/6 UL94 V-0, RMS-19, COLOUR: NATURAL.
c) UVB STABILIZED NYLON 6/6 RMS-46, COLOUR: BLACK.

INFORMATION CONTAINED IN THIS DOCUMENT IS CONFIDENTIAL TO RICHCO INTERNATIONAL Co. Ltd. AND MAY NOT BE DISCLOSED OR REPRODUCED IN WHOLE OR PART WITHOUT THEIR WRITTEN CONSENT.



METRIC PRIMARY UNITS: mm
IMPERIAL SECONDARY UNITS: [inches]
GENERAL TOLERANCES ±0.25 [.010]
UNLESS OTHERWISE STATED
1 DECIMAL PLACE ±
2 DECIMAL PLACES ±
ANGULAR ±1°



MATERIAL: NYLON 6/6 UL94 V-2 (RMS-01)		COLOUR: NATURAL	
DESCRIPTION: CABLE TIE WITH CUPPED BASE		PART No: SEE TABLE	
DRG No: 07-121	NPR No: 2007-048	SHEET SIZE A4	
DRN NJB	DATE 31/10/07	CHKD TC	DATE 31/10/07
SCALE NTS	SHEET No. 1 OF 1		

WIT-30RCA-16	180.2 [7.094]	25.4 [1.00]	13 [30]	31.8 [1.250]
WIT-30RCA-12	174.6 [6.874]	19.8 [.779]	13 [30]	31.8 [1.250]
WIT-30RCA-8	168.3 [6.625]	13.5 [.531]	13 [30]	31.8 [1.250]
WIT-30RCA-4	160.7 [6.326]	7.1 [.279]	13 [30]	31.8 [1.250]
PART No.	'L' Ref	'A' Ref	MIN. LOOP TENSILE Kg [lbs]	MAX BUNDLE DIAMETER