

PRODUCT NUMBER
57202-XXX-XXXXXLF

PLATING
S = 0.38µm GOLD/GXT ON CONTACT AREA
2µm MIN MATTE TIN ON TAIL
G = 0.76µm GOLD/GXT ON CONTACT AREA
2µm MIN MATTE TIN ON TAIL
F = GOLD FLASH ON CONTACT AREA
2µm MIN MATTE TIN ON TAIL
T = 2-6.0µm FULL MATTE TIN
1.27µm MIN NICKEL UNDERPLATING

RoHS COMPATIBLE
SEE NOTE 7

POLARIZATION, SEE NOTE 6

PACKAGING, SEE NOTE 5

NB OF POS PER ROW : 02 TO 25


STYLE	POST LENGTH ±0.2
51	2.00
52	4.00
53	3.50
54	2.50

NOTES:




1. MATERIAL HOUSING: HIGH TEMP. THERMOPLASTIC
UL 94V-0, COLOR BLACK
2. MATERIAL TERMINAL: COPPER ALLOY
3. TO DETERMINE DIMENSIONS:
N = NUMBER OF POSITIONS PER ROW.
4. 7N MIN. PIN RETENTION IN EITHER DIRECTION.
5. PACKAGING:
 - = STANDARD PACKAGING IN POLYBAGS
 - = POLYBAGS PACKAGING WHEN POLARISATION FEATURE APPLICABLE.
 - U = TUBE AVAILABLE FROM 04 TO 25 POS PER ROW.
 - A = TAPE AND REEL WITH PICK UP CAP INSTALLED
IN THE CENTER OF THE PRODUCT FOR PICK AND PLACE
SEE TA 884 FOR PRODUCT AVAILABILITY.
 - K = TAPE AND REEL WITHOUT CAP, SEE TA884 FOR AVAILABILITY.
6. FOR POLARIZATION, SPECIFY POSITION NUMBER TO OMIT PIN.
EXAMPLE : 03 = OMIT PIN POSITION 3, SEE TOP VIEW.
OMIT FROM PRODUCT NUMBER IF THIS FEATURE IS NOT APPLICABLE.

7. RoHS COMPATIBLE PRODUCT SPECIFICATIONS

- a - PLATING:
 - "LF" MEANS THE PRODUCT IS LEAD-FREE,
2µm MINIMUM MATTE TIN OVER 1.27µm
MINIMUM NICKEL UNDERPLATE.
- b - MANUFACTURING PROCESS COMPATIBILITY
 - THE HOUSING WILL WITHSTAND EXPOSURE TO
260°C PEAK TEMPERATURE FOR 30 SECONDES
IN A CONVECTION, INFRA-RED OR VAPOR
PHASE REFLOW OVEN.
- c - LABELLING:
 - MEETS PACKAGING SPECS AS PER GS-14-920
- d - LEGAL STATEMENT : SEE GS-47-0004



TOP VIEW



CAP DIMS FOR 2x3 POS UP TO 2x25 POS		CAP DIMS FOR 2x2 POS	
mat'l. code		surface ☒ ISO 1302	tolerance ☒ ISO 406 ISO 1101
ltr ecn no dr date		tolerances unless otherwise specified	projection
L F09-0087 JCO 09.09.04		angles linear .X ±0.3	mm
M F11-0026 LMU 11.05.12		.XX ±0.13	scale 1:1
N B-19190 LMU 14.10.24		.XXX ±0.05	
P B-19797 AMA 14.12.16		dr L.MULIN 04.05.06	
R B-19988 LMU 15.01.13		engr J.COMPAGNON 04.11.25	
S B-20032 AMA 15.01.20		chr appd J.M.C 04.11.25	
sheet index		revision sheet	
product family		MINITEK	
title		UNSH HEADER 2.00 mm VERTICAL SMT	
dwg no		sheet 1 of 1	size A3
57202		CUSTOMER Drawing	